

USB-C to DVI Adapter Cable, 10 ft.

MODEL NUMBER: **U444-010-DE**



USB-C to DVI converter connects a DVI display to your tablet, MacBook, Chromebook, Ultrabook or smartphone's USB-C or Thunderbolt 3 port.

Features

USB-C to DVI Adapter Connects to Your Laptop's USB-C or Thunderbolt 3 Port This USB Type-C to DVI adapter connects a DVI monitor or projector to the USB-C or Thunderbolt 3 port on your computer, tablet, laptop, notebook, MacBook, Chromebook, Ultrabook or smartphone. It's an ideal connector for multitasking, presenting video at trade shows and conferences, editing documents, playing online games and watching movies on a larger screen. It saves you money by allowing you to use your existing DVI display instead of buying a new monitor.

Supports USB-C DisplayPort Alternate Mode for Transmitting Video Signals By connecting the USB-C cable to a source device that supports USB DisplayPort Alt Mode, you can output 1080p video to a compatible monitor or projector without installing special software drivers.

Transmits Crystal-Clear 1080p Video to a DVI Display Connect the dual-link DVI-D male connector to a compatible display to transmit high-definition video resolutions up to 1920 x 1200 (1080p) at 60 Hz. and 24-bit Deep Color (8 bits per channel).

Reversible USB-C Connector Attaches in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

Ready to Use Right from the Package, So You Can Plug and Play Immediately The plug-and-play USB Type-C to DVI cable is specifically designed for use with the MacBook, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no software, drivers or external power. The 10-foot (3-meter) length allows you great flexibility in placing the source and display devices where they're most convenient.

Highlights

- Transmits video signals from sources supporting USB DisplayPort Alt Mode
- Delivers HD picture quality at resolutions up to 1920 x 1200 (1080p) @ 60 Hz
- Plug-and-play operation with no software required for easy, immediate installation
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- 10 ft. length allows great flexibility in placing source and display devices
- Note: This cable is unidirectional. Will only work from a USB-C port to DVI port

Applications

- Connect your laptop to a DVI monitor in a lecture hall or conference room for a video presentation
- Add a secondary monitor to the MacBook, Chromebook or laptop in your office or home workspace
- Stream online video or games from your computer on a larger DVI display

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with DVI input



Package Includes

- U444-010-DE USB-C to DVI Adapter Cable (M/M), White, 10 ft. (3 m)

Specifications

OVERVIEW	
UPC Code	037332237378
INPUT	
Cable Length (ft.)	10
Cable Length (m)	3
Bus Powered	Yes
PHYSICAL	
Cable Jacket Rating	VW-1
Color	Black
Material of Construction	PVC
Unit Dimensions (hwd / in.)	0.65 x 1.64 x 1.99
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32 ~ 113F (0 ~ 45C)
Storage Temperature Range	14 ~ 158F (-10 ~ 70C)
Operating Humidity Range	10% ~ 85% RH
Storage Humidity Range	5% ~ 90% RH
CONNECTIONS	
Side A - Connector 1	DVI-D DUAL LINK (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	1080p
HDCP Specification	1.3



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
USB Power Delivery (PD) Charging Support	No
Max Supported Color Depth	24-bit True Color
Technology	DVI; USB 3.1 (Gen 1)
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>