





Rocker Switch


multicomp PRO

**RoHS
Compliant**

Specifications

Rating	: 20A 125V AC 1/3HP, 16A 250V AC 1/2HP 
	16A 125V AC, 10A 250V AC 
	10(4)A 250V 
	16A 125V AC, 10A 250V AC 
	16(4)A 250V AC
Contract Resistance	: 50m Ω Max.
Insulation Resistance	: DC 500V 100M Ω Min.
Dielectric Strength	: AC 1500V 1 minute
Operation Temperature	: -25°C to +85°C
Switch Function	: 2 Position SPST OFF-ON

Mounting Hole




Circuit Diagram



Thickness	X	Y
0.75-3	27.6-0.1	13.8+0.1
3-4	27.8-0.1	
4-5	28-0.1	

Material

Frame	: Nylon#66, Black
Actuator	: Nylon#66, Red/Black
Terminals	: Silver Plated, Copper Alloy



Tolerance ±0.3 Unless Otherwise Specified

Dimensions : Millimetres

Part Number Table

Description	Part Number
Rocker Switch, SPST, On-Off, Red/Balck	MP004573

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO