

### RoHS Compliant

- 1. Scope: This specification for approval relates to Extra High Power Thick Film Chip Resistors (KIT).
- 2. Type designation: The type designation shall be in the following form:


Туре	Power Rating	Resistance tolerance	Nominal Resistance
2512	3W	J	10Ω

### 3. Ratings:

Туре	2512
Power Rating at 70°C	3W
Max. Working Voltage	250 V
Max. Overload Voltage	500 V
Dielectric Withstanding Voltage	500 V
Temperature Range	-55°C to +155°C
Ambient Temperature	70°C

### 3.1 Power rating:

Resistors shall have a power rating based on continuous load operation at an ambient temperature of  $70^{\circ}$ C. For temperature in excess of  $70^{\circ}$ C, The load shall be derate as shown in figure 1.




3.2 Nominal Resistance : Effective figures of nominal resistance shall be in accordance with E-24 series




### multicomp PRO

#### 4. Construction



### 5. Power rating and dimensions



### **Dimension**

Type	Dimension (mm)				
Туре	L ±0.1	W ±0.15	H ±0.1	ℓ1 ±0.25	ℓ2 ±0.2
2512	6.35	3.2	1.1	0.6	1.8

### **Power Rating**

Туре	Power Rating	Tolerance	Resistance	Standard
	at 70°C	%	Range	Series
2512	3W	± 5	1Ω to $10$ mΩ	E-24

### 6. Marking:

### 6.1 Resistors

A. Marking for E-24 series 5% in size: 3 Digits

Ex. 102 1KΩ



<sup>\*</sup>The first 2 digits are significant figures of resistance and the 3th digit denoted number of zeros.



\*For ohmic values below 10  $\Omega$ , letter"R" is for decimal point.

Ex. R68 0.68\$\text{Q}
------------------------

### 7. Performance specification:

Characteristics	Limits	Test Methods (JIS C 5201-1)
Dielectric withstanding voltage	No evidence of flashover mechanical damage, arcing or insulation break down	4.7 Clamped in the trough of a 90°C metallic v-block and shall be tested at ac potential respectively specified in the type for 60-70 seconds
Temperature Coefficient	$1\Omega$ to $10\Omega$ ≤± $200$ PPM/°C $10.1\Omega$ to $10$ mΩ ≤± $100$ PPM/°C	4.8 Natural resistance change per temp. degree centigrade.  R2-R1  x 10 <sup>6</sup> (PPM/)  R1(t2-t1)  R1: Resistance value at room temperature (T1) R2: Resistance value at room temp. plus 100°c (T2) Test pattern: room temp. (T1), room temp. +100°C (T2)
Short time overload	Resistance change rate is ± (2% + 0.1Ω) Max.	4.13 Permanent resistance change after the application of a potential of 2.5 times RCWV for 5 seconds
Soldering temp. Reference	Electrical characteristics shall be satisfied. Without distinct deformation in appearance. (95% coverage Min.)	Wave soldering condition: (2 cycles Max.)  Pre-heat: 100°C to 120°C, 30 ±5 sec.  Suggestion solder temp.: 235°C to 255°C, 10 sec. (Max.)  Peak temp.: 260°C  Reflow soldering condition: (2 cycles Max.)  Pre-heat: 150°C to 180°C, 90°C to 120 sec.  Suggestion solder temp.: 235°C to 255°C, 20 to 40 sec.  Peak temp.: 260°C  Peak: 260°C (Max)  235°C ~ 255°C  200  Pre Heating Zone  150  Pre Heating Zone  150  Pre Heating Zone  150  Temperature profile for avaluation  Hand soldering condition:  The soldering iron tip temperature should be less than 300°C and maximum contract time should be 5 sec.






Characteristics	Limits	Test Methods (JIS C 5201-1)		
Soldering heat	Resistance change rate is: $\pm (1\%+0.05\Omega)$ Max.	4.18 Dip the resistor into a solder bath having a temperature of 260°C±3°C and hold it for 10±1 seconds.		
			4.19 Resistance change after continuous 5 cycles for duty cycle specified below :	
		Step	Temperature	Time
	Resistance change rate is	1	-55°C ±3°C	30 mins
Temperature cycling	$\pm$ (1% + 0.1Ω) Max.	2	Room temp.	10 to 15 mins
		3	+155°C ±2°C	30 mins
		4	Room temp.	10 to 15 mins
				•
Humidity	Resistance change rate is $\pm (3\% + 0.1\Omega)$ Max.	4.24 Temporary resistance change after 240 hours exposure in a humidity test chamber controlled at 40±2°C and 90-95% relative humidity		nber controlled at
Load life in humidity	Resistance change rate is ± (3% + 0.1Ω) Max.	7.9 Resistance change after 1,000 hours (1.5 hours "on", 0.5 hour "off") at RCWV in a humidity chamber controlled at 40°C ±2°C and 90 to 95 % relative humidity		
Load Life	Resistance change rate is ± (3% + 0.1Ω) Max.	4.25.1 Permanent resistance change after 1,000 hours operating at RCWV, with duty cycle of (1.5 hours"on", 0.5 hour"off") at 70°C ± 2°C ambient		cle of (1.5 hours"on", 0.5
Terminal bending	Resistance change rate is $\pm (1\% + 0.05\Omega)$ Max.	4.33 Twist of Test Board : Y/X = 3/90 mm for 60 seconds		

### 8. Kit resistors:

8.1 Insert for Chip Kit Dimension (mm)








#### 8.2 Album for Chip Kit

Dimension (mm)

\* Green Album



#### **Environment Related Substance**

This product complies to EU RoHS directive, EU PAHs directive, EU PFOS directive and Halogen free.

Ozone layer depleting substances.

Ozone depleting substances are not used in our manufacturing process of this product.

This product is not manufactured using Chloro fluorocarbons (CFCs), Hydrochlorofluorocarbons (HCFCs),

Hydrobromofluorocarbons (HBFCs) or other ozone depleting substances in any phase of the manufacturing process.

#### **Storage Condition**


The performance of these products, including the solderability, is guaranteed for a year from the date of arrival at your company, provided that they remain packed as they were when delivered and stored at a temperature of  $25^{\circ}$ C  $\pm$   $10^{\circ}$ C and a relative humidity of  $60^{\circ}$ RH  $\pm$   $10^{\circ}$ RH, chemical and dust free atmosphere

Even within the above guarantee periods, do not store these products in the following conditions.

Otherwise, their electrical performance and/or solderability may be deteriorated, and the packaging materials (e.g. taping materials) may be deformed or deteriorated, resulting in mounting failures.

- 1. In salty air or in air with a high concentration of corrosive gas, such as Cl<sub>2</sub>, H<sub>2</sub>S, NH<sub>3</sub>, SO<sub>2</sub>, or NO<sub>2</sub>
- 2. In direct sunlight

### Recommended solder pad



А	В	С
3.7 mm.	2.8 mm.	2.7 mm.

4 layers PCB specification:

- 1) Outside 2 layers (Top and Bottom) with copper foil thickness at 2oz.
- 2) Inside 2 layers (Middle layers) with copper foil thickness at 4 oz.





PRODUCT: Kit +/-5%
E24 Series = 87 values (1R to 10M)
(With resistor 1 strip per value)
Total Qty: 4,300pcs.)

NO.	Value
1	1E
2	1.2E
3	1.5E
4	1.8E
5	2.2E
6	2.7E
7	3.3E
8	3.9E
9	4.7E
10	5.6E
11	6.8E
12	8.2E
13	10E
14	12E
15	15E
16	18E
17	22E
18	27E
19	33E
20	39E
21	47E
22	56E

	Iotal C
NO.	Value
23	68E
24	82E
25	100E
26	120E
27	150E
28	180E
29	200E
30	220E
31	270E
32	300E
33	330E
34	390E
35	470E
36	560E
37	680E
38	820E
39	1K
40	1.2K
41	1.5K
42	1.8K
43	2.2K
44	2.7K

NO.	Value
45	3.3K
46	3.9K
47	4.7K
48	5.6K
49	6.8K
50	8.2K
51	10K
52	12K
53	15K
54	18K
55	22K
56	27K
57	33K
58	39K
59	47K
60	56K
61	68K
62	82K
63	100K
64	120K
65	150K
66	180K

NO.	Value
67	220K
68	270K
69	330K
70	390K
71	470K
72	560K
73	680K
74	820K
75	1M
76	1.2M
77	1.5M
78	1.8M
79	2.2M
80	2.7M
81	3.3M
82	3.9M
83	4.7M
84	5.6M
85	6.8M
86	8.2M
87	10M

### **Part Number Table**

Description	Part Number
Chip Resistor Kit, 3W, 5%, 1R to 10M, E24, 2512, 4300 Pcs	MP002931

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

