



### Main

Range of product	Square D Pumptrol
Pressure sensor name	9013FH
Pressure sensor size	200 psi
Value of setting	Off at 175 psi
Electrical circuit type	Power circuit
Product specific application	Control small electrically driven air compressors
Quantity per set	1
Type of packing	Individual

### Complementary

Pressure sensor type	Electromechanical pressure switch
Controlled fluid	Air (-22...257 °F)
Adjustable range on rising pressure	689.48...1378.95 kPa
Approximate fixed differential	275.79 kPa
Destruction pressure	1516.85 kPa
Pressure actuator	Diaphragm
Pressure switch type of operation	Regulation between 2 thresholds
Scale type	Fixed differential
Setting	Internal
Local display	Without
Contacts type and composition	2 NC, snap action, DPST-DB, Form YY
Cable entry number	2 0.88 in cable entries with 0.84 in across flats conforming to UL 508
Electrical connection	Screw-clamp terminals, clamping capacity: 10 AWG Screw-clamp terminals, clamping capacity: 5.261 mm <sup>2</sup>
Fluid connection type	0.25 inch 4-way flange conforming to UL 508
Short-circuit protection	20 A cartridge fuse, type gG
Materials in contact with fluid	Zinc plated steel or equivalent flange Nitrile (Buna-N) or equivalent rubber diaphragm
Material	Polypropylene: cover Noryl thermoplastic resin or equivalent: cover
Operating position	Any position
Motor power kW	1.5 kW (2 hp) at 230 V AC, 1 phase

1.1 kW (1.5 hp) at 115 V AC, 1 phase  
 1.5 kW (2 hp) at 115 V AC, 3 phases  
 2.2 kW (3 hp) at 230 V AC, 3 phases  
 0.75 kW (1 hp) at 460 V AC, 3 phases  
 0.75 kW (1 hp) at 575 V AC, 3 phases

Electrical durability	100000 cycles, operating rate <10 cyc/mn
Mechanical durability	300000 cycles
Terminal block type	4 terminals
Maximum operating rate	10 cyc/mn
[Ui] rated insulation voltage	575 V conforming to UL 508
Net weight	0.45 kg
Repeat accuracy	+/- 3 %
Terminals description ISO n°1	L1-T1 L2-T2
Width	78.74 mm
Height	113.03 mm
Depth	95.50 mm
Factory modification	Maintained manual cut-out lever (AUTO-OFF) 2-way pressure release valve

## Environment

Standards	UL 508 CE
Ambient air temperature for operation	-36...125 °C
Ambient air temperature for storage	-36...125 °C
Protective treatment	None
NEMA degree of protection	NEMA 1 conforming to UL 50
IP degree of protection	IP20 conforming to IEC 60529
Product certifications	UL listed file E12158 CSA file LR25490

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------