



### Main

Range	TeSys
Device short name	GV2ME
Product or component type	Motor starter
Motor starter type	Non reversing
Poles description	3P
Utilisation category	AC-3
Motor power kW	1.5 kW at 440 V AC 50/60 Hz 1.1 kW at 400/415 V AC 50/60 Hz 1.5 kW at 400/415 V AC 50/60 Hz 1.5 kW at 500 V AC 50/60 Hz 2.2 kW at 500 V AC 50/60 Hz
[Uc] control circuit voltage	24 V AC 50/60 Hz
Magnetic tripping current	51 A

### Complementary

Device composition	1 motor circuit breaker type GV2ME 1 3-pole contactor 1 combination block GV2AF01
Coordination type	Type 1
Thermal protection adjustment range	2.5...4 A
Breaking capacity	50 kA I <sub>q</sub> at 400/415 V AC 50/60 Hz conforming to IEC 60947-4-1 50 kA I <sub>q</sub> at 440 V AC 50/60 Hz conforming to IEC 60947-4-1 50 kA I <sub>q</sub> at 500 V AC 50/60 Hz conforming to IEC 60947-4-1
Net weight	0.46 kg
Height	152 mm
Width	45 mm
Depth	87 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------