

2812X Figure-8 Twin



Features

- Plain annealed copper conductor in a flat figure 8 construction and PVC insulated with one core ribbed for identification
- Conforms to BS6500, harmonised code H03VH-H

Specification Table

Characteristics	Part Number			
	2812X 0.5 BLK	2812X 0.5 WHI	2812X 0.75 BLK	2812X 0.75 WHI
Specification	2812X Figure 8 Twin 3A (0.5mm ²)		2812X Figure 8 Twin 6A (0.75mm ²)	
Number of Wires	28 × 0.15		42 × 0.15	
Conductor	Plain annealed copper wire			
Insulation	PVC			
Nominal Wall Thickness	0.8			
Maximum Temperature (°C)	70			
Voltage Rating (V)	300 / 300			
Nominal Overall Dimensions	2.8 × 5.5		3 × 5.9	
Weight (Kg / Km)	24		29	
Colour	Black	White	Black	White
Current Rating (A)	3		6	
Reel Length (m)	100			

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.