



Main

Range	TeSys
Product name	TeSys GS
Device short name	GS2D
Product or component type	Switch-disconnector-fuse
Poles description	4P
Protected poles description	4t
Contacts type and composition	4 NO
[I _{th}] conventional free air thermal current	32 A (at 40 °C)
[I _e] rated operational current	20 A at 440 V 2 poles in series per phase DC-23A 20 A at 440 V 2 poles in series per phase DC-23B 32 A at 400 V AC-23A 32 A at 400 V AC-23B 32 A at 500 V AC-23A 32 A at 500 V AC-23B 32 A at 690 V AC-23A 32 A at 690 V AC-23B
Fuse type	BS
Fuse size	A1
Network type	DC AC
Network frequency	50/60 Hz

Complementary

Type of operating handle	External frontal External right side
Mounting support	Rail Plate
[U _i] rated insulation voltage	750 V AC 50/60 Hz
[U _{imp}] rated impulse withstand voltage	8 kV
Rated operational power in W	15 kW at 400 V 18.5 kW at 500 V 25 kW at 690 V
Making capacity	320 A at 400 V AC-23B

[Icm] rated short-circuit making capacity	80 kA at 400 V with protection by gG fuses
Breaking capacity	256 A at 400 V (AC-23B)
Short-circuit withstand	9 kA
Mechanical durability	10000 cycles
Electrical durability	1500 cycles AC-23A 1500 cycles AC-23B 300 cycles DC-23A 300 cycles DC-23B
Connections - terminals	Power circuit: screw-clamp terminals 6...25 mm ²
Tightening torque	Power circuit: 3.2 N.m

Environment

Standards	IEC 60947-3
Product certifications	CE
IP degree of protection	IP20 conforming to IEC 60529 (with terminal cover)
Ambient air temperature for operation	-20...70 °C
Ambient air temperature for storage	-40...80 °C
Fire resistance	960 °C body conforming to IEC 60695-2-1
Height	118 mm
Width	148 mm
Depth	87 mm
Net weight	1 kg

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration

Contractual warranty

Warranty	18 months
----------	-----------