

EVO-STIK LIQUID NAILS GRAB ADHESIVE
Supersedes Date: 07-Apr-2020Revision date 02-Jul-2020
Revision Number 3**SECTION 1: Identification of the substance/mixture and of the company/undertaking****1.1. Product Identifier****Product Name** EVO-STIK LIQUID NAILS GRAB ADHESIVE
Pure substance/mixture Mixture**1.2. Relevant identified uses of the substance or mixture and uses advised against****Recommended use** Adhesive.
Uses advised against None known**1.3. Details of the supplier of the safety data sheet****Company Name**Bostik Limited
Common Rd
ST16 3EH
Stafford UK
Tel: +44 (1785) 27 26 25
Fax: +44 (1785) 25 72 36**E-mail address** SDS.box-EU@bostik.com**1.4. Emergency telephone number****United Kingdom** +44 (1785) 272650
Ireland +353 (1) 8624900 (Monday- Friday 9am-5pm)**SECTION 2: Hazards identification****2.1. Classification of the substance or mixture**

Regulation (EC) No 1272/2008

Skin corrosion/irritation	Category 2 - (H315)
Chronic aquatic toxicity	Category 3 - (H412)
Flammable liquids	Category 2 - (H225)

2.2. Label Elements**Signal word**
DANGER**Hazard statements**H315 - Causes skin irritation.
H412 - Harmful to aquatic life with long lasting effects.
H225 - Highly flammable liquid and vapour.

SAFETY DATA SHEET

EVO-STIK LIQUID NAILS GRAB ADHESIVE
Supersedes Date: 07-Apr-2020

Revision date 02-Jul-2020
Revision Number 3

Precautionary statements

P101 - If medical advice is needed, have product container or label at hand.
P102 - Keep out of reach of children.
P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P273 - Avoid release to the environment.
P280 - Wear protective gloves and eye/face protection.
P302 + P352 - IF ON SKIN: Wash with plenty of water and soap.
P403 + P233 - Store in a well-ventilated place. Keep container tightly closed.
P501 - Dispose of contents/ container to an approved waste disposal plant.

Additional information

This product requires tactile warnings if supplied to the general public.

2.3. Other Hazards

In use may form flammable/explosive vapour-air mixture

PBT & vPvB

This mixture contains no substance considered to be persistent, bioaccumulating or toxic (PBT) This mixture contains no substance considered to be very persistent nor very bioaccumulating (vPvB)

SECTION 3: Composition/information on ingredients

3.1 Substances

Not applicable

3.2. Mixtures

Chemical name	EC No	CAS No	Weight-%	Classification according to Regulation (EC) No. 1272/2008 [CLP]	Specific concentration limit (SCL)	REACH Registration Number
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics	927-510-4	--	10 - <20	STOT SE 3 (H336) Asp. Tox. 1 (H304) Skin Irrit. 2 (H315) Aquatic Chronic 2 (H411) Flam. Liq. 2 (H225)		01-2119475515-33-xxxx
Hydrocarbons, C6, isoalkanes, <5% n-hexane	931-254-9	--	5 - <10	STOT SE 3 (H336) Asp. Tox. 1 (H304) Skin Irrit. 2 (H315) Aquatic Chronic 2 (H411) Flam Liq. 2 (H225) (EUH066)		01-2119484651-34-XXXX

Full text of H- and EUH-phrases: see section 16

Note: ^ indicates not classified, however, the substance is listed in section 3 as it has an OEL

SAFETY DATA SHEET

EVO-STIK LIQUID NAILS GRAB ADHESIVE
Supersedes Date: 07-Apr-2020

Revision date 02-Jul-2020
Revision Number 3

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (Regulation (EC) No. 1907/2006 (REACH), Article 59)

SECTION 4: First aid measures

4.1. Description of first aid measures

General advice	Show this safety data sheet to the doctor in attendance.
Inhalation	Remove to fresh air. Get medical attention immediately if symptoms occur.
Eye contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Keep eye wide open while rinsing. Do not rub affected area. Remove contact lenses, if present and easy to do. Continue rinsing. Consult an ophthalmologist.
Skin contact	Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Get medical attention if irritation develops and persists.
Ingestion	Clean mouth with water and drink afterwards plenty of water. Never give anything by mouth to an unconscious person. Do NOT induce vomiting. Call a doctor.
Self-protection of the first aider	Remove all sources of ignition. Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination. Use personal protective equipment as required. See section 8 for more information. Avoid contact with skin, eyes or clothing.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms	No information available.
-----------------	---------------------------

4.3. Indication of any immediate medical attention and special treatment needed

Note to doctors	Treat symptomatically.
------------------------	------------------------

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	Dry chemical. Carbon dioxide (CO ₂). Water spray. Alcohol resistant foam.
Unsuitable extinguishing media	Do not use straight streams. CAUTION: Use of water spray when fighting fire may be inefficient.

5.2. Special hazards arising from the substance or mixture

Specific hazards arising from the chemical	Risk of ignition. Keep product and empty container away from heat and sources of ignition. In the event of fire, cool tanks with water spray. Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
Hazardous combustion products	Carbon dioxide (CO ₂). Silicon oxides.

5.3. Advice for firefighters

Special protective equipment for fire-fighters	Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment.
---	--

SECTION 6: Accidental release measures

SAFETY DATA SHEET

EVO-STIK LIQUID NAILS GRAB ADHESIVE
Supersedes Date: 07-Apr-2020

Revision date 02-Jul-2020
Revision Number 3

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions	Evacuate personnel to safe areas. Use personal protective equipment as required. Avoid contact with skin, eyes or clothing. Avoid breathing vapours or mists. Ensure adequate ventilation. ELIMINATE all ignition sources (no smoking, flares, sparks or flames in immediate area). Pay attention to flashback. Take precautionary measures against static discharges. All equipment used when handling the product must be grounded.
Other information	Ventilate the area. Refer to protective measures listed in Sections 7 and 8.
For emergency responders	Use personal protection recommended in Section 8.

6.2. Environmental precautions

Environmental precautions	Prevent further leakage or spillage if safe to do so. Prevent product from entering drains. Do not allow to enter into soil/subsoil.
----------------------------------	--

6.3. Methods and material for containment and cleaning up

Methods for containment	Dyke far ahead of spill; use dry sand to contain the flow of material. Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal.
Methods for cleaning up	Dam up. Soak up with inert absorbent material. Pick up and transfer to properly labelled containers. Take up mechanically, placing in appropriate containers for disposal.
Prevention of secondary hazards	Eliminate all ignition sources if safe to do so.

6.4. Reference to other sections

Reference to other sections	See section 8 for more information. See section 13 for more information.
------------------------------------	--

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling	Use personal protection equipment. Avoid breathing vapours or mists. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Use grounding and bonding connection when transferring this material to prevent static discharge, fire or explosion. Use with local exhaust ventilation. Use spark-proof tools and explosion-proof equipment. Keep in an area equipped with sprinklers. Use according to package label instructions. Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Do not eat, drink or smoke when using this product.
General hygiene considerations	Keep away from food, drink and animal feedingstuffs. Do not eat, drink or smoke when using this product. Wash hands before breaks and immediately after handling the product. Contaminated work clothing should not be allowed out of the workplace. Regular cleaning of equipment, work area and clothing is recommended. Wear suitable gloves and eye/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Storage Conditions	Keep containers tightly closed in a dry, cool and well-ventilated place. Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity). Keep in properly labelled containers. Do not store near combustible materials. Keep in an area equipped with sprinklers. Store in accordance with the particular national regulations.
---------------------------	--

7.3. Specific end use(s)

SAFETY DATA SHEET

EVO-STIK LIQUID NAILS GRAB ADHESIVE
Supercedes Date: 07-Apr-2020

Revision date 02-Jul-2020
Revision Number 3

Specific Use(s)
Adhesive.

Risk Management Methods (RMM) The information required is contained in this Safety Data Sheet.

Other information Observe technical data sheet.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure Limits This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies

Chemical name	European Union	Ireland	United Kingdom
Kaolin 1332-58-7	-	TWA: 2 mg/m ³	TWA: 2 mg/m ³ STEL: 6 mg/m ³
Isopropyl alcohol 67-63-0	-	TWA: 200 ppm STEL: 400 ppm Sk*	TWA: 400 ppm TWA: 999 mg/m ³ STEL: 500 ppm STEL: 1250 mg/m ³

Derived No Effect Level (DNEL) No information available

Derived No Effect Level (DNEL) Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics (--)			
Type	Exposure route	Derived No Effect Level (DNEL)	Safety factor
worker Long term Systemic health effects	Inhalation	2085 mg/m ³	
worker Long term Systemic health effects	Dermal	300 mg/kg bw/d	

Derived No Effect Level (DNEL) Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics (--)			
Type	Exposure route	Derived No Effect Level (DNEL)	Safety factor
Consumer Long term Systemic health effects	Inhalation	447 mg/m ³	
Consumer Long term Systemic health effects	Dermal	149 mg/kg bw/d	
Consumer Long term Systemic health effects	Oral	149 mg/kg bw/d	

Predicted No Effect Concentration (PNEC) No information available.

8.2. Exposure controls

Engineering controls Ensure adequate ventilation, especially in confined areas.

Personal Protective Equipment

Eye/face protection
Hand protection

Tight sealing safety goggles.
Wear protective gloves. Gloves must conform to standard EN 374. The breakthrough

SAFETY DATA SHEET

EVO-STIK LIQUID NAILS GRAB ADHESIVE
Supersedes Date: 07-Apr-2020

Revision date 02-Jul-2020
Revision Number 3

Skin and body protection Respiratory protection

Recommended filter type:

time of the gloves depends on the material and the thickness as well as the temperature. Ensure that the breakthrough time of the glove material is not exceeded. Refer to glove supplier for information on breakthrough time for specific gloves. Gloves should be replaced regularly and if there is any sign of damage to the glove material. Antistatic footwear. Wear fire/flame resistant/retardant clothing. In case of mist, spray or aerosol exposure wear suitable personal respiratory protection and protective suit. In case of inadequate ventilation wear respiratory protection. Organic gases and vapours filter conforming to EN 14387.

Environmental exposure controls Do not allow into any sewer, on the ground or into any body of water.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	Liquid
Appearance	Paste
Colour	Light yellow
Odour	Solvent
Odour threshold	No information available

Property	Values	Remarks • Method
pH	No data available	
Melting point / freezing point	No data available	
Boiling point / boiling range	66 °C	
Flash point	-20 °C	
Evaporation rate	No data available	
Flammability (solid, gas)	Not applicable for liquids	
Flammability Limit in Air		
Upper flammability or explosive limits	No data available	
Lower flammability or explosive limits	No data available	
Vapour pressure	No data available	
Vapour density	No data available	
Relative density	No data available	
Water solubility	No data available	
Solubility(ies)	No data available	
Partition coefficient	No data available	
Autoignition temperature	No data available	
Decomposition temperature		
Kinematic viscosity	> 700 mm ² /s	
Dynamic viscosity	No data available	
Explosive properties	No data available	
Oxidising properties	No data available	

9.2. Other information

Solid content (%)	No information available
VOC Content (%)	No information available
Density	1.43

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity No information available.

10.2. Chemical stability

SAFETY DATA SHEET

EVO-STIK LIQUID NAILS GRAB ADHESIVE
Supersedes Date: 07-Apr-2020

Revision date 02-Jul-2020
Revision Number 3

Stability Stable under normal conditions.

Explosion data
Sensitivity to mechanical impact None.
Sensitivity to static discharge Yes.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions None under normal processing.

10.4. Conditions to avoid

Conditions to avoid Heat, flames and sparks.

10.5. Incompatible materials

Incompatible materials Strong acids. Strong bases. Strong oxidising agents.

10.6. Hazardous decomposition products

Hazardous decomposition products None under normal use conditions. Stable under recommended storage conditions.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Information on likely routes of exposure

Product Information .

Inhalation May cause irritation of respiratory tract.

Eye contact Irritating to eyes.

Skin contact Causes skin irritation.

Ingestion Based on available data, the classification criteria are not met.

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms Redness. May cause redness and tearing of the eyes.

Numerical measures of toxicity

Acute toxicity

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (dermal) 4,132.20 mg/kg

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics --	LD50 >5840 mg/kg Rat	LD50 >2920 mg/kg (Rattus)	LC50 >23.3 mg/L (4h)(Rat, vapour) (OECD 403)
Hydrocarbons, C6, isoalkanes,	>16750 mg/Kg (Rattus)	>3350 mg/Kg (Oryctolagus	259354 mg/m ³ (vapour) (rat

SAFETY DATA SHEET

EVO-STIK LIQUID NAILS GRAB ADHESIVE
 Supersedes Date: 07-Apr-2020

Revision date 02-Jul-2020
 Revision Number 3

<5% n-hexane --		cuniculus) OECD 402	OECD 403)
--------------------	--	---------------------	-----------

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation Classification based on data available for ingredients. Causes skin irritation.

Serious eye damage/eye irritation Based on available data, the classification criteria are not met.

Respiratory or skin sensitisation Based on available data, the classification criteria are not met.

Germ cell mutagenicity Based on available data, the classification criteria are not met.

Carcinogenicity Based on available data, the classification criteria are not met.

Reproductive toxicity Based on available data, the classification criteria are not met.

STOT - single exposure Based on available data, the classification criteria are not met.

STOT - repeated exposure Based on available data, the classification criteria are not met.

Aspiration hazard Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

12.1. Toxicity

Ecotoxicity Harmful to aquatic life with long lasting effects.

Chemical name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea	M-Factor	M-Factor (long-term)
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics --	ErL50 (72h) = 10-30 mg/L (Pseudokirchneriella subcapitata)	LL50 (96h) >13.4 mg/L (Oncorhynchus mykiss) OECD 203	-	EL50 (48h) = 3.0 mg/L (Daphnia magna)		
Hydrocarbons, C6, isoalkanes, <5% n-hexane --	EL50 (72h) = 13.6 mg/l (Pseudokirchneriella subcapitata)	LL50 (96h) = 18.27 mg/l (Oncorhynchus mykiss)	-	EL50 (48h)= 31.9 mg/l (Daphnia magna)		

12.2. Persistence and degradability

Persistence and degradability No information available.

Component Information

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics (--)

Method	Exposure time	Value	Results
--------	---------------	-------	---------

SAFETY DATA SHEET

EVO-STIK LIQUID NAILS GRAB ADHESIVE
Supersedes Date: 07-Apr-2020

Revision date 02-Jul-2020
Revision Number 3

OECD Test No. 301F: Ready Biodegradability: Manometric Respirometry Test (TG 301 F)	28 days	98%	Readily biodegradable
---	---------	-----	-----------------------

12.3. Bioaccumulative potential

Bioaccumulation There is no data for this product.

Component Information

Chemical name	Partition coefficient	Bioconcentration factor (BCF)
Hydrocarbons, C6, isoalkanes, <5% n-hexane --	3.6	501

12.4. Mobility in soil

Mobility in soil No information available.

12.5. Results of PBT and vPvB assessment

PBT and vPvB assessment No information available.

12.6. Other adverse effects

Other adverse effects No information available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste from residues/unused products Should not be released into the environment. Dispose of in accordance with local regulations. Dispose of waste in accordance with environmental legislation.

Contaminated packaging Empty containers pose a potential fire and explosion hazard. Do not cut, puncture or weld containers.

European Waste Catalogue 08 04 09* waste adhesives and sealants containing organic solvents or other dangerous substances
15 01 10*: Packaging containing residues of or contaminated by dangerous substances

Other information Waste codes should be assigned by the user based on the application for which the product was used.

SECTION 14: Transport information

Note: The shipping descriptions shown here are for bulk shipments only, and may not apply to shipments made in non-bulk packages (see regulatory definition). The information shown here, may not always agree with the bill of lading shipping description for the material.

Land transport (ADR/RID)

14.1 UN number UN1133
14.2 Proper Shipping Name Adhesives
14.3 Transport hazard class(es) 3
Labels 3

SAFETY DATA SHEET

EVO-STIK LIQUID NAILS GRAB ADHESIVE
Supersedes Date: 07-Apr-2020

Revision date 02-Jul-2020
Revision Number 3

14.4 Packing group	II
Description	UN1133, Adhesives, 3, II, (D/E)
14.5 Environmental hazards	Not applicable
14.6 Special Provisions	640D
Classification code	F1
Tunnel restriction code	(D/E)
Limited Quantity (LQ)	5 L
ADR Hazard Id (Kemmler Number)	33

IMDG

14.1 UN number	UN1133
14.2 Proper Shipping Name	Adhesives
14.3 Transport hazard class(es)	3
14.4 Packing group	II
Description	UN1133, Adhesives, 3, II, (-20°C c.c.)
14.5 Marine pollutant	Np
14.6 Special Provisions	None
Limited Quantity (LQ)	5 L
EmS-No	F-E, S-D
14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	Not applicable

Air transport (ICAO-TI / IATA-DGR)

14.1 UN number	UN1133
14.2 Proper Shipping Name	Adhesives
14.3 Transport hazard class(es)	3
14.4 Packing group	II
Description	UN1133, Adhesives, 3, II
14.5 Environmental hazards	Not applicable
14.6 Special Provisions	A3
Limited Quantity (LQ)	1 L
ERG Code	3L

Section 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

European Union

Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work

Check whether measures in accordance with Directive 94/33/EC for the protection of young people at work must be taken.

Take note of Directive 92/85/EC on the protection of pregnant and breastfeeding women at work

Registration, Evaluation, Authorization, and Restriction of Chemicals (REACH) Regulation (EC 1907/2006)

SVHC: Substances of Very High Concern for Authorisation:

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (Regulation (EC) No. 1907/2006 (REACH), Article 59)

EU-REACH (1907/2006) - Annex XVII - Substances subject to Restriction

This product does not contain substances subject to restriction (Regulation (EC) No. 1907/2006 (REACH), Annex XVII).

Substance subject to authorisation per REACH Annex XIV

This product does not contain substances subject to authorisation (Regulation (EC) No. 1907/2006 (REACH), Annex XIV)

SAFETY DATA SHEET

EVO-STIK LIQUID NAILS GRAB ADHESIVE
Supersedes Date: 07-Apr-2020

Revision date 02-Jul-2020
Revision Number 3

Dangerous substance category per Seveso Directive (2012/18/EU)

P5a - FLAMMABLE LIQUIDS
P5b - FLAMMABLE LIQUIDS
P5c - FLAMMABLE LIQUIDS

Ozone-depleting substances (ODS) regulation (EC) 1005/2009
Not applicable

Persistent Organic Pollutants
Not applicable

15.2. Chemical safety assessment

Chemical Safety Assessments have been carried out by the Reach registrants for substances registered at >10 tpa. No Chemical Safety Assessment has been carried out for this mixture

SECTION 16: Other information

Key or legend to abbreviations and acronyms used in the safety data sheet

Full text of H-Statements referred to under section 3

EUH066 - Repeated exposure may cause skin dryness or cracking
H225 - Highly flammable liquid and vapour
H304 - May be fatal if swallowed and enters airways
H315 - Causes skin irritation
H336 - May cause drowsiness or dizziness
H411 - Toxic to aquatic life with long lasting effects

Legend

TWA	TWA (time-weighted average)
STEL	STEL (Short Term Exposure Limit)
Ceiling	Ceiling Limit Value
*	Skin designation
SVHC	Substance(s) of Very High Concern
PBT	Persistent, Bioaccumulative, and Toxic (PBT) Chemicals
vPvB	Very Persistent and very Bioaccumulative (vPvB) Chemicals
STOT RE	Specific target organ toxicity - Repeated exposure
STOT SE	Specific target organ toxicity - Single exposure
EWC	European Waste Catalogue

Key literature references and sources for data

No information available

Prepared By Product Safety & Regulatory Affairs

Revision date 02-Jul-2020

Indication of changes

Revision note Not applicable.

Training Advice Provide adequate information, instruction, and training for operator

Further information No information available

SAFETY DATA SHEET

EVO-STIK LIQUID NAILS GRAB ADHESIVE
Supersedes Date: 07-Apr-2020

Revision date 02-Jul-2020
Revision Number 3

This material safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet