

Data sheet

Art.No.: 83.050.0000.0

HMI Touch Panel HMI-ECO-043

HMI Eco touch panel, 4,3" diagonal, TFT, 480x272 Pixel, IP66 for frontside, 64 MB RAM, USB Host/Client, Ethernet, Modbus TCP, Programmable with the software hmiPLAN



Art.No.	83.050.0000.0
EAN	4049088468735
Order Unit	1

Certificates / Approvals



Technical data

Supply circuit

Min. rated supply voltage at DC	21.6 V
Max. rated supply voltage at DC	26.4 V
Voltage type	DC
Rated consumption DC	10 W

Dimensions

Width of the front	129 mm
Height of the front	103 mm
Build in depth	33 mm
Cutout Dimension Width	118.5 mm
Cutout Dimension Height	92.5 mm
Weight	230 g

Classification

ECLASS 8.1	27242301
ETIM 7.0	EC001414
ETIM 6.0	EC001414
ETIM 5.0	EC001414
ETIM 4.0	EC001414




Display

Screen diagonal (Inch)	4.3
Number of pixels, horizontal	480
Number of pixels, vertical	272
Type of display	TFT Colour LCD with LED Backlight

Max. Colors	16 Bit
Backlight Life in Hours	20000
Touch Technology	Resistive touch
CPU Typ	RISC ARM9 32 Bit
Max. main memory	64 MB

Technical data


Operating temperature min.	-10 °C
Operating temperature max.	60 °C
Storage temperature / transport max.	70 °C
Storage temperature / transport min.	-20 °C
relative humidity min.	10 %
relative humidity max.	90 %
Degree of protection (IP)	IP66
Degree of protection (NEMA)	4X
Number of HW-interfaces industrial Ethernet	1
Number of HW-interfaces RS232	1
Number of HW-interfaces RS422	1
Number of HW-interfaces RS485	3
Number of HW-interfaces USB	1
Supporting MODBUS protocol	Yes
Standards	EN61000-6-2, EN61000-6-4
Approvals	Yes
cooling	Natural Cooling with min. 50 mm distance to environment
Shock	50 G, 11 Ms, X, Y, Z Direction (EN 60068-2-27)
EMI	FCC Part 15 Class A
Real Time Clock	Yes
Battery Backed RAM	Yes
Vibration	10...55 Hz (IEC60068-2-64)
UL Certification	UL61010
ROHS Certification	Yes
Ethernet Protocols	ADS for TwinCAT3, Modbus TCP Slave, Modbus TCP Master, Ethernet IP, u.v.a.
Compatible PLC families	Siemens, Allen Bradley, Beckhoff, Wago, Schneider, u.v.a.
Operating Cycles	≥ 1000000
Power Supply Type	SELV (UL 508, UL 248)
Font Type	Taiwanese (traditional Chinese), Japanese (ANK, Kanji), Kyrilic, Korean, Chinese (simp. Chinese), ASCII (Europ front type)



Cutout Dimension



Ansicht unten / view below



Weitere Angaben siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog.				www.wieland-electric.com eshop.wieland-electric.com			
ja/yes <input checked="" type="checkbox"/> Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!							
Freitoleranz nach General tolerance			CAD-Zeichnung, keine manuellen Änderungen CAD drawing, no manual modifications allowed			1. Verwendung: First Use:	Blatt: Sheet:
		Werkstoff / Material		2017	Tag/Date	Name	Zeichnung Nr. / Drawing No.
		Maßstab/Scale		gezeichnet drawn	27.11.	Koetzner	83.050.0000.0 01K
				geprüft checked			Maße in mm / Dimensions are in mm
				Normgepr. Stand. check			
Datei / File: 045611_A01K.DCD				Ersatz für / Replacement for:			
④		13.02.20		Type		Benennung / Title	
Index		Datum / Blatt Date / Sheet		wieland www.wieland-electric.com		Teilespezifikation / Component specification HMI TOUCH PANEL HMI-ECO-043	
		Änderung / Revision					

Qu - PEE 12/92

A
1
2
3
4
5
6
7
8
9
10
11
12
13
14
15
16
17
18
19
20
M1
M2
M3
L
G
i
11.1
12.1
1.1