

Unscreened Multicore Cable to Defence Standard 61-12 Part 4 7-2- *A

multicomp PRO

**RoHS
Compliant**



Description

This unscreened multicore cable is manufactured to Defence Standard 61-12 Part 4 and is designed for high density wiring between components and within instruments and electronic equipment. It is not to be used for the direct connection to Mains Power Supplies.

Reference Standard

Multicore Cable to DEF. STAN. 61-12 part 4. 0.22mm² (7/0.2mm) Conductors, Unscreened with Black PVC Jacket

Cable Construction

Conductor

Electrolytic Annealed Tinned Copper Conductor 7/0.2mm

Nominal Core Resistance @ 20°C : 92Ω/km

Current Rating (per core) : 1 Amp

Insulation and Conductors

Core insulation of PVC to BS676 type 2 Nom. Radial Thickness 0.3mm

Insulation Resistance @ 20°C : Min. 100MΩ×km

Nominal Overall Ø of Conductor : 1.2mm

Conductors Colour Coded as per DEF. STAN. 61-12 Part 4

Test Voltage (1 minute, core to core) : 1000V

Wrap

Cores wrapped with Plastic Tape

Sheath

Black PVC jacket to BS6746 Type 6

Temperature Range : 0°C to + 70°C

Nominal Voltage : 440V AC rms @ 1600Hz

Minimum Bending Radius : 6 x cable Ø

Insulation Colours table

Core Number	Colour
1	Red
2	Blue
3	Green
4	Yellow
5	White
6	Black
7	Brown
8	Violet
9	Orange
10	Pink
11	Turquoise
12	Grey

Core Number	Colour
13	Red/Blue
14	Green/Red
15	Yellow/Red
16	White/Red
17	Red/Black
18	Red/Brown
19	Yellow/Blue
20	White/Blue
21	Blue/Black
22	Orange/Blue
23	Green/Blue
24	Grey/Blue

Core Number	Colour
25	Yellow/Green
26	White/Green
27	Green/Black
28	Orange/Green
29	Grey/Green
30	Yellow/Brown
31	White/Brown
32	Brown/Black
33	Grey/Brown
34	Yellow/Violet
35	Violet/Black
36	White/Violet

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

Unscreened Multicore Cable to Defence Standard 61-12 Part 4 7-2- *A



Part Number Table

Description	No. of Cores	Diameter over Cores (mm)	Jacket Radial Thickness (mm)	Jacket Diameter (mm)	Filler	Reel Length (m)	Part Number	
Cable, Unscreened, DEF 7-2-2A	2	2.4	0.45	3.4	-	25	PP000272	
						100	PP000273	
Cable, Unscreened, DEF 7-2-3A	3	2.6		3.6		-	25	PP000274
							100	PP000275
Cable, Unscreened, DEF 7-2-4A	4	2.9		3.9		-	25	PP000276
							100	PP000277
Cable, Unscreened, DEF 7-2-6A	6	3.6		4.6		1.2 PVC Strip	25	PP000278
							100	PP000279
Cable, Unscreened, DEF 7-2-8A	8	4.1		5.1		1.9 PVC Strip	25	PP000280
							100	PP000281
Cable, Unscreened, DEF 7-2-12A	12	5	0.55	6.1	-	25	PP000282	
						100	PP000283	
Cable, Unscreened, DEF 7-2-18A	18	6	0.65	7.4	1.2 PVC Strip	25	PP000284	
						100	PP000285	
Cable, Unscreened, DEF 7-2-20A	20	6.5		7.8	-	25	PP000286	
						100	PP000287	
Cable, Unscreened, DEF 7-2-25A	25	7.2		8.7	-	25	PP000288	
						100	PP000289	
Cable, Unscreened, DEF 7-2-36A	36	8.4mm		9.8mm	1.2 PVC Strip	100	PP000290	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

