

PRODUCT-DETAILS

UA1-230

UA1-230 Undervoltage Release



General Information

Extended Product Type	UA1-230
Product ID	1SAM201904R1005
EAN	4013614320460
Catalog Description	UA1-230 Undervoltage Release
Long Description	UA1-230 Undervoltage release 230 V 50 Hz / 240 V 60 Hz

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080

Popular Downloads

Data Sheet, Technical Information	1SBC100192C02--
Instructions and Manuals	2CDC131011M6802 2CDC131034M6801 2CDC131022M6802

Dimensions

Product Net Width	18 mm
Product Net Height	90 mm

Product Net Depth / Length	75.5 mm
Product Net Weight	0.1 kg

Technical

Terminal Type	Screw Terminals
Rated Control Supply Voltage (U _s)	(50 Hz) 230 V (60 Hz) 240 V
Rated Impulse Withstand Voltage (U _{imp})	Auxiliary Circuit 6 kV
Rated Insulation Voltage (U _i)	690 V
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1/2x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 1x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 2x 0.75 ... 1.5 mm ² Flexible 1/2x 0.75 ... 2.5 mm ² Rigid 1/2x 1 ... 4 mm ²
Tightening Torque	Auxiliary Circuit 0.8 ... 1.2 N·m
Wire Stripping Length	Auxiliary Circuit 10 mm
Recommended Screw Driver	Pozidriv 2
Standards	CSA 22.2 No. 14 IEC/EN 60947-1 IEC/EN 60947-4-1 UL 508 UL 60947-1 UL 60947-4-1
Product Name	Undervoltage Release
Suitable For	MS116 MS132 MO132 MS165 MO165
Suitable for Product Class	Manual Motor Starter
Accessory Group	Electrical
Accessory Type	Undervoltage Release
Remarks	The mechanical and electrical durability of manual motor starters in combination with UA1/AA1 is reduced. Values are provided on request.

Technical UL/CSA

Connecting Capacity Auxiliary Circuit UL/CSA	Flexible 1/2x 16-12 AWG Stranded 1/2x 16-12 AWG
Tightening Torque UL/CSA	Auxiliary Circuit 7 in·lb

Environmental

Ambient Air Temperature	Operation -25 ... +60 °C Storage -50 ... +80 °C
Resistance to Shock acc. to IEC 60068-2-27	11 ms Pulse 15g
RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

ABS Certificate	1SAA963001-0101
BV Certificate	1SAA963002-0201

cUL Certificate	cUL_E137861
Declaration of Conformity - CE	1SAD938504-0196 1SAD938507-0190 1SAD938504-0198 1SAD938505-0197 1SAD938506-0191 1SAD938507-0188 1SAD938508-0183 1SAD938514-0125 1SAD938521-0060 1SAD938503-0304
DNV GL Certificate	1SAA963001-0304
GOST Certificate	1SAA937000-2703
Instructions and Manuals	2CDC131011M6802 2CDC131034M6801 2CDC131022M6802
LR Certificate	1SAA963001-0502 1SAA918001-0501
RINA Certificate	Rina_MS132
RoHS Information	1SAA963001-4407
UL Certificate	UL_E137861

Container Information

Package Level 1 Width	93 mm
Package Level 1 Depth / Length	25 mm
Package Level 1 Height	80 mm
Package Level 1 Gross Weight	0.11 kg
Package Level 1 EAN	4013614320460
Package Level 1 Units	box 1 piece
Package Level 2 Width	280 mm
Package Level 2 Depth / Length	395 mm
Package Level 2 Height	210 mm
Package Level 2 Gross Weight	9.175 kg
Package Level 2 EAN	4013614526121
Package Level 2 Units	carton 80 piece

Classifications

Object Classification Code	Q
ETIM 4	EC002498 - Accessories for low-voltage switch technology
ETIM 5	EC001022 - Under voltage coil
ETIM 6	EC001022 - Under voltage coil
ETIM 7	EC001022 - Under voltage coil
eClass	7.0 27370417
UNSPSC	39121521
IDEA Granular Category Code (IGCC)	4148 >> Under voltage coil
E-Number (Sweden)	3112029

Categories

Low Voltage Products and Systems → Control Products → Manual Motor Starters → Manual Motor Starters Accessories

