

# PROFET ™+2 12 V Grade0 customer evaluation board

## **Quick start guide**

BTS7004-1EPZ BTS7006-1EPZ, BTS7008-1EPZ, BTS7008-2EPZ, BTS7040-1EPZ, BTS7080-2EPZ

### About this document

#### Scope and purpose

This document provides a quick introduction to the Grade0 PROFET™ +2 12V customer evaluation board, which is designed to handle all devices in the PROFET™ +2 12V Grade0 family.

The intention of the evaluation board is to give the customers a quick start for lab evaluation of the performance to this product family.

Infineon's automotive qualified PROFET™ +2 12V family consists of six different high-side switches (from 4 mOhm to 80 mOhm) and offers an extended junction temperature range up to 175°C that allows partitioning at high ambient temperatures with higher ohmic parts. Furthermore, thanks to the AEC-Q100 Grade0 qualification, the PROFET™+2 12V Grade0 portfolio is able to fulfill extended lifetime at elevated temperatures. The PROFET™+2 12V Grade0 devices are suitable to drive resistive, inductive and/or capacitive loads and are the perfect fit for applications with extended or/and high temperature mission profiles, such as under the hood, powertrain and transmission applications.




Figure 1 Customer evaluation board

#### Intended audience

Customers requiring a quick start guide to the evaluation board.



## Table of contents

## **Table of contents**

	About this document	1
	Table of contents	2
1	Evaluation board description	3
1.1	Basic features	3
1.2	Protection features	
1.3	Diagnostic features	
1.4	Product validation	3
1.5	Set up details	3
2	Board connectors and functions	4
3	Schematic	6
4	Layout	7
5	Revision history	8
	Disclaimer	9



#### 1 Evaluation board description

# 1 Evaluation board description

#### 1.1 Basic features

- High-side switch with diagnosis and embedded protection
- Part of PROFET<sup>™</sup>+2 12V family
- ReverseON for low power dissipation in reverse polarity
- Green product (RoHS compliant)

#### 1.2 Protection features

- Absolute and dynamic temperature limitation with controlled reactivation
- Overcurrent protection (tripping) with Intelligent Latch or Intelligent Restart Control
- Undervoltage shutdown
- Overvoltage protection with external components
- Maximum temperature for board and device: 175 °C

## 1.3 Diagnostic features

- Proportional load current sense
- Open load in ON and OFF state
- Short circuit to ground and battery

#### 1.4 Product validation

Qualified for automotive applications. Product validation according to AEC-Q100 Grade0.

### 1.5 Set up details

- Jumper JP\_GND must be set
- A DC power supply (typically 12 V) needs to be connected to VS
- A load (for example, a bulb or a power resistor) can be connected to OUT0 or OUT1
- To enable the device a 3.3 V or 5 V signal, such as the digital output of a microcontroller or signal generator for example, needs to be available to INO and/or IN1 and DEN, respectively
- The ground reference of the digital enable signal (MGND contact), the negative load contact, and the negative/GND output of the DC power supply have to be connected together

The voltage at IS can be measured with a voltmeter. If IN=DEN=high, the load current can be calculated with this formula: I\_load = voltage(IS) x kILIS / 1.2 k $\Omega$ 



### 2 Board connectors and functions

#### **Board connectors and functions** 2

#### Table 1 **Evaluation board connectors and functions**

Connector	Function		
INO	<ul> <li>Input signal for channel 0 of IC1</li> <li>3.3 V or 5 V logical input</li> <li>Turns the device ON/OFF and resets the fault if triggered</li> </ul>		
DEN	<ul> <li>Sense enable signal of IC1</li> <li>3.3 V or 5 V logical input</li> <li>Turns measurements signalized at the IS pin ON/OFF and resets the fault if triggered</li> </ul>		
DSEL	<ul> <li>Diagnostic select signal</li> <li>3.3 V or 5 V logical input</li> <li>Selects the channel which has to be diagnosed</li> </ul>		
IN1	<ul> <li>Input signal for channel 1 of IC1</li> <li>3.3 V or 5 V logical input</li> <li>Turns the device ON/OFF and resets the fault if triggered</li> </ul>		
IS	Sense output of IC1		
OUT0	<ul> <li>Output0 of IC1</li> <li>Connects a grounded load to this pin, such as a power resistor, 12 V heating elements, or a glow plug for example</li> </ul>		
OUT1	<ul> <li>Output1 of IC1</li> <li>Connects a grounded load to this pin, such as a power resistor, 12 V heating elements, or a glow plug for example</li> </ul>		
VS	Supply pin  Connects the positive supply voltage (4.1 V 28 V, typical 12 V DC) to this pin		
MGND	<ul><li>Ground pin</li><li>Connection for the module X_GND to the device GND</li></ul>		
JP_GND	Ground resistor • Closes the jumper to use the 47 Ω default sense resistor		
JP_OUT	<ul> <li>Output connection</li> <li>Closes the jumper to increase the current capabilities performances in case of a single channel device</li> </ul>		

#### Table 2 **Component values**

Component name	Value	Description
C_VSGND	47 nF	High Operating Temperature Radial Leaded Multilayer Ceramic Capacitor



## 2 Board connectors and functions

### Table 2 Component values (continued)

Component name	Value	Description
R_ADC, R_DEN, R_DSEL, R_IN0, R_IN1, R_IS_PROT	4.7 k	Metal thin film chip resistor
R_SENSE1	1.21 k	Metal thin film chip resistor
C_VS	68 nF	MLCC RHS series Used for Automotive Electronic Equipment
C_SENSE	220 pF	SMD Industrial Ceramic, High Temperature, Ultra- Stable,Low Loss, 0402
R_GND	49.9 R	Thick film chip resistor
C_OUT0, C_OUT1	10 nF	Ultra-Stable, Low Loss, Multi-layer Ceramic Capacitor
D_Z1	V <sub>Z</sub> = 6.2 V	Zener diode with Surge Current



3 Schematic

#### Schematic 3




Figure 2 Schematic of PROFET™+2 12V Grade0 customer evaluation board



4 Layout

# 4 Layout




Figure 3 Top layout




Figure 4 Bottom layout



5 Revision history

# 5 Revision history

## Table 3 Revision history

<b>Document version</b>	Date of release	Description of changes
Rev. 0.01	2020-04-09	User manual creation

#### Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2020-04-09 Published by Infineon Technologies AG 81726 Munich, Germany

© 2020 Infineon Technologies AG All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference IFX-bvi1584088624509

#### IMPORTANT NOTICE

The information contained in this application note is given as a hint for the implementation of the product only and shall in no event be regarded as a description or warranty of a certain functionality, condition or quality of the product. Before implementation of the product, the recipient of this application note must verify any function and other technical information given herein in the real application. Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind (including without limitation warranties of non-infringement of intellectual property rights of any third party) with respect to any and all information given in this application note.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

#### WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury