

THERMOSTATS

* * * * T23 SPECIFICATION(1) (S P S T) * * * *

Operation Temperature : One Fixed Point In The Range Of 50 °C To 205 °C

Temperature Tolerance : Operating Temperature ± 5 °C (± 3 °C Available
Or Appointed Temperature Tolerance By Customers.)
Reset Temperature ± 6 °C (± 4 °C Available Or
Appointed Temperature Tolerance By Customers)

Differential(Difference Between On Point And Off Point)
: Normal 10 °C — 30 °C

Heat Resistivity : 240 °C

* * * * * ELECTRICAL * * * * *

Electrical Rating : 15A 125V AC (Resistive Load)
10A 250V AC (Resistive Load)
15A 250V AC (Resistive Load)

Contact Resistance : 50m Ω Or Less

Dielectric Strength : AC 1000V For One Minutes Or More Between
Non-Live Metal Parts And Terminals

Insulation Resistance : 100M Ω Or More Between The Non-Live Metal
Parts And Terminals.

Operating Life : 100K Cycles (Class II VDE)
10K Cycles (15A 250V AC estimated life)