

Type TLRS Series


Key Features

Three Sizes

Power ratings
to 7W

Resistance
value from
0.2mΩ~5mΩ

Electron beam
welding,
stable
performance



Applications

Current
sensors for
Hybrid power
sources

Frequency
convertors

High Current
Handling for
Automotive
Engine
Controls and
Power
Management

TE Connectivity is pleased to offer this Low Ohmic Surface Mount Shunt Resistor. Featuring Heavy Copper connectors, electron beam welded to a Manganin or NiCr alloy element, this resistor offers excellent long term stability and low inductance, and can be mounted using re-flow soldering techniques or welding on copper.

Characteristics – Electrical


Type	Power Rating (W)	Resistance Range (mΩ)		TCR (PPM/°C)
		±1%	±5%	
TLRS0630	2.5	4		±100
	3	0.3, 0.5, 0.9, 1		±50
	3	2, 3		±100
TLRS1050	2	5		±100
	2.5	4		±100
	3	3		±100
	4	1		±60
	4	2		±100
	4	0.5		±75
TLRS1575	5	0.2, 0.3		±75
	3	5		±100
	3.5	3		±100
	4	2		±100
	6	0.5, 1		±100
	6	0.4		±50
	7	0.2		±50

Environmental Characteristics

Item	Requirement	Test Methods
Short time Overload	$\Delta R \leq \pm 0.5\%R$	Rated Power $\times 5$ for 5 seconds
Load Life	$\Delta R \leq \pm 1.0\%R$	70°C Rated Power for 1000 Hours
Resistance to Soldering Heat	$\Delta R \leq \pm 0.5\%R$	260°C for 10 \pm 1 seconds
Thermal Shock	$\Delta R \leq \pm 0.5\%R$	-55°C/175°C, 30min, 5 cycles
Moisture Resistance	$\Delta R \leq \pm 1.0\%R$	-55°C, 93 \pm 3%RH, 56 days
High Temperature Exposure	$\Delta R \leq \pm 1.0\%R$	175°C for 1000 hours
Vibration	$\Delta R \leq \pm 0.5\%R$	10~200Hz, 98m/S ² , 6 hours

Storage Temperature: 15 ~28 °C; Humidity < 80%RH


Construction and Dimensions:




Type	Resistance (mΩ)	Material	A ±0.3 (mm)	B ±0.3 (mm)	C ±0.3 (mm)	D ±0.3 (mm)	E nom (mm)	H1 nom (mm)	H2 nom (mm)
TLRS0630	0.3	Manganin	6.35	3.05	1.14	3.0	0.35	0.95	0.95
	0.5	Manganin	6.35	3.05	1.14	3.0	0.35	0.89	0.89
	0.9	Manganin	6.35	3.05	1.14	3.0	0.35	0.50	0.50
	1	Manganin	6.35	3.05	1.14	3.0	0.35	0.42	0.42
	2	Manganin	6.35	3.05	1.14	3.0	0.35	0.72	0.62
	3	NiCr alloy	6.35	3.05	1.14	3.0	0.35	0.48	0.42
TLRS1050	0.2, 0.3	Manganin	10.5	5.0	2.0	5.0	0.50	1.42	1.42
	0.5	Manganin	10.5	5.0	2.0	5.0	0.50	0.76	0.88
	1	Manganin	10.5	5.0	2.0	5.0	0.50	0.38	0.43
	2	NiCr alloy	10.5	5.0	2.0	5.0	0.50	0.69	0.64
	3	NiCr alloy	10.5	5.0	2.0	5.0	0.50	0.43	0.43
	4	NiCr alloy	10.5	5.0	2.0	5.0	0.50	0.32	0.32
TLRS1575	0.2	Manganin	15.2	7.5	4.0	5.0	0.50	1.42	1.42
	0.4	Manganin	15.2	7.5	4.0	5.0	0.50	0.76	0.74
	0.5	Manganin	15.2	7.5	4.0	5.0	0.50	0.56	0.56
	1	Manganin	15.2	7.5	4.0	5.0	0.50	0.84	0.84
	2	NiCr alloy	15.2	7.5	4.0	5.0	0.50	0.40	0.40
	3	NiCr alloy	15.2	7.5	4.0	5.0	0.50	0.27	0.27
5	NiCr alloy	15.2	7.5	4.0	5.0	0.50	0.20	0.20	

Derating Curve


TLRS0630 / 1050



TLRS1575




Pulse Energy




Packaging

Reel Dimensions (mm)



Type	Quantity	Tape Width (mm)	Reel Diameter (inch)	ØA ±1.0 (mm)	ØB ±0.5 (mm)	ØC +0.3/-0.2 (mm)	W ±0.5 (mm)
TLRS0630	5K	16	13	330.5	99.5	13.2	17.4
TLRS1050	3K	24	13	330.5	99.5	13.2	25.4
TLRS1575	2K	24	13	330.5	99.5	13.2	25.4

Tape Specifications – Embossed Plastic



Type	A ±0.1 (mm)	B ±0.1 (mm)	W ±0.3 (mm)	E ±0.1 (mm)	F ±0.15 (mm)	P ₀ ±0.1 (mm)	P ₁ ±0.1 (mm)	P ₂ (mm)	ØD ₀ +0.1 -0 (mm)	T ±0.1 (mm)
0630	3.5	6.8	16.0	1.75	7.5	4.0	8.0	2.0	1.5	1.45
1050	5.7	11.2	24.0	1.75	11.5	4.0	8.0	2.0	1.5	2.05
1575	8.2	15.9	24.0	1.75	11.5	4.0	12.0	2.0	1.5	2.05

How To Order

TLRS1050	40	E	R002	F	TDG
Common Part	Power Rating	TCR	Resistance Code	Tolerance Code	Packaging
TLRS0630 TLRS1050 TLRS1575	25 – 2.5W 30 – 3W 35 – 3.5W 40 – 4W 50 – 5W Etc.	D - ±50PPM P - ±60PPM W - ±75PPM E - ±100PPM	R0002 – 0.2mΩ R001 – 1mΩ	F - ±1% J - ±5%	TDG – Standard Tape and Reel Quantity as above chart