

HARDCASE® PROFESSIONAL® PROJECTPLUS

HCHH41

For the most demanding tasks, look no further than the *Energizer® HARDCASE® PROFESSIONAL® PROJECTPLUS*. With tool-quality construction and advanced LED technology, this light is designed to meet even the most challenging jobs. Constructed with Professionals in mind, it withstands drop after drop, off a ladder or even a two story building. Featuring bright, uniform light with an extended beam distance, this light is built to provide a great combination of brightness and long runtime. The large push button switch and ergonomic handle allow for easy operation even with gloves, while adjustable light modes let the user decide the exact balance of brightness and runtime. In addition, this light is water resistant for user confidence even during extreme, outdoor tasks.



Provides 400 Lumens of Light




Provides Run Time of 11 hours



Illuminates objects up to 125m away



Sustains 7 Meter Drop Test



Water Resistant IPX4 – works after splashing water on all sides

DESIGN BENEFITS

- ✓ Exceptionally durable
- ✓ Survives drop after drop from a two-story building
- ✓ Weather-resistant
- ✓ Shatterproof lens
- ✓ Built-in lanyard slot
- ✓ Large switch for easy operation
- ✓ 20 Year Designed To Last based on typical consumer usage patterns

LIGHT AND POWER SOURCE

- ✓ Features Advanced LED Technology
- ✓ Operates on 4 AA batteries

ELECTRICAL CHARACTERISTICS

Electrical Characteristics Nominal Power:
 Power consumption xxxW / Battery Energizer E91 xxxV dc
 LED Specifications: LED 3.0V cc / xxx mA

CERTIFICATES AND COMPLIANCE



EMC, EN62471, FCC



This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Tested according to ANSI/NEMA FL1 Standards

Results based on: Energizer® MAX, Alkaline / E91

PERFORMANCE BENEFITS

- ✓ Bright, uniform light with extended beam distance
- ✓ Adjustable beam for customized light output and extended runtime up to 50h
- ✓ Excellent delivery of both Spot and Flood lighting

SPECIFICATIONS

Weight Excluding Batteries:

210 grams / 7.4 ounces

Dimensions:

215mm x 45mm x 55mm / 8.5" x 1.75" x 2.25"

NUMBER OF OPERATING MODES: 3

Mode	Lumens (lm)	Runtime (h)	Beam Distance (m)
Spot & Flood-High	400	11	125
Flood-Low	300	14	NA
Lowest Dimming	40	50	NA