


**ELECTRICAL TEST:**



- 1.100% OPEN SHORT MIS WIRE TEST
- 2.CONTACT RESISTANCE:5 OHM MAX
- 3.INSULATION RESISTANCE:5M OHM MIN
- 4.HI-POT TEST:DC 300V/10ms
- 5.PASS 8K@60Hz ( 7680\*4320 ) /48Gbps TEST

CONSUMER ITEM	LENGTH(mm)
3.0M	3000±30



**PIN Assignment**

**P1 HDMI AM      P2 HDMI AM**



⑤	CABLE	28-30#(1/0.32BC*1P+1/0.254TC+AL-Foil+ADHESIVE-PET)*5C+1/0.254BC*4C+AL-Foil+1/0.254TC+160#/0.12AL BLACK PVC Jacket OD:7.3±0.15	m
④	MODEL	Black 45P PVC	xxg
③	MODEL	PE,Nature color	xxg
②	Copper foil	Copper foil size:5mm	cm
①	plug	HDMI AM 19P SHELL/PIN: Gold plated three-pieces	2pcs
NO.	PART NAME	DESCRIPTION	UNIT

				DESCRIPTION	FINISHED PRODUCT'S FIGURE	SCALE	FIT	UNITS: MM	1RD ANGLE
				MODEL NO.		△			
APPROVED	CHECKED	DRAWING	DESIGNED	DRAWING NO.		△			
		HENRY	L.H.R	FINISHING		△	2020/01/10		A1
				MATERIAL		SYM	DATE		REVISION