


ELECTRICAL TEST:



- 1.100% OPEN SHORT MIS WIRE TEST
- 2.CONTACT RESISTANCE:5 OHM MAX
- 3.INSULATION RESISTANCE:5M OHM MIN
- 4.HI-POT TEST:DC 300V/10ms
- 5.PASS 8K@60Hz (7680*4320) /48Gbps TEST

CONSUMER ITEM	LENGTH(mm)
0.5M	500±20
1.0M	1000±30
1.5M	1500±30
2.0M	2000±30



PIN Assignment

P1 HDMI AM P2 HDMI AM



⑤	CABLE	30#(1/0.254BC*1P+1/0.254TC+AL-Foil+ADHESIVE-PET)*5C+1/0.254BC*4C+AL-Foil+1/0.254TC+144#/0.12AL BLACK Soft PVC Jacket OD:6.3±0.15	m
④	MODEL	Black 45P PVC	xxg
③	MODEL	PE,Nature color	xxg
③	shell	Black Gun Zinc alloy shell	PCS
②	Copper foil	Copper foil size:5mm	cm
①	plug	HDMI AM 19P SHELL/PIN:Gold plated three-pieces	2pcs
NO.	PART NAME	DESCRIPTION	UNIT

				DESCRIPTION	FINISHED PRODUCT'S FIGURE	SCALE	FIT	UNITS: MM	1RD ANGLE
				MODEL NO.		△			
APPROVED	CHECKED	DRAWING	DESIGNED	DRAWING NO.		△			
		HENRY	L.H.R	FINISHING		△	2020/01/10		A1
				MATERIAL		SYM	DATE		REVISION