

300 Mbps Whole Home Mesh Wi-Fi System

Model: Halo S3

// Highlights


- One Unified Network – Run a single home network with one Wi-Fi name and password
- Seamless Roaming – Choose the best signal and enjoy the best connections for all your devices
- Connects over 40 Devices – Enjoy lag-free connection and non-stop entertainment on all your devices
- IPTV Compatible – Enjoy multimedia services as you want
- 300Mbps Wireless Speed - Ideal for HD streaming, online gaming, and large file downloads



// Applications



Ideal for large homes with multiple rooms and multiple users



Ideal for average internet users seeking fast downloads, seamless streaming audio, uninterrupted streaming video, and lag-free online gaming

// Features



Speed

Wireless Speed – Wireless speed of up to 300 Mbps



Range

Internal omni-directional antennas provide great wireless coverage

Mesh Wi-Fi system extends Wi-Fi range to every corner of your home, covering up to 2,200 square feet.



Easy Setup

Quick Installation – Intuitive webpage supports quick, hassle free installation




Security

Guest Network – Creates a separate network for your guests to ensure safety

Parental Controls – Parents can establish appropriate access policies for children devices

// Whole Home Mesh Wi-Fi System

Halo S3 works as a unified system to guarantee a strong Wi-Fi signal in every corner of your home. Mercusys Mesh Technology provides an incredibly fast and stable usage experience when you walk around your home. Interruption and buffering will be a thing of the past.



Seamless Roaming

Intelligently connects devices to the Halo with the strongest signal and highest capacity. No more sudden signal drops or lagging Wi-Fi when you're roaming at home.

Self-Healing

If one AP node drops in a multi-node mesh network, the system will reconfigure automatically based on the other nodes. Data connectivity is always maintained and there is no interruption experience at all.

Connects over 40 devices

Smart home devices, gaming, 4K streaming, and AR/VR all compete for network resources, Halo S3 can provide fast connections for over 40 devices, keeping all your devices connected.

// Specifications

Physical Specifications

Ports

2 10/100 Mbps ports per Halo unit
(WAN/LAN auto-sensing)

Button

Pair button, Reset button

External Power Supply

9V/0.6A

Dimensions (W x D x H)

3.5 × 3.5 × 3.5 in (88 × 88 × 88 mm)

Package Contents(2-pack)

- 2× Halo S3 Units
- 1× RJ45 Ethernet Cable
- 2× Power Adapters
- 1× Quick Installation Guide

Package Contents(3-pack)

- 3× Halo S3 Units
- 1× RJ45 Ethernet Cable
- 3× Power Adapters
- 1× Quick Installation Guide

Wireless Specifications

Wireless Standards

IEEE 802.11b/g/n

Frequency

2.4 - 2.5 GHz

Mesh protocol

802.11k/v

Signal Rate

300 Mbps on 2.4 GHz

Transmit Power

<20dBm (EIRP)

Reception Sensitivity

- 11g 6M: -95dBm
- 11g 54M: -77dBm
- 11n 20M MCS7: -75dBm
- 11n 40M MCS7: -72dBm

Wireless Function

Enable/Disable Wireless Radio, Wireless Statistics

Wireless Security

WPA2-PSK + AES

Operation Specifications

WAN Type

Dynamic IP/Static IP/PPPoE/PPTP/L2TP

DHCP

Server, Address Reservation, DHCP Client List

Port Forwarding

Virtual Server, UPnP, DMZ, Port Triggering

Management

Access Control
Local Management
Remote Management

Protocols

IPv4, IPv6

Guest Network

2.4 GHz Guest Network

Environment

- Operating Temperature: 0°C~40°C (32°F~104°F)
- Storage Temperature: -40°C~70°C (-40°F~158°F)
- Operating Humidity: 10%~90% Non-Condensing
- Storage Humidity: 5%~90% Non-Condensing

Specifications are subject to change without notice. MERCUSYS is a registered trademark of MERCUSYS TECHNOLOGIES CO., LTD. Other brands and product names are trademarks or registered trademarks of their respective holders. Copyright © 2019 MERCUSYS TECHNOLOGIES CO., LTD. All rights reserved.

* Maximum wireless signal rates are the physical rates derived from IEEE Standard 802.11 specifications. Actual wireless data throughput and wireless coverage are not guaranteed and will vary as a result of 1) environmental factors, including building materials, physical objects, and obstacles, 2) network conditions, including local interference, volume and density of traffic, product location, network complexity, and network overhead, and 3) client limitations, including rated performance, location, connection, quality, and client condition.