4 Channel Programmable Linear Power Supplies



RoHS Compliant



Description

These four-channel DC power supplies can provide pure linear output of 4 isolated channels with features such as stability, free interference, low ripple and low noise. And the power supplies have four-channel cooperative output characteristics, which can realize multi-channel various sequence wave output and complete complex test requirements. Moreover, the output voltage and current can be observed through the oscilloscope of the LCD, and the test data can be directly imported and exported through the U disk.

Features

- · 4-channel independent output
- 4-channel high-speed coordinated output, and each channel can be individually controlled with 4-channel output delays as low as microseconds
- · LIST programmable output sequence, 100 consecutive different settings
- LIST mode and normal mode can be switched automatically with One Key
- · Oscilloscope function for simultaneous display of four channels of voltage and current
- Oscilloscope screen capture via USB access to U disk
- U disk import and export output table data, and you can edit it by computer EXCEL
- Low chopping and low noise
- · High resolution and precision
- Remote measurement function
- Built-in USB/RS232/GPIB/LAN communication interfaces

Specifications

Note: The specifications below are tested under the conditions of temperature 25°C ±5°C and the warm-up for 10 minutes.

Models	MP710508	MP710509		
Voltage	0 to 30V × 4	0 to 60V × 4		
Current	0 to 5A × 4	0 to 3A × 4		
Load Regulation				
Voltage	≤1mv	≤1mv		
Current	≤1mA	≤1mA		
Line Regulation				
Voltage	≤0.01%+1mv	≤0.01%+1mv		
Current	≤0.1%+1mA	≤0.1%+1mA		

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



4 Channel Programmable Linear Power Supplies



Setup Resolution				
Voltage	1mV	1mV		
Current	0.1mA	0.1mA		
Read Back Resolution				
Voltage	1mV	1mV		
Current	0.1mA	0.1mA		
Setup Accuracy (25°C ±5°C)				
Voltage	≤0.005% +2mV	≤0.005% +2mV		
Current	≤0.05% +1mA	≤0.05% +1mA		
Ripple(20-20M)				
Voltage	≤1mVrms	≤1mVrms		
Current	≤3mArms	≤3mArms		
Temp. Coefficient				
Voltage	≤100ppm	≤100ppm		
Current	≤100ppm	≤100ppm		
Read Back Temp. Coefficient				
Voltage	≤100ppm	≤100ppm		
Current	≤100ppm	≤100ppm		
Weight and Dimension: 430mm(W) × 88mm(H) × 440mm(D), 16.5Kg				
Input Supply Voltage : 115V/230V, 50Hz/60Hz				

Accessories

UK/EU Power Cord, User Manual, USB cable, RS232 cable and LAN cable

Standard Warranty: 12 Months

Part Number Table

Description	Part Number
Programmable Linear Power Supply, 4 Channel, 0V to 30V, 5A	MP710508
Programmable Linear Power Supply, 4 Channel, 0V to 60V, 3A	MP710509

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

