Slide Type DIP Switch - MCDHN Series **Half Pitch**

multicomp PRO



Electrical Specifications


Contact Arrangement	: SPST	
No. of Poles	: 2, 3, 4, 6, 8, 10 Pole	
Contact Rating	: 25mA, 24VDC	
Contact Resistance	: 100mΩ Max.	
Insulation Resistance	: 100MΩ Min. 500V D	
Dielectric Strength	: 300V AC/1 minute	
Operating Force	: 500gf max.	
Travel	: 0.6mm	
Operating Life	1,000 cycles	
Operating Temperature	: -40°C to +85°C	
Storage Temperature	: -40°C to +85°C	

Features


DC


- Low profile 1.6mm height
- Gold contact for high reliability
- Top tape type for washing process

CIRCUIT









Dimensions : Millimetres

Part Number Table

Description		Part Number
DIP Switch, Half-Pitch, Top Tape Sealed, Flush Slide, 2Pole, SPST, Black/White, SMD	3.77mm	MCDHN-02F-T-V
DIP Switch, Half-Pitch, Flush Slide, 2Pole, SPST, Black/White, SMD	3.7711111	MCDHN-02F-V
DIP Switch, Half-Pitch, Top Tape Sealed, Flush Slide, 4Pole, SPST, Black/White, SMD	6.21mm	MCDHN-04F-T-V
DIP Switch, Half-Pitch, Flush Slide, 4Pole, SPST, Black/White, SMD	h Slide, 4Pole, SPST, Black/White, SMD 6.31mm	
DIP Switch, Half-Pitch, Top Tape Sealed, Flush Slide, 6Pole, SPST, Black/White, SMD	8.85mm	MCDHN-06F-T-V
DIP Switch, Half-Pitch, Top Tape Sealed, Flush Slide, 8Pole, SPST, Black/White, SMD	11.39mm	MCDHN-08F-T-V
DIP Switch, Half-Pitch, Flush Slide, 8Pole, SPST, Black/White, SMD	11.59000	MCDHN-08F-V
DIP Switch, Half-Pitch, Top Tape Sealed, Flush Slide, 10Pole, SPST, Black/White, SMD	12.02mm	MCDHN-10F-T-V
DIP Switch, Half-Pitch, Flush Slide, 10Pole, SPST, Black/White, SMD	13.93mm	MCDHN-10F-V

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

