

# WIMA MP 3-Y2 / 3R-Y2



**Metallized Paper (MP) RFI-Capacitors Class Y2  
in PCM 10 mm to 27.5 mm. Capacitances from 1000 pF to 0.1 µF.  
Rated Voltages 250 VAC and 300 VAC.**

## Special Features

- Particularly high reliability against active and passive flammability
- Excellent self-healing as well as high voltage strength
- Twice the safety by internal series connection (300 VAC)
- High degree of interference suppression due to good attenuation and low ESR
- For temperatures up to +110° C
- According to RoHS 2011/65/EU

## Typical Applications

**Class Y2 RFI applications to meet EMC regulations**

- Capacitors connected to the mains between phase or neutral and earthed casing
- By-passing of the basic or supplementary insulation, pulse peak voltage ≤ 5 kV

## Construction

### Dielectric:

Paper, epoxy resin impregnated

### Capacitor electrodes:

Vacuum-deposited

### Internal construction:



### Encapsulation:

Self-extinguishing epoxy resin, UL 94 V-0, metal foil

### Terminations:

Tinned wire.

### Marking:

Marking: Black on Silver.

## Electrical Data

### Capacitance range:

1000 pF to 0.1 µF (E12-values on request)

### Rated voltages:

250 VAC, 300 VAC

### Continuous DC voltage\* (general guide):

250 VAC: ≤ 1000 V

300 VAC: ≤ 1250 V

### Capacitance tolerances: ±20%

### Operating temperature range:

-40° C to +110° C

### Climatic test category:

250 VAC: 40/110/56/C

300 VAC: 40/110/56/B

in accordance with IEC

### Insulation resistance at +20° C:

≥ 12 x 10<sup>3</sup> MΩ

Measuring voltage: 100 V/1 min.

### Dissipation factors:

tan δ ≤ 13 x 10<sup>-3</sup> at 1 kHz and +20° C

### Test specifications:

in accordance with IEC 60384-14

### Approvals:

Authority	Specification	Symbol	Approval-No.
UL/Demko	EN 60384-14		ENEC-02833 (250 VAC) ENEC-02399 (300 VAC)
UL	UL 60384-14 CAN/CSA-E60384-14		E 100438

### Maximum pulse rise time 250 VAC:

Capacitance pF/µF	Pulse rise time V/µsec max. operation
1000 ... 4700	2500
6800 ... 0.022	1750

### Maximum pulse rise time 300 VAC:

Capacitance pF/µF	Pulse rise time V/µsec max. operation
1000 ... 4700	2500
6800 ... 0.015	1850
0.022 ... 0.1	600

for pulses equal to a voltage amplitude with  $\sqrt{2} \times 250 \text{ VAC} = 355 \text{ V}$   
with  $\sqrt{2} \times 300 \text{ VAC} = 425 \text{ V}$   
according to IEC 60384-14

**Test voltage:** 2400 VDC, 2sec.

### Reliability:

Operational life > 300 000 hours

Failure rate < 1 fit (0.5 x U<sub>r</sub> and 40° C)

## Mechanical Tests

**Pull test on pins:** 10 N in direction of pins according to IEC 60068-2-21

**Vibration:** 6 hours at 10 ... 2000 Hz and 0.75 mm displacement amplitude or 10 g in accordance with IEC 60068-2-6

**Low air density:** 1kPa = 10 mbar in accordance with IEC 60068-2-13

**Bump test:** 4000 bumps at 390 m/sec<sup>2</sup> in accordance with IEC 60068-2-29

\* If safety-approved EMI suppression capacitors are operated with a DC voltage being above the specified AC voltage rating the given approvals are no longer valid (IEC 60384-14).

Furthermore the permissible pulse rise time du/dt (F<sub>max.</sub>) will be subject to a reduction according to

$$F_{\text{max.}} = F_r \times \sqrt{2} \times \text{UAC} / \text{UDC}$$

if the DC operating voltage UDC is higher than  $\sqrt{2} \times \text{UAC}$

## Packing

Available taped and reeled.

Detailed taping information and graphs at the end of the catalogue.

For further details and graphs please refer to Technical Information.

## Continuation

### General Data

Capacitance	250 VAC*					300 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
1000 pF	4	8.5	13.5	10	MPY20W1100FA00_____	5	13	19	15	MPLY2W1100FC00_____
1500 „	4	8.5	13.5	10	MPY20W1150FA00_____	5	13	19	15	MPLY2W1150FC00_____
2200 „	4	8.5	13.5	10	MPY20W1220FA00_____	5	13	19	15	MPLY2W1220FC00_____
3300 „	4	8.5	13.5	10	MPY20W1330FA00_____	5	13	19	15	MPLY2W1330FC00_____
4700 „	5	10	13.5	10	MPY20W1470FB00_____	6	14	19	15	MPLY2W1470FD00_____
6800 „	5	13	19	15	MPY20W1680FC00_____	7	15	19	15	MPLY2W1680FE00_____
0.01 µF	5	13	19	15	MPY20W2100FC00_____	8	17	19	15	MPLY2W2100FF00_____
0.015 „	6	14	19	15	MPY20W2150FD00_____	10	18	19	15	MPLY2W2150FG00_____
0.022 „	7	15	19	15	MPY20W2220FE00_____	8	20	28	22.5	MPLY2W2220FH00_____
0.033 „						8	20	28	22.5	MPLY2W2330FH00_____
0.047 „						10	22	28	22.5	MPLY2W2470FI00_____
0.068 „						12	24	28	22.5	MPLY2W2680FJ00_____
0.1 µF						13	25	33	27.5	MPLY2W3100FK00_____

\* f = 50/60 Hz

\*\* PCM = Printed circuit module = pin spacing

Upon request with long pins 35-2 mm max.

Dims. in mm.

d = 0.6 ø if PCM 10  
d = 0.8 ø if PCM ≥ 15




Part number completion:

Tolerance: 20 % = M

Packing: bulk = S

Pin length: 6-2 = SD

Taped version see page 149.



Impedance change with frequency (general guide)



Impedance change with frequency (general guide)

Rights reserved to amend design data without prior notification.

## Recommendation for Processing and Application of Through-Hole Capacitors

### Soldering Process

Internal temperature of the capacitor must be kept as follows:

Polyester: preheating:  $T_{max.} \leq 125^{\circ}C$   
soldering:  $T_{max.} \leq 135^{\circ}C$

Polypropylene: preheating:  $T_{max.} \leq 100^{\circ}C$   
soldering:  $T_{max.} \leq 110^{\circ}C$

### Single wave soldering

Soldering bath temperature:  $T < 260^{\circ}C$   
Dwell time:  $t < 5 \text{ sec}$

### Double wave soldering

Soldering bath temperature:  $T < 260^{\circ}C$   
Dwell time:  $\Sigma t < 5 \text{ sec}$

Due to different soldering processes and heat requirements the graphs are to be regarded as a recommendation only.



## WIMA Quality and Environmental Philosophy

### ISO 9001:2015 Certification

ISO 9001:2015 is an international basic standard of quality assurance systems for all branches of industry. The approval according to ISO 9001:2015 of our factories by the infaz (Institut für Auditierung und Zertifizierung) certifies that organisation, equipment and monitoring of quality assurance in our factories correspond to internationally recognized standards.

### WIMA WPCS

The WIMA Process Control System (WPCS) is a quality surveillance and optimization system developed by WIMA. WPCS is a major part of the quality-oriented WIMA production. Points of application during production process:

- incoming material inspection
- metallization
- film inspection
- schoopage
- pre-healing
- pin attachment
- cast resin preparation/encapsulation
- 100% final inspection
- Testing as per customer requirements

### WIMA Environmental Policy

All WIMA capacitors, irrespective of whether through-hole devices or SMD, are made of environmentally friendly materials. Neither during manufacture nor in the product itself any toxic substances are used, e.g.

- Lead
- PCB
- CFC
- Hydrocarbon chloride
- Chromium 6+
- PBB/PBDE
- Arsenic
- Cadmium
- Mercury
- etc.

We merely use pure, recyclable materials for packing our components, such as:

- carton
- cardboard
- adhesive tape made of paper
- polystyrene

We almost completely refrain from using packing materials such as:

- adhesive tapes made of plastic
- metal clips

### RoHS Compliance

According to the RoHS Directive 2011/65/EU as amended from time to time certain hazardous substances like e.g. lead, cadmium, mercury must not be used any longer in electronic equipment as of July 1st, 2006. For the sake of the environment WIMA has refrained from using such substances since years already.



WIMA Kondensatoren sind bleifrei konform RoHS 2011/65/EU

WIMA capacitors are lead free in accordance with RoHS 2011/65/EU

Tape for lead-free WIMA capacitors

### DIN EN ISO 14001:2004

WIMA's environmental management has been established in accordance with the guidelines of DIN EN ISO 14001:2004 to optimize the production processes with regard to energy and resources.

# Typical Dimensions for Taping Configuration




Diagram 1:  
PCM 2.5/5/7.5mm

Diagram 2: PCM 10/15 mm

Diagram 3: PCM 22.5 and 27.5\*mm

\*PCM 27.5 taping possible with two feed holes between components

Designation	Symbol	Dimensions for Radial Taping						
		PCM 2.5 taping	PCM 5 taping	PCM 7.5 taping	PCM 10 taping*	PCM 15 taping*	PCM 22.5 taping	PCM 27.5 taping
Carrier tape width	W	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5
Hold-down tape width	W <sub>0</sub>	6.0 for hot-sealing adhesive tape	6.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape
Hole position	W <sub>1</sub>	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5
Hold-down tape position	W <sub>2</sub>	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.
Feed hole diameter	D <sub>0</sub>	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2
Pitch of component	P	12.7 ±1.0	12.7 ±1.0	12.7 ±1.0	25.4 ±1.0	25.4 ±1.0	38.1 ±1.5	38.1 ±1.5 or 50.8 ±1.5
Feed hole pitch	P <sub>0</sub>	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch
Feed hole centre to pin	P <sub>1</sub>	5.1 ±0.5	3.85 ±0.7	2.6 ±0.7	7.7 ±0.7	5.2 ±0.7	7.8 ±0.7	5.3 ±0.7
Hole centre to component centre	P <sub>2</sub>	6.35 ±1.3	6.35 ±1.3	6.35 ±1.3	12.7 ±1.3	12.7 ±1.3	19.05 ±1.3	19.05 ±1.3
Feed hole centre to bottom edge of the component	H	16.5 ±0.3 18.5 ±0.5	16.5 ±0.3 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5
Feed hole centre to top edge of the component	H <sub>1</sub>	H+H <sub>component</sub> < H <sub>1</sub> 32.25 max.	H+H <sub>component</sub> < H <sub>1</sub> 32.25 max.	H+H <sub>component</sub> < H <sub>1</sub> 24.5 to 31.5	H+H <sub>component</sub> < H <sub>1</sub> 25.0 to 31.5	H+H <sub>component</sub> < H <sub>1</sub> 26.0 to 37.0	H+H <sub>component</sub> < H <sub>1</sub> 30.0 to 43.0	H+H <sub>component</sub> < H <sub>1</sub> 35.0 to 45.0
Pin spacing at upper edge of carrier tape	F	2.5 ±0.5	5.0 <sup>+0.8</sup> <sub>-0.2</sub>	7.5 ±0.8	10.0 ±0.8	15 ±0.8	22.5 ±0.8	27.5 ±0.8
Pin diameter	d	0.4 ±0.05	0.5 ±0.05	0.5 ±0.05 or 0.6 <sup>+0.06</sup> <sub>-0.05</sub>	0.5 ±0.05 or 0.6 <sup>+0.06</sup> <sub>-0.05</sub>	0.8 <sup>+0.08</sup> <sub>-0.05</sub>	0.8 <sup>+0.08</sup> <sub>-0.05</sub>	0.8 <sup>+0.08</sup> <sub>-0.05</sub>
Component alignment	Δh	± 2.0 max.	± 2.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.
Total tape thickness	t	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2
Package (see also page 150)	ROLL/AMMO			AMMO				
	REEL	$\phi$ 360 max. $\phi$ 30 ±1	$B$ 52 ±2 $B$ 58 ±2 } depending on comp. dimensions	REEL $\phi$ 360 max. $\phi$ 30 ±1	$B$ 52 ±2 $B$ 58 ±2 or $B$ 66 ±2	REEL $\phi$ 500 max. $\phi$ 25 ±1	$B$ 54 ±2 $B$ 60 ±2 $B$ 68 ±2 } depending on PCM and component dimensions	
Unit	see details page 151.							

Dims in mm.

\* Diameter of pins see General Data.

\* PCM 10 and PCM 15 can be crimped to PCM 7.5.

Position of components according to PCM 7.5 (sketch 11). P<sub>0</sub> = 12.7 or 15.0 is possible

Please clarify customer-specific deviations with the manufacturer.

## Types of Tape Packaging of Capacitors for Automatic Radial Insertion

### ■ ROLL Packaging



### ■ AMMO Packaging



### ■ REEL Packaging



## BAR CODE (Labelling)

Labelling of package units in plain text and with alphanumerical Bar Code

Scanner decoding of

- WIMA supplier number
- Customer's P/O number
- Customer's part number
- WIMA confirmation number
- WIMA part number
- Lot number
- Date code
- Quantity

In addition part description of

- article
- capacitance value
- rated voltage
- dimensions
- capacitance tolerance
- packing

as well as gross weight and customer's name are indicated in plain text.

<b>WIMA</b> Best Capacitors Made In Germany		Werk Unna	
Supplier-ID: 123456789	<b>RoHS</b> 2011/65/EU	Date Code: 08.10.10	
Purchase Order No. (P/O): Bestellung xyz		Quantity: 5.000	
Customer Part No.: KUNDETEILENUMMER		Customer No.: 0000100002	
		Gross Weight [g]: 1870	
WIMA Confirmation No.: 0001004053000100	WIMA Part No.: MKS2C034701C00K88D		
Handling Unit: <b>MKS 2</b>	<b>QTY: 5.000</b>	<b>COO: DE</b>	
	<b>MKS 2 0.47 µF 63 VDC 3.5x8.5x7.2 RM5</b>		
<b>1000067326</b>	Standard 10% Loss - Standard Dichte 6-2	Week 03/2011	
	Vorlage Debitor Inland		

BARCODE „Code 39“

# Packing Quantities for Capacitors with Radial Pins in PCM 2.5 mm to 22.5 mm



PCM	Size				bulk	pcs. per packing unit									
						ROLL		REEL				AMMO			
	W	H	L	Codes		S	H16.5	H18.5	ø 360	H16.5	H18.5	ø 500	H16.5	H18.5	340 x 340
					N	O	F	I	H	J	A	C	B	D	
<b>2.5 mm</b>	2.5	7	4.6	<b>0B</b>	5000		2200		2500		-		2800		-
	3	7.5	4.6	<b>0C</b>	5000		2000		2300		-		2300		-
	3.8	8.5	4.6	<b>0D</b>	5000		1500		1800		-		1800		-
	4.6	9	4.6	<b>0E</b>	5000		1200		1500		-		1500		-
	5.5	10	4.6	<b>0F</b>	5000		900		1200		-		1200		-
<b>5 mm</b>	2.5	6.5	7.2	<b>1A</b>	5000		2200		2500		-		2800		-
	3	7.5	7.2	<b>1B</b>	5000		2000		2300		-		2300		-
	3.5	8.5	7.2	<b>1C</b>	5000		1600		2000		-		2000		-
	4.5	6	7.2	<b>1D</b>	6000		1300		1500		-		1500		-
	4.5	9.5	7.2	<b>1E</b>	4000		1300		1500		-		1500		-
	5	10	7.2	<b>1F</b>	3500		1100		1400		-		1400		-
	5.5	7	7.2	<b>1G</b>	4000		1000		1200		-		1200		-
	5.5	11.5	7.2	<b>1H</b>	2500		1000		1200		-		1200		-
	6.5	8	7.2	<b>1I</b>	2500		800		1000		-		1000		-
	7.2	8.5	7.2	<b>1J</b>	2500		700		1000		-		1000		-
	7.2	13	7.2	<b>1K</b>	2000		700		950		-		1000		-
	8.5	10	7.2	<b>1L</b>	2000		600		800		-		800		-
8.5	14	7.2	<b>1M</b>	1500		600		800		-		800		-	
11	16	7.2	<b>1N</b>	1000		500		600		-		640		-	
<b>7.5 mm</b>	2.5	7	10	<b>2A</b>	5000		-		2500		4400		2500		-
	3	8.5	10	<b>2B</b>	5000		-		2200		4300		2300		4150
	4	9	10	<b>2C</b>	4000		-		1700		3200		1700		3100
	4.5	9.5	10.3	<b>2D</b>	3500		-		1500		2900		1400		2700
	5	10.5	10.3	<b>2E</b>	3000		-		1300		2500		1300		-
	5.7	12.5	10.3	<b>2F</b>	2000		-		1000		2200		1100		-
	7.2	12.5	10.3	<b>2G</b>	1500		-		900		1800		1000		-
<b>10 mm</b>	3	9	13	<b>3A</b>	3000		-		1100		2200		-		1900
	4	8.5	13.5	<b>FA</b>	3000		-		900		1600		-		1450
	4	9	13	<b>3C</b>	3000		-		900		1600		-		1450
	4	9.5	13	<b>3D</b>	3000		-		900		1600		-		1400
	5	10	13.5	<b>FB</b>	2000		-		700		1300		-		1200
	5	11	13	<b>3F</b>	3000		-		700		1300		-		1200
	6	12	13	<b>3G</b>	2400		-		550		1100		-		1000
	6	12.5	13	<b>3H</b>	2400		-		550		1100		-		1000
8	12	13	<b>3I</b>	2000		-		400		800		-		740	
<b>15 mm</b>	5	11	18	<b>4B</b>	2400		-		600		1200		-		1150
	5	13	19	<b>FC</b>	1000		-		600		1200		-		1200
	6	12.5	18	<b>4C</b>	2000		-		500		1000		-		1000
	6	14	19	<b>FD</b>	1000		-		500		1000		-		1000
	7	14	18	<b>4D</b>	1600		-		450		900		-		850
	7	15	19	<b>FE</b>	1000		-		450		900		-		850
	8	15	18	<b>4F</b>	1200		-		400		800		-		740
	8	17	19	<b>FF</b>	500		-		400		800		-		740
	9	14	18	<b>4H</b>	1200		-		350		700		-		650
	9	16	18	<b>4J</b>	900		-		350		700		-		650
	10	18	19	<b>FG</b>	500		-		300		650		-		590
11	14	18	<b>4M</b>	1000		-		300		600		-		540	
<b>22.5 mm</b>	5	14	26.5	<b>5A</b>	1200		-		-		800		-		770
	6	15	26.5	<b>5B</b>	1000		-		-		700		-		640
	7	16.5	26.5	<b>5D</b>	760		-		-		600		-		550
	8	20	28	<b>FH</b>	500		-		-		500		-		480
	8.5	18.5	26.5	<b>5F</b>	500		-		-		480		-		450
	10	22	28	<b>FI</b>	570*		-		-		420		-		380
	10.5	19	26.5	<b>5G</b>	594*		-		-		400		-		360
	10.5	20.5	26.5	<b>5H</b>	594*		-		-		400		-		360
	11	21	26.5	<b>5I</b>	561*		-		-		380		-		350
	12	24	28	<b>FJ</b>	480*		-		-		350		-		310

\* TPS (Tray-Packing-System). Plate versions may have different packing units. Samples and pre-production needs on request.

■ Moulded versions.

Rights reserved to amend design data without prior notification.



## Packing Quantities for Capacitors with Radial Pins in PCM 27.5 mm to 52.5 mm

PCM	Size				bulk	pcs. per packing unit											
						ROLL		REEL				AMMO					
	W	H	L	Codes		S	N	O	ø 360		ø 500		340 x 340		490 x 370		
								H16.5	H18.5	H16.5	H18.5	H16.5	H18.5	H16.5	H18.5	H16.5	H18.5
								F	I	H	J	A	C	B	D		
<b>27.5 mm</b>	9	19	31.5	<b>6A</b>	567*	-	-	-	-	460/340*	-	-	420				
	11	21	31.5	<b>6B</b>	459*	-	-	-	-	380/280*	-	-	350				
	13	24	31.5	<b>6D</b>	378*	-	-	-	-	300	-	-	290				
	13	25	33	<b>FK</b>	405*	-	-	-	-	-	-	-	-				
	15	26	31.5	<b>6F</b>	324*	-	-	-	-	270	-	-	250				
	15	26	33	<b>FL</b>	324*	-	-	-	-	-	-	-	-				
	17	29	31.5	<b>6G</b>	198*	-	-	-	-	-	-	-	-				
	17	34.5	31.5	<b>6I</b>	198*	-	-	-	-	-	-	-	-				
	20	32	33	<b>FM</b>	162*	-	-	-	-	-	-	-	-				
20	39.5	31.5	<b>6J</b>	162*	-	-	-	-	-	-	-	-					
<b>37.5 mm</b>	9	19	41.5	<b>7A</b>	441*	-	-	-	-	-	-	-	-				
	11	22	41.5	<b>7B</b>	357*	-	-	-	-	-	-	-	-				
	13	24	41.5	<b>7C</b>	294*	-	-	-	-	-	-	-	-				
	15	26	41.5	<b>7D</b>	252*	-	-	-	-	-	-	-	-				
	17	29	41.5	<b>7E</b>	154*	-	-	-	-	-	-	-	-				
	19	32	41.5	<b>7F</b>	140*	-	-	-	-	-	-	-	-				
	20	39.5	41.5	<b>7G</b>	126*	-	-	-	-	-	-	-	-				
	24	45.5	41.5	<b>7H</b>	112*	-	-	-	-	-	-	-	-				
	31	46	41.5	<b>7I</b>	84*	-	-	-	-	-	-	-	-				
	35	50	41.5	<b>7J</b>	35*	-	-	-	-	-	-	-	-				
	40	55	41.5	<b>7K</b>	28*	-	-	-	-	-	-	-	-				
<b>48.5 mm</b>	19	31	56	<b>8D</b>	120*	-	-	-	-	-	-	-	-				
	23	34	56	<b>8E</b>	80*	-	-	-	-	-	-	-	-				
	27	37.5	56	<b>8H</b>	84*	-	-	-	-	-	-	-	-				
	33	48	56	<b>8J</b>	25*	-	-	-	-	-	-	-	-				
	37	54	56	<b>8L</b>	25*	-	-	-	-	-	-	-	-				
<b>52.5 mm</b>	25	45	57	<b>9D</b>	70*	-	-	-	-	-	-	-	-				
	30	45	57	<b>9E</b>	60*	-	-	-	-	-	-	-	-				
	35	50	57	<b>9F</b>	25*	-	-	-	-	-	-	-	-				
	45	55	57	<b>9H</b>	20*	-	-	-	-	-	-	-	-				
	45	65	57	<b>9J</b>	20*	-	-	-	-	-	-	-	-				

\* for 2-inch transport pitches.

\* TPS (Tray-Packing-System). Plate versions may have different packing units. Samples and pre-production needs on request.

■ Moulded versions. Rights reserved to amend design data without prior notification.

Updated data on [www.wima.com](http://www.wima.com)



A WIMA part number consists of 18 digits and is composed as follows:

- Field 1 - 4: Type description
- Field 5 - 6: Rated voltage
- Field 7 - 10: Capacitance
- Field 11 - 12: Size and PCM
- Field 13 - 14: Version code (e.g. Snubber versions)
- Field 15: Capacitance tolerance
- Field 16: Packing
- Field 17 - 18: Pin length (untaped)

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
<b>M</b>	<b>K</b>	<b>S</b>	<b>2</b>	<b>C</b>	<b>0</b>	<b>2</b>	<b>1</b>	<b>0</b>	<b>0</b>	<b>1</b>	<b>A</b>	<b>0</b>	<b>0</b>	<b>M</b>	<b>S</b>	<b>S</b>	<b>D</b>
MKS 2				63 VDC		0.01 µF			2.5x6.5x7.2		-		20%	bulk	6 -2		

<p><b>Type description:</b></p> <p>SMD-PET = SMDT              SMD-PEN = SMDN              SMD-PPS = SMDI              FKP 02 = FKPO              MKS 02 = MKS0              FKS 2 = FKS2              FKP 2 = FKP2              FKS 3 = FKS3              FKP 3 = FKP 3              MKS 2 = MKS2              MKP 2 = MKP2              MKS 4 = MKS4              MKP 4C = MKPC              MKP 4 = MKP4              MKP 10 = MKP1              FKP 1 = FKP1              MKP-X2 = MKX2              MKP-X1 R = MKX1              MKP-Y2 = MKY2              MP 3-X2 = MPX2              MP 3-X1 = MPX1              MP 3-Y2 = MPY2              MP 3R-Y2 = MPRY              MKP 4F = MKPF              Snubber MKP = SNMP              Snubber FKP = SNFP              GTO MKP = GTOM              DC-LINK MKP 3 = DCP3              DC-LINK MKP 4 = DCP4              DC-LINK MKP 4S = DCP5              DC-LINK MKP 5 = DCP5              DC-LINK MKP 6 = DCP6              DC-LINK HC = DCHC              DC-LINK HY = DCHY</p>	<p><b>Rated voltage:</b></p> <p>50 VDC = B0              63 VDC = C0              100 VDC = D0              250 VDC = F0              400 VDC = G0              450 VDC = H0              520 VDC = H2              600 VDC = I0              630 VDC = J0              700 VDC = K0              800 VDC = L0              850 VDC = M0              900 VDC = N0              1000 VDC = O1              1100 VDC = P0              1200 VDC = Q0              1250 VDC = R0              1500 VDC = S0              1600 VDC = T0              2000 VDC = U0              2500 VDC = V0              3000 VDC = W0              4000 VDC = X0              6000 VDC = Y0              250 VAC = 0W              275 VAC = 1W              300 VAC = 2W              305 VAC = AW              350 VAC = BW              440 VAC = 4W              500 VAC = 5W              ...</p>	<p><b>Capacitance:</b></p> <p>22 pF = 0022              47 pF = 0047              100 pF = 0100              150 pF = 0150              220 pF = 0220              330 pF = 0330              470 pF = 0470              680 pF = 0680              1000 pF = 1100              1500 pF = 1150              2200 pF = 1220              3300 pF = 1330              4700 pF = 1470              6800 pF = 1680              0.01 µF = 2100              0.022 µF = 2220              0.047 µF = 2470              0.1 µF = 3100              0.22 µF = 3220              0.47 µF = 3470              1 µF = 4100              2.2 µF = 4220              4.7 µF = 4470              10 µF = 5100              22 µF = 5220              47 µF = 5470              100 µF = 6100              220 µF = 6220              1000 µF = 7100              1500 µF = 7150              ...</p>	<p><b>Size:</b></p> <p>4.8x3.3x3 Size 1812 = KA              4.8x3.3x4 Size 1812 = KB              5.7x5.1x3.5 Size 2220 = QA              5.7x5.1x4.5 Size 2220 = QB              7.2x6.1x3 Size 2824 = TA              7.2x6.1x5 Size 2824 = TB              10.2x7.6x5 Size 4030 = VA              12.7x10.2x6 Size 5040 = XA              15.3x13.7x7 Size 6054 = YA              2.5x7x4.6 PCM 2.5 = 0B              3x7.5x4.6 PCM 2.5 = 0C              2.5x6.5x7.2 PCM 5 = 1A              3x7.5x7.2 PCM 5 = 1B              2.5x7x10 PCM 7.5 = 2A              3x8.5x10 PCM 7.5 = 2B              3x9x13 PCM 10 = 3A              4x9x13 PCM 10 = 3C              5x11x18 PCM 15 = 4B              6x12.5x18 PCM 15 = 4C              5x14x26.5 PCM 22.5 = 5A              6x15x26.5 PCM 22.5 = 5B              9x19x31.5 PCM 27.5 = 6A              11x21x31.5 PCM 27.5 = 6B              9x19x41.5 PCM 37.5 = 7A              11x22x41.5 PCM 37.5 = 7B              19x31x56 PCM 48.5 = 8D              25x45x57 PCM 52.5 = 9D              ...</p> <p><b>Version code:</b></p> <p>Standard = 00              Version A1 = 1A              Version A1.1.1 = 1B              Version A2 = 2A              ...</p>	<p><b>Tolerance:</b></p> <p>±20% = M              ±10% = K              ±5% = J              ±2.5% = H              ±1% = E              ...</p> <p><b>Packing:</b></p> <p>AMMO H16.5 340x340 = A              AMMO H16.5 490x370 = B              AMMO H18.5 340x340 = C              AMMO H18.5 490x370 = D              REEL H16.5 360 = F              REEL H16.5 500 = H              REEL H18.5 360 = I              REEL H18.5 500 = J              ROLL H16.5 = N              ROLL H18.5 = O              BLISTER W12 180 = P              BLISTER W12 330 = Q              BLISTER W16 330 = R              BLISTER W24 330 = T              Bulk/TPS Standard = S              ...</p> <p><b>Pin length (untaped)</b></p> <p>3.5 ±0.5 = C9              6 -2 = SD              16 ±1 = P1              ...</p> <p><b>Pin length (taped)</b></p> <p>none = 00</p>
--	--	---	--	---

The data on this page is not complete and serves only to explain the part number system. Part number information is listed on the pages of the respective WIMA range.