

Crimp contact - CDC-MP 1,5-2,5-R - 1016659


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimp contact



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 3000 pc |
| Minimum order quantity | 3000 pc |
| GTIN |  4 055626 498645 |
| GTIN | 4055626498645 |
| Weight per Piece (excluding packing) | 0.210 g |
| Custom tariff number | 85366990 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions for the product

| | |
|-------|------|
| Pitch | 0 mm |
|-------|------|

Packaging information

| | |
|----------------------------|------|
| Type of packaging | Belt |
| Pieces per package | 3000 |
| Denomination packing units | Pcs. |

General product information

| | |
|--------------|--|
| Type of note | Note on application |
| | Order information: |
| | Note regarding documentation |
| Note | The crimp contacts may only be processed with approved crimping tools. |

Crimp contact - CDC-MP 1,5-2,5-R - 1016659

Technical data

General product information

| | |
|--|---|
| | You can find ordering information for the approved crimping tool for automated conductor connections in the installation instructions in the Downloads section. |
| | The crimp heights depend on the crimping tool used. You can find the values in the tool documentation. |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27260700 |
| eCl@ss 4.1 | 27260700 |
| eCl@ss 5.0 | 27260700 |
| eCl@ss 5.1 | 27260700 |
| eCl@ss 6.0 | 27260700 |
| eCl@ss 7.0 | 27440309 |
| eCl@ss 8.0 | 27440204 |
| eCl@ss 9.0 | 27440204 |

ETIM

| | |
|----------|----------|
| ETIM 5.0 | EC000796 |
| ETIM 6.0 | EC002638 |
| ETIM 7.0 | EC002638 |

Accessories

Additional products

Direct connector - CDDC 2,5/ 2-PV-5,0 - 1016293



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 2, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

Direct connector - CDDC 2,5/ 3-PV-5,0 - 1016292



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 3, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology, pin layout: Linear pinning

Crimp contact - CDC-MP 1,5-2,5-R - 1016659

Accessories

Direct connector - CDDC 2,5/ 4-PV-5,0 - 1016290



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 4, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD
- Direct plug-in technology, pin layout: Linear pinning

Direct connector - CDDC 2,5/ 5-PV-5,0 - 1016289



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 5, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD
- Direct plug-in technology, pin layout: Linear pinning

Direct connector - CDDC 2,5/ 6-PV-5,0 - 1016288



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 6, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD
- Direct plug-in technology, pin layout: Linear pinning

Direct connector - CDDC 2,5/ 7-PV-5,0 - 1016286



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 7, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD
- Direct plug-in technology, pin layout: Linear pinning

Direct connector - CDDC 2,5/ 8-PV-5,0 - 1016285



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 8, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD
- Direct plug-in technology

Crimp contact - CDC-MP 1,5-2,5-R - 1016659

Accessories

Direct connector - CDDC 2,5/ 9-PV-5,0 - 1016280



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 9, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology

PCB direct plug - CDDC 2,5/10-PV-5,0 - 1016279



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 10, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology

PCB direct plug - CDDC 2,5/11-PV-5,0 - 1016278



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 11, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology

PCB direct plug - CDDC 2,5/12-PV-5,0 - 1016277



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 12, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology

PCB direct plug - CDDC 2,5/13-PV-5,0 - 1016276



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 13, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology

Crimp contact - CDC-MP 1,5-2,5-R - 1016659

Accessories

PCB direct plug - CDDC 2,5/14-PV-5,0 - 1016274



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 14, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology

PCB direct plug - CDDC 2,5/15-PV-5,0 - 1016273



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 15, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology

PCB direct plug - CDDC 2,5/16-PV-5,0 - 1016272



PCB direct plug, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 16, pitch: 5 mm, connection method: Crimp connection, color: green, contact surface: Tin, mounting: SKEDD - Direct plug-in technology