

PRODUCT-DETAILS

# XQM0404

## KFF STR CONNECTORS 20X20MM



Product image  
not available

### General Information

|                       |  |
|-----------------------|--|
| Extended Product Type | XQM0404  |
| Product ID            | 7TCA297020R0489  |
| EAN                   | 5011949209541  |
| Catalog Description   | KFF STR CONNECTORS 20X20MM   |
| Long Description      | Liquid Tight Fitting for Covered Conduit, Straight with External Male Thread, Conduit Size 20mm, M20 Thread, Very High Mechanical and UV Protection, IP66, IP67 Ratings, Nickel Plated Brass with a Co-Polyester Seal and Nylon Insert |

### Ordering

|                       |               |
|-----------------------|---------------|
| EAN                   | 5011949209541 |
| Customs Tariff Number | 7412200090    |

### Dimensions

|                    |                    |
|--------------------|--------------------|
| Product Net Weight | .11 lb<br>49.887 g |
|--------------------|--------------------|

### Container Information

|                       |           |
|-----------------------|-----------|
| Package Level 1 Units | 25 piece  |
| Package Level 2 Units | 200 piece |
| Package Level 2 Width | 13 in     |

|                                |        |
|--------------------------------|--------|
|                                | 330 mm |
| Package Level 2 Height         | 7 in   |
|                                | 178 mm |
| Package Level 2 Depth / Length | 13 in  |
|                                | 330 mm |

## Additional Information

|                     |   |
|---------------------|---|
| Application         | For Insertion Into Threaded Entries & Knockouts Using a Locknut to Secure |
| Brand / Label       | Kopex   |
| Color               | Metallic  |
| Insulation Material | IP66, 67 Rating   |
| Material            | Brass with a Co-Polyester Seal and Nylon Insert                           |
| Number of Batteries | 0   |
| Product Name        | BRASS FITTING FOR CONDUIT   |
| Product Type        | Straight Fitting with External Thread for Covered Conduit                 |
| Size                | Conduit Size 20mm ; M20 Thread  |
| Special Functions   | Very High UV Protection and Mechanical Protection                         |
| Standards           | UL E60625, BSI Kitemark KM-90009, Low Voltage Directive                   |
| Surface Finishing   | Nickel Plated   |
| UPC                 | 786210253954  |

## Certificates and Declarations (Document Number)

|                                   |                 |
|-----------------------------------|-----------------|
| Data Sheet, Technical Information | XQM0404         |
| Declaration of Conformity - CE    | 9AKK107492A9617 |
| Instructions and Manuals          | XQM0404         |

## Classifications

|                                    |  |
|------------------------------------|--|
| ETIM 6                             | EC001180 - Screw connection for protective metallic hose |
| ETIM 7                             | EC001180 - Screw connection for protective metallic hose |
| UNSPSC                             | 39121420   |
| WEEE Category                      | Product Not in WEEE Scope                                |
| IDEA Granular Category Code (IGCC) | 4585 >> Liquid tight connectors                          |

## Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image  
not available