



(IRM-90)



(IRM-90-xxST)























Features

- 3.43"x2.05"compact size
- PCB, chassis or screw terminal mounting version
- · Universal input 80~305VAC
- No load power consumption<0.21W
- EMI EN55032 ClassB without additional components
- Wide operating temp. rage -30~80°C
- · Protections: Short circuit / Overload / Over voltage
- Cooling by free air convection
- Isolation Class Ⅱ
- Over voltage category Ⅲ
- Operating attitude up to 4000 meters (Note.7)
- 100W peak(10 sec.)
- · 3 years warranty


Applications

- · Industrial electrical equipment
- · Mechanical equipment
- Factory automation equipment
- · Handheld electronic device

Description

IRM-90 is a 90W miniature (87*52*29.5mm) AC-DC PCB-mount module type power supply, ready to be soldered onto the PCB boards of various kinds of electronic instruments or industrial automation equipments. This product allows the universal input voltage range of 80~305VAC. The 94V-0 flame retardant plastic case and the fully-potted silicone enhance the heat dissipation and meet the anti-vibration demand up to 2~5G anti-vibration by model; moreover, it provides the fundamental resistance to dust and moisture.

With the high efficiency up to 93% and the extremely low no-load power consumption below 0.21W, IRM-90 series fulfills the worldwide regulation for the low power consumption requirement for electronics. The entire series is a Class II design (no FG pin), incorporating the built-in EMI filtering components, enabling the compliance with EN55032 Class B; the supreme EMC features keep the end electronic units from from electromagnetic interference. In addition to the PCB mounting style model, IRM-90 series also offers the screw terminal style model (ST).




90W AC-DC PCB-Mount Green Power Module

IRM-90 series

SPECIFICATION

MODEL		IRM-90-12	IRM-90-15	IRM-90-24	IRM-90-48	
	DC VOLTAG	GE	12V	15V	24V	48V
		Peak(10 sec.)	7.37A	6.23A	4.13A	2.07A
	CURRENT	Convection	6.7A	5.67A	3.75A	1.88A
	RATED	Peak(10 sec.)Note.2	88,4W	93.5W	99W	99.2W
		Convection	80,4W	85,05W	90W	90,2W
OUTPUT	RIPPLE & NOISE (max.) Note.			150mVp-p	200mVp-p	240mVp-p
	VOLTAGE TOLERANCE Note.4		±2.0%	±2.0%	±2.0%	±2,0%
	LINE REGULATION		±0.5%	±0.5%	±0.5%	±0.5%
	LOAD REGULATION		±1,0%	±0.5%	±0,5%	±0.5%
	SETUP. RISE TIME		1000ms, 30ms/230VAC 1000ms, 30ms/115VAC at full load			
	HOLD UP TIME (Typ.)		30ms/230VAC 10ms/115VAC at full load			
INPUT	VOLTAGE RANGE Note.5					
	FREQUENCY RANGE		47 ~ 63Hz	1/	1	000/
	EFFICIENCY (Typ.)		92%	92.5%	93%	93%
	AC CURRENT (Typ.)		1.9A/115VAC 1.1A/230VAC			
	INRUSH CURRENT (Typ.)		COLD START 30A/115VAC 65A/230VAC			
	LEAKAGE CURRENT (max.) Note.6					
DDOTECTION	OVERLOAD		115% ~ 160% rated output power			
	OVERLOAD	, 	Protection type: Hiccup mode, recovers automatically after fault condition is removed			
PROTECTION	0.450.401.74.05		12.6 ~ 16.2V	15.8 ~ 20.3V	25.2 ~ 32.4V	50.4 ~ 64.8V
	OVER VOLTAGE		Protection type : Shut down o/p	voltage, re-power on to re	cover	
	OVER TEMPERATURE		Protection type: Shut down o/p voltage, re-power on to recover			
ENVIRONMENT	WORKING TEMP.		-30 ~ +80°C (Refer to "Derating Curve")			
	WORKING HUMIDITY		20 ~ 90% RH non-condensing			
	STORAGE TEMP.		-40~+85°C			
	TEMP. COEFFICIENT		±0,03%/°C (0~50°C)			
	SOLDERING TEMPERATURE					
	VIBRATION OPERATING ALTITUDE Note.7		Blank:10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes			
			ST:10 ~ 500Hz, 5G 10min./1cycle, period for 60min. each along X, Y, Z axes			
SAFETY &	SAFETY STANDARDS		IEC62368-1, UL62368-1, TUV EN62368-1, EAC TP TC 004 approved; Design refer to EN60335-1(by request)			
	WITHSTAND VOLTAGE		I/P-O/P:4KVAC			
	ISOLATION RESISTANCE		I/P-O/P:100M Ohms / 500VDC / 25°C / 70% RH			
	ISOLATION RESISTANCE		Parameter	Standard		Test Level / Note
	EMC EMISSION EMC IMMUNITY		Conducted	EN55032 (CIS	PDD22)	Class B
			Radiated	`	· · · · · · · · · · · · · · · · · · ·	Class B
				EN55032 (CIS	· · · · · · · · · · · · · · · · · · ·	
			Harmonic Current	EN61000-3-2		Class A
			Voltage Flicker	EN61000-3-3		
EMC			EN55035, EN61000-6-2			
(Note 8)			Parameter	Standard		Test Level / Note
			ESD	EN61000-4-2		Level 3, 8KV air; Level 2, 4KV contact, criteria A
			RF field susceptibility	EN61000-4-3		Level 3, criteria A
			EET huroto	EN61000-4-4		Level 3, criteria A
			EFT bursts EN61000-4-4 Surge susceptibility EN61000-4-5			· ·
			0 1 7			Level 4,2KV/L-N, criteria A
			· ,	EN61000-4-6		Level 3, criteria A
			Magnetic field immunity	EN61000-4-8		Level 4, criteria A
			Voltage dip, interruption	EN61000-4-1	1	>95% dip 0. 5 periods, 30% dip 25 periods, >95% interruptions 250 periods
OTHERS	MTBF		310Khrs min. MIL-HDBK-217F (25°C); 1694.28Khrs min. Telcordia TR/SR-332 (Bellcore) (25°C)			
	DIMENSION		PCB mounting style: 87*52*29.5mm (L*W*H) Screw terminal style: 109*52*33.5mm (L*W*H)			
	PACKING		PCB mounting style : 0.197Kg;60pcs/11.8Kg/0.97CUFT Screw terminal style : 0.219Kg;50pcs/12Kg/0.55CUFT			
NOTE	 All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature. 33% Duty cycle maximum within every 30 seconds. Average output power should not exceed the rated power. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1 μ f & 47 μ f parallel capacitor. Tolerance: includes set up tolerance, line regulation and load regulation. Derating may be needed under low input voltages. Please check the derating curve for more details. Leakage current was measured from primary input to DC output. The ambient temperature derating of 3.5°C/1000m with fanless models and of 5°C/1000m with fan models for operating altitude higher than 2000m(6500ft) The power supply is considered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies." (as available on http://www.meanwell.com) 					





115 120 140 160 180 200 220 240 264


INPUT VOLTAGE (VAC) 60Hz


Case No.IRM60 Unit:mm



■ Mechanical Specification


• PCB mounting style (IRM-90)






AC/L, AC/N P/N diameter:1 ψ +Vo, -Vo P/N diameter:2 ψ

• Screw terminal style (IRM-90-xxST)





■ Installation Manual

Please refer to: http://www.meanwell.com/manual.html