

PRODUCT-DETAILS

PST0410

LS1 PLIABLE CONDUIT TYPE T 20MM 10M



Product image
not available

General Information

Extended Product Type	PST0410
Product ID	7TCA297020R0342
EAN	5011949217089
Catalog Description	LS1 PLIABLE CONDUIT TYPE T 20MM 10M
Long Description	Liquid Tight, Low Fire Hazard Covered Conduit, Nominal Conduit Size 20mm, 1/2 Inch US Trade Size, Outside Diameter 21.0mm, Inside Diameter 14.6mm, Static Bend Radius 40mm, Reel Length 10 Meters, IP66, IP67 Rating, Galvanised Steel and Kraft Paper Core with Low Fire Hazard Covering, Black

Ordering

EAN	5011949217089
Customs Tariff Number	8307106000

Dimensions

Product Net Weight	6.32 lb 2.866 kg
--------------------	---------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

Additional Information

Application	Liquid Resistant Indoors / Outdoors, Light Industrial, Underground, Rail Infrastructure, Where Low Smoke & Toxicity is a Primary Concern
Brand / Label	Kopex
Color	Black
Inside Diameter	14.6 mm
Material	Galvanized Steel with Kraft Paper Core and Low Fire Hazard Coating
Nominal Size	1/2 in NC20
Number of Batteries	0
Outside Diameter	21.0 mm
Product Name	FLEXIBLE METAL CONDUIT
Product Type	Liquid Tight Low Fire Hazard Conduit
Radius	40 mm
Standards	BSI Kitemark KM-90009, Low Voltage Directive, London Underground I-085, NFF16-101 (I1 F1)
UPC	786210272207

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	PST0410
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	PST0410

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image
not available