



SAFETY DATA SHEET SUPER CLEAN

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name SUPER CLEAN

Product number CSC005

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Cleaning agent.

1.3. Details of the supplier of the safety data sheet

Manufacturer TETROSYL LIMITED
Bury
Lancashire
England
BL9 7NY
0161 764 5981
0161 797 5899
info@tetrosyl.com

1.4. Emergency telephone number

Emergency telephone +44 (0)161 764 5981

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards Not Classified

Health hazards Eye Dam. 1 - H318 Skin Sens. 1 - H317

Environmental hazards Not Classified

2.2. Label elements

Hazard pictograms



Signal word Danger

Hazard statements
H318 Causes serious eye damage.
H317 May cause an allergic skin reaction.

SUPER CLEAN

Precautionary statements	<p>P101 If medical advice is needed, have product container or label at hand.</p> <p>P102 Keep out of reach of children.</p> <p>P261 Avoid breathing vapour/ spray.</p> <p>P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.</p> <p>P302+P352 IF ON SKIN: Wash with plenty of water.</p> <p>P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.</p> <p>P310 Immediately call a POISON CENTER/ doctor.</p> <p>P333+P313 If skin irritation or rash occurs: Get medical advice/ attention.</p> <p>P362+P364 Take off contaminated clothing and wash it before reuse.</p> <p>P501 Dispose of contents/ container in accordance with national regulations.</p>
Contains	C6 ALKYL GLUCOSIDE, 2-PROPYLHEPTANOL ETHOXYLATE, (R)-p-mentha-1,8-diene, 2-METHYLISOTHIAZOL-3(2H)-ONE
Detergent labelling	< 5% non-ionic surfactants, < 5% perfumes, < 5% phosphates, Contains LIMONENE, CITRAL, BENZISOTHIAZOLINONE, METHYLISOTHIAZOLINONE
Supplementary precautionary statements	<p>P272 Contaminated work clothing should not be allowed out of the workplace.</p> <p>P321 Specific treatment (see medical advice on this label).</p>

2.3. Other hazards

Not applicable.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

TETRAPOTASSIUM PYROPHOSPHATE			3-<5.0%
CAS number: 7320-34-5	EC number: 230-785-7	REACH registration number: 01-2119489369-18-0003	
Classification Eye Irrit. 2 - H319			

C6 ALKYL GLUCOSIDE			3-<5.0%
CAS number: 54549-24-5	EC number: 259-217-6	REACH registration number: 01-2119492545-29	
Classification Eye Dam. 1 - H318			

2-PROPYLHEPTANOL ETHOXYLATE			1-<2%
CAS number: 160875-66-1	EC number: 605-233-7		
Classification Acute Tox. 4 - H302 Eye Dam. 1 - H318			

SUPER CLEAN

(R)-p-mentha-1,8-diene			0.1-<0.3%
CAS number: 5989-27-5	EC number: 227-813-5		
M factor (Acute) = 1	M factor (Chronic) = 1		
Classification Flam. Liq. 3 - H226 Skin Irrit. 2 - H315 Skin Sens. 1 - H317 Aquatic Acute 1 - H400 Aquatic Chronic 1 - H410			

2-METHYLISOTHIAZOL-3(2H)-ONE			0.001 - <0.005%
CAS number: 2682-20-4	EC number: 220-239-6		
M factor (Acute) = 1			
Classification Acute Tox. 3 - H301 Acute Tox. 3 - H311 Skin Corr. 1B - H314 Eye Dam. 1 - H318 Skin Sens. 1 - H317 STOT SE 3 - H335 Aquatic Acute 1 - H400			

BUTYLATED HYDROXYTOLUENE			0.001 - <0.005%
CAS number: 128-37-0	EC number: 204-881-4	REACH registration number: 01-2119565113-46-0000	
M factor (Acute) = 1	M factor (Chronic) = 1		
Classification Aquatic Acute 1 - H400 Aquatic Chronic 1 - H410			

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information	Get medical attention if any discomfort continues. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Remove affected person from source of contamination.
Inhalation	Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Get medical attention. Symptoms of lung oedema (shortness of breath) may develop up to 24 hours after exposure. Show this Safety Data Sheet to the medical personnel.
Ingestion	Get medical attention. Rinse mouth thoroughly with water. Give plenty of water to drink. Keep affected person under observation. Get medical attention if any discomfort continues. Show this Safety Data Sheet to the medical personnel.
Skin contact	Remove contaminated clothing immediately and wash skin with soap and water. Rinse with water. Get medical attention if irritation persists after washing.

SUPER CLEAN

Eye contact Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes. Do not rub eye. Get medical attention promptly if symptoms occur after washing.

4.2. Most important symptoms and effects, both acute and delayed

General information The severity of the symptoms described will vary dependent on the concentration and the length of exposure. Effects may be delayed. Keep affected person under observation.

Inhalation Upper respiratory irritation. Difficulty in breathing.

Ingestion May cause chemical burns in mouth and throat. May cause stomach pain or vomiting.

Skin contact Prolonged skin contact may cause redness and irritation. Allergic rash.

Eye contact May cause severe eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor No specific recommendations. If in doubt, get medical attention promptly.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media The product is not flammable.

5.2. Special hazards arising from the substance or mixture

Specific hazards Not relevant. No unusual fire or explosion hazards noted.

Hazardous combustion products Does not decompose when used and stored as recommended.

5.3. Advice for firefighters

Protective actions during firefighting No specific firefighting precautions known.

Special protective equipment for firefighters Leave danger zone immediately.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions For personal protection, see Section 8. In case of spills, beware of slippery floors and surfaces. Avoid inhalation of spray mist and contact with skin and eyes.

6.2. Environmental precautions

Environmental precautions Avoid discharge into drains or watercourses or onto the ground. Collect and dispose of spillage as indicated in Section 13.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Stop leak if possible without risk. Small Spillages: Flush contaminated area with plenty of water.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8. For waste disposal, see section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

SUPER CLEAN

Usage precautions

Good personal hygiene procedures should be implemented. Wash hands and any other contaminated areas of the body with soap and water before leaving the work site. Avoid eating, drinking and smoking when using the product. Avoid inhalation of vapours/spray and contact with skin and eyes.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions

Keep containers upright. Store in tightly-closed, original container.

7.3. Specific end use(s)

Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Occupational exposure limits

BUTYLATED HYDROXYTOLUENE

Long-term exposure limit (8-hour TWA): WEL 10 mg/m³

WEL = Workplace Exposure Limit

8.2. Exposure controls

Protective equipment



Appropriate engineering controls

All handling should only take place in well-ventilated areas.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. The following protection should be worn: Chemical splash goggles.

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. It is recommended that gloves are made of the following material: Nitrile rubber. It should be noted that liquid may penetrate the gloves. Frequent changes are recommended.

Other skin and body protection

Wear appropriate clothing to prevent any possibility of skin contact. Provide eyewash station.

Hygiene measures

Provide eyewash station and safety shower. Wash contaminated clothing before reuse. Wash hands after contact. When using do not eat, drink or smoke.

Respiratory protection

No specific recommendations. Respiratory protection may be required if excessive airborne contamination occurs.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Liquid.
Colour	Fluorescent. Green.
Odour	Citrus.
pH	pH (concentrated solution): 11.0
Melting point	Not determined.
Initial boiling point and range	100°C @ 1013 hPa

SUPER CLEAN

Flash point	This product does not sustain combustion.
Evaporation rate	Not determined.
Upper/lower flammability or explosive limits	Not determined.
Vapour pressure	Not determined.
Vapour density	Not determined.
Relative density	1.030g/cm ³ @ 20°C
Solubility(ies)	Miscible with water.
Partition coefficient	Not determined.
Auto-ignition temperature	Not determined.
Decomposition Temperature	Not determined.
Viscosity	<100 cP @ 20°C
Explosive properties	Not considered to be explosive.
Explosive under the influence of a flame	Not considered to be explosive.
Oxidising properties	Does not meet the criteria for classification as oxidising.

9.2. Other information

Other information	None.
--------------------------	-------

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity	The following materials may react strongly with the product: Alkaline earth metals. Powdered metal.
-------------------	---

10.2. Chemical stability

Stability	No particular stability concerns.
------------------	-----------------------------------

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	Not applicable.
---	-----------------

10.4. Conditions to avoid

Conditions to avoid	There are no known conditions that are likely to result in a hazardous situation.
----------------------------	---

10.5. Incompatible materials

Materials to avoid	Alkali metals. Powdered metal.
---------------------------	--------------------------------

10.6. Hazardous decomposition products

Hazardous decomposition products	Does not decompose when used and stored as recommended.
---	---

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Toxicological effects	No information available.
------------------------------	---------------------------

Acute toxicity - oral

SUPER CLEAN

ATE oral (mg/kg) 27,777.78

Inhalation No specific health hazards known.

Ingestion May cause discomfort if swallowed.

Skin contact Prolonged and frequent contact may cause redness and irritation. May cause an allergic skin reaction.

Eye contact Causes serious eye damage.

Acute and chronic health hazards May cause skin irritation/eczema. May cause internal injury.

SECTION 12: Ecological information

Ecotoxicity Not regarded as dangerous for the environment.

12.1. Toxicity

Acute aquatic toxicity

Acute toxicity - fish Not available.

Acute toxicity - aquatic invertebrates Not available.

12.2. Persistence and degradability

Persistence and degradability There are no data on the degradability of this product.

12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

Partition coefficient Not determined.

12.4. Mobility in soil

Mobility The product is miscible with water and may spread in water systems.

Adsorption/desorption coefficient Not available.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This substance is not classified as PBT or vPvB according to current EU criteria.

12.6. Other adverse effects

Other adverse effects Not applicable.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information Waste should be treated as controlled waste. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

Disposal methods Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority. Confirm disposal procedures with environmental engineer and local regulations.

SECTION 14: Transport information

SUPER CLEAN

General The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

Annex II of MARPOL 73/78
and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations EH40/2005 Workplace exposure limits.

EU legislation Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended).

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Revision comments NOTE: Lines within the margin indicate significant changes from the previous revision.

Issued by Health & Safety Department

Revision date 23/05/2019

Revision 5

Supersedes date 10/07/2018

SDS number 32600

SDS status Approved.

SUPER CLEAN

Hazard statements in full

H226 Flammable liquid and vapour.
H301 Toxic if swallowed.
H302 Harmful if swallowed.
H311 Toxic in contact with skin.
H314 Causes severe skin burns and eye damage.
H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H318 Causes serious eye damage.
H319 Causes serious eye irritation.
H335 May cause respiratory irritation.
H400 Very toxic to aquatic life.
H410 Very toxic to aquatic life with long lasting effects.