Terminal Block 4Way, 10A





Specifications:

Current Rating : 10A (300V AC) Min. Withstanding Insulation Voltage : 2,000V AC


Insulation Resistance : > 2,000MW (500V DC)


Operating Temperature : -40°C to +105°C Wire Range : 16AWG to 30AWG

Screw Torque : 8lb-inch to 10lb-inch

Connector Mounting : Panel Pitch Spacing : 6.35mm No. of Contacts : 4 **Contact Material** : Brass Contact Plating : Tin Terminal Type : Screw Termination Method : Vertical Wire Area Size Max : 1.3mm²

Diagram





Dimensions

Α	В
26.6	19.05

Dimensions: Millimetres

No	Description	Material	Plating/Finish	Colour
1	Insulating Body	Polyamide 66	-	Black
2	Terminal	Brass	Tin Plated	
3	Screw	Steel	Ni Plated	-

Part Number Table

Description	Part Number
Terminal Block - 4 Way 10A	T40-BS16-04

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

