



### TECHNICAL INFORMATION

Shape:	Round
Input Power:	AC:220-240V, 50Hz
Unit Color:	Black
Body Type:	Stainless Steel
Cutting Size:	90mm
Dimmable:	No
Rated Load:	Max 35W
Dimension:	110x110x120mm

### UNDERGROUND FITTINGS GU10 | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 7515 - 938

[View more details](#)



**STAINLESS STEEL  
FINISH**



**IP65**  
RATING



**2 YEAR**  
WARRANTY

### FEATURES

- Perfect replacement for traditional underground fittings
- Strong and sturdy Stainless Steel body
- Ingress protection IP65
- Easy to install and requires little maintenance
- Compatible with GU10 holder type (Fitting only - light not included)
- Suitable for pathways, driveways, tree uplighting etc.
- Recommended daily usage: 10 - 12 hours \*Exceeding recommended daily usage will void warranty

CE/EMC CE/LVD



### PACKAGING

Gross Weight (Kgs): 0.67  
Unit CBM: 0.0021125  
Dimension: 110x110x120mm

### MASTER BOX PACKAGING

Box Qty: 24  
Qty Per Pallet: 480  
Length (Box) mm: 130  
Width (Box) mm: 125  
Height (Box) mm: 130

### LISTING DETAILS

Commodity Code: 9405109890  
EanCode: 3800157617741