


Type: **PKZM0-2,5**
 Article No.: **072736**



Ordering information

Connection technique			Screw terminals
Motor rating AC-3 220 V 230 V 240 V	<i>P</i>	kW	0.37
Motor rating AC-3 380 V 400 V 415 V	<i>P</i>	kW	0.75
Motor rating AC-3 440 V	<i>P</i>	kW	1.1
Motor rating AC-3 500 V	<i>P</i>	kW	1.1
Motor rating AC-3 690 V	<i>P</i>	kW	1.5
Rated uninterrupted current	I_u	A	2.5
Setting range			
Overload releases	I_r	A	1,6 – 2,5
Short-circuit releases	I_{rm}	A	35

Notes concerning the product group



Accessories

3 Standard auxiliary contact → 072896

5 Trip-indicating auxiliary contact → 072898

6 Shunt release, undervoltage release → 073187

Single-phasing sensitivity to IEC/EN 60947-4-1

Can be snap-fitted to IEC/EN 60715 top-hat rail with 7.5 or 15 mm height




→ 266164

PTB 02 ATEX 3151, see manual


General			
Standards			IEC/EN 60947, VDE 0660, UL 508, CSA C 22.2 No. 14
Climatic proofing			Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
Ambient temperature			
Storage		°C	-25/+80
Open		°C	-25/55
Enclosed		°C	-25/40
Direction of incoming supply			As required
Degree of protection			
Device			IP 20
Terminations			IP00
Protection against direct contact			Finger and back-of-hand proof
Mechanical shock resistance half-sinusoidal shock 10 ms to IEC 60068-2-27		g	25
Altitude		m	2000
Terminal capacities			
Solid		mm ²	1 × (1 – 6) 2 × (1 – 6)
Flexible with ferrule to DIN 46228		mm ²	1 × (1 – 6) 2 × (1 – 6)
Solid or stranded		AWG	18 – 10
Specified tightening torque for terminal screws			
Main cable		Nm	1,7
Control circuit cables		Nm	1

Main conducting paths			
Rated impulse withstand voltage	U_{imp}	V AC	6000
Overtoltage category/pollution degree			III/3
Rated operational voltage	U_e	V AC	690
Rated uninterrupted current = rated operational current	$I_u = I_e$	A	32 or current setting of the overcurrent release
Rated frequency		Hz	40 – 60
Current heat loss (3 pole at operating temperature)		W	6
Lifespan, mechanical	Operations	$\times 10^6$	> 0,05
Lifespan, electrical (AC–3 at 400 V)	Operations	$\times 10^6$	0,05
Maximum operating frequency			
Max. operating frequency		Ops/h	40
Short–circuit rating			
AC			
Short–circuit protection maximum fuse			Page 4/33
DC			
Short–circuit rating		kA	60
Short–circuit rating			60 (up to PKZM0–16) 40 (PKZM0–20 to PKZM0–32)
Motor switching capacity			
AC–3 up to 690 V		A	32
DC–5 (up to 250 V)		A	25 (3 contacts in series)
Trip blocks			
Temperature compensation to IEC/EN 60947, VDE 0660		°C	–5 – 40
Operating range		°C	–25 – 55
Temperature compensation residual error for $T > 40$ °C		%/K	0.25
Setting range of overload releases		$\times I_u$	0,6 – 1
Short–circuit release fixed		$\times I_u$	14
Short–circuit release tolerance		%	± 20
Phase–failure sensitivity			IEC/EN 60947–4–1, VDE 0660 Part 102
Dimensions			
			PKZM0–...(+NHI–E–...–PKZ0)
Explanation			Motor–protective circuit–breaker tripping characteristic (high–capacity) compact starter,


Mounting position




Mounting position



Dimensions



Characteristic curve



Moeller GmbH, Hein-Moeller-Str. 7-11, D-53115 Bonn
 E-Mail: catalog@moeller.net, Internet: www.moeller.net, <http://catalog.moeller.net>
 Copyright 2006 by Moeller GmbH. Subject to modifications. HPL-C2006GB-INT V2.3