

Product information

90 42 340

- To join metal section sheets used in dry walling with a lock seam
- For U- and C-shaped sections with max 1.2 mm metal (2 x 0.6 mm)
- Minimum handforce required due to optimum lever transmission
- Pliers body: special tool steel, rolled, oil-hardened

Punch Lock Riveter



General

Article No.	90 42 340
EAN	4003773071884
Pliers	burnished
Handles	with multi-component grips
weight	966 g
Dimensions	340 x 96 x 19 mm

Technische Attribute

Capacity in millimetres	max. 1.2 (2 x 0.6)
-------------------------	--------------------

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC011914
ETIM 6.0	EC011914
proficl@ss 6.0	EAC043c008
UNSPSC 13.1	27112115

technical change and errors excepted



The punching tool is squeezed through the metal section sheets