

Straight-Through HDMI Plug to HDMI Receptacle Swivel Coupler




Product Overview

Precision engineered passive high speed HDMI coupler can be used to reposition the HDMI plug for a better fit, or adapt from one HDMI connection to another. Compatible with 3D and 4K display technologies, bi-directional A/V and data connectivity, and 120Hz refresh rates.

Specifications

Contact Resistance : 2Ω (Max.)
 Insulation Resistance : 5Ω (Min.)
 Hi-Pot Test : DC 100V/10ms

Diagram



PIN Assignment

P1	P2	P1	P2
1	1	13	13
3	3	14	14
2	2	15	15
4	4	16	16
6	6	17	17
5	5	18	18
7	7	19	19
9	9		
8	8		
10	10		
12	12		
11	11		
She11			She11

Part Number Table

Description	Part Number
Straight-Through HDMI Plug to HDMI Receptacle Swivel Coupler	24-11016

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

