

M1559CWT

L1: GPS, GLONASS, GALILEO, BEIDOU

Part #: 100-00118-01

Description

The M1559CWT is an active multi-frequency, high accuracy, GNSS antenna for the L1 GPS, Galileo, Beidou and GLONASS band. The antenna's excellent radiation pattern, exceptional out-of-band rejection, minimal group delay variation, and low noise figure ensures optimal performance of GNSS systems. It features a 5 m cable with an integrated SMA, SMB, or MCX connector (customer choice). The M1559CWT is ideal for applications requiring minimal integration effort or for retrofitting existing products and is rated IP67. The antenna is manufactured using automotive grade housing.

Passive Antenna Performance

Parameter	Specification
Frequency	1559-1610 MHz (L1, E1, B1, B1-2, G1)
Peak Efficiency	40%
Polarization	RHCP
Realized Gain	3.3 dB
Axial Ratio	Max 2.7 dB at the Zenith
VSWR	Max 2.3:1
Beamwidth	100°

Phase Center Variation

Maximum Phase Center Variation (mm)	
In azimuth plane	Max 10 mm
As low as 40 degree elevation	Max 10 mm
Between samples	Max 5 mm
Over frequency band	Max 10 mm

RF Specifications

Parameter	Specification
Conducted Gain	28 dB \pm 3 dB
Noise Figure	2 dB max
Voltage	3.0 - 5.0 V
Current	35 mA (max)
Out of Band Rejection	40 dB (typical)
Group Delay Variation	Less than 5 ns over GNSS bands
EMI Immunity Out of Band	30 V/m
ESD Circuit Protection	15 kV human body model air discharge




Features

- Low profile design
- Concurrent GNSS reception on L1: GPS, GLONASS, Galileo, Beidou
- Rugged IP67 rating
- Small form factor
- GIS, RTK and other high accuracy GNSS applications
- Low power consumption
- Minimal phase center variation over azimuth and elevation
- Negligible group delay variation
- Automotive grade housing

L1 Band Radiation Patterns


Maxtena's M1559CWT uses patented optimized microstrip technology which results in minimal dependence on frequency and features wide beamwidth, low axial ratio and radiation pattern symmetry across all desired frequencies in the L1 band.

RHCP Realized Gain [dBic] - Elevation Cuts




A 100 degree beamwidth ensures excellent hemispherical coverage.

RHCP Realized Gain [dBic] - Azimuth Cuts




Symmetric coverage even in low elevation enhances accuracy.

Axial Ratio [dB] - Zenith




Axial Ratio [dB] - Azimuth Cuts




Phase Center Variation

Maxtena's M1559CWT has minimal phase center variation over azimuth and elevation in the L1 band.



Phase Center Variation vs. Elevation in L1 band.




Phase Center Variation vs. Azimuth at Theta=30° in L1 band.

Excellent Group Delay Variation


Using GPS carrier phase to increase accuracy in GNSS applications has been proven reliable and has made mm-level accuracy possible. However, in resolving carrier phase ambiguity, it is necessary to make sure carrier phase is received and measured accurately and the effect of antenna and receiver on carrier phase is minimized. Maxtena's M1559CWT has a flat response over its specified GNSS band and has minimal group delay variation over frequency.

Filtering and LNA Performance

Maxtena's M1559CWT antenna has a flat response over the L1 band, with less than 1 dB variation over it. The superior out-of-band rejection ensures minimal interference.





< 2 ns group delay variation over L1-band.



Outstanding out-of-band rejection and less than 1dB fluctuation of in-band frequency response over L1-band.

Mechanical Specifications

Parameter	Specification
Weight	230 g (w/ cable) 167 g (w/o cable)
Size	75 x 70 x 23 mm
Cable	5 m RG174 standard
Connector	SMA, SMB, MCX (customer choice)
Mounting	Magnetic base (TNC version), fixed installation option
Ground Plane	150 mm x 150 mm
Color	Black
Operating Temperature Range	-40 to +105°C



Dimensions are in mm.