

PRO-ELEC



29" Tower Fan with Remote Control

Model: PEL01932 & PEL01933

Please read these instructions carefully before use and retain for future reference.

IMPORTANT SAFETY INFORMATION

- When using electrical appliances basic safety precautions should always be followed.
- Check that the voltage indicated on the rating plate corresponds with that of the local network before connecting the appliance to the mains power supply.
- This appliance is intended for domestic use only. It should not be used for commercial purposes.
- This appliance can be used by children aged from 8 years and above and persons with reduced physical, sensory or mental capabilities or lack of experience and knowledge if they have been given supervision or instruction concerning the use of the appliance in a safe way and understands the hazards involved.
- Children shall not play with this appliance.
- Cleaning and maintenance shall not be made by children without supervision.
- There are no user-serviceable parts in this product. Refer servicing to qualified personnel.
- Do not operate this fan with a damaged plug or cord, after a malfunction or after being dropped or damaged in any way.
- If the supply cord is damaged, it must be replaced by the manufacturer, its service agent or similarly qualified persons in order to avoid a hazard.
- Ensure that the fan is switched off before removing the guard.
- Do not insert anything through the grille when the fan is in use.
- Make sure that the fan is on a stable surface when operating.
- It is recommended to unplug the fan from the mains socket when not in use.

ASSEMBLY

- Unscrew the locking wheel from the base of main body.


Note: The UK 13A plug may not fit through the hole in the base therefore it is recommended to assemble the base around the cord.

- Align the two base halves guides together and combine into one base plate.
- Use the provided cable grip and screws to fix the cable in position to prevent it becoming trapped under the base.
- Position the base part to the bottom of the main body.
- Align the holes on the base plate to the two guide pins on the bottom of main body.
- Secure the base plate to the main body by refitting the locking wheel and tightening securely.
- Turn the fan into it's upright position ready to use.



OPERATION

- Connect the mains plug to a suitable outlet.
- Turn the fan on using the **ON/OFF** button.
- Select the desired speed by pressing the **SPEED** button, until the desired speed LED is lit.
- Turn “swing” (oscillation) on or off by pressing the **SWING** button.
- Pressing the **MODE** button will select either “general”, “normal” or “sleep” mode.
- Each mode provides a unique sequence of varying speed changes. Sleep mode gradually reduces the fan speed over time.
- Pressing timer will step through the various time limits from 30mins to 4hrs after which the fan will power off.



Remote Control

- The remote control can be used to adjust all of these features remotely by pressing the corresponding buttons on the remote control.
- Please remove the foil battery contact protector film before use.
- The remote requires a CR2025 coin cell battery.

CLEANING & MAINTENANCE

- Before cleaning, switch the fan off and unplug from the power supply.
- To clean the fan, use a soft cloth to wipe off any dust. If the fan is very dirty, use a damp cloth with some mild detergent then wipe dry.
- Do not use any chemicals, abrasives or solvents that could damage the fan.
- Keep the air vents at the rear of the main body free from dust or fluff - use a vacuum cleaner to clear these when necessary.

TECHNICAL SPECIFICATION

Power consumption	50W
Main voltage	220-240V~ 50Hz
Dimensions (HxWxD)	730 x 220 x 220mm
Weight	2.1kg



INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.

When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.



Made in China. PR2 9PP

Man Rev 1.1