



Main

Device short name	XCSL
Enclosure type	Water resistant enclosure for indoor/outdoor Dustproof enclosure for indoor/outdoor Ice/sleet proof enclosure for indoor/outdoor

Complementary

[In] rated current	10 A
[Us] rated supply voltage	24 V DC
Actuator	Key
Contact operation	Slow-break, break before make
Contacts type and composition	1 NO for staggered 2 NC
Depth	43.94 mm
Enclosure material	metal enclosure
Height	194.06 mm
Installation direction	Electromagnet connection: left Actuator supply: right
Key locking position	Front
Locking options description	With locking of actuator, unlocking by key operated lock
Number of poles	3
Permissible voltage	300 V AC
Pilot light	LED orange

Environment

Ambient air temperature for operation	-25...70 °C
IP degree of protection	IP67
NEMA degree of protection	NEMA 1/2/3/4/12

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	956 g
Package 1 Height	5 cm
Package 1 width	28 cm
Package 1 Length	6.2 cm
Unit Type of Package 2	S02
Number of Units in Package 2	10
Package 2 Weight	9.886 kg
Package 2 Height	15 cm
Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------