



Main

Range of product	PowerLogic
Product name	PowerTag A9 M63
Product or component type	Energy sensor
Poles	3P + N
Maximum current [Imax]	63 A
[Ib] basic current	10 A
[Ib] basic current	40 mA
Saturation current	130 A
Product specific application	Circuit monitoring Overload alarm Load monitoring Cost allocation Energy management
Product specific application	Acti9 Smartlink SI B Acti9 Smartlink SI D Acti9 PowerTag Link C Acti9 PowerTag Link Acti9 PowerTag Link HD
Range compatibility	Acti 9 iKQE RCBO Multi 9 C60 Multi 9 ID Multi 9 C32N Multi 9 C65 Acti 9 iID Acti 9 iID K Acti 9 iK60 Acti 9 iKQ Acti 9 K60 Acti 9 Reflex iC60 Acti 9 iC65 Acti 9 DT60 Acti 9 iC60 single terminal
Type of measurement	Voltage

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

	Power factor Active power Active energy Current
Accuracy class	Class 1 current conforming to IEC 61557-12 Class 0.5 voltage conforming to IEC 61557-12 Class 1 active power conforming to IEC 61557-12 Class 1 active energy conforming to IEC 61557-12 Class 1 power factor conforming to IEC 61557-12
Mounting location	Bottom
Mounting support	On circuit breaker
Product destination	Switchboard
Event management	Voltage loss with measured current at voltage loss
Transmission support medium	Radio frequency 2.4...2.4835 GHz conforming to IEEE 802.15.4
Maximum emission power	10 mW

Complementary

Mounting mode	By screws (terminals)
Electrical connection (voltage sensing & power supply)	Connector tooth
Cable cross section	1 rigid cable 1.5...16 mm ² 2 stranded cable 1.5...2.5 mm ² 2 rigid cable 1.5...2.5 mm ² 1 stranded cable 1.5...16 mm ²
Supply voltage	220...240 V AC, +/- 20 %, between phase and neutral 380...415 V AC, +/- 20 %, between phases
Network frequency	50 Hz 60 Hz
Maximum power consumption	2 VA
Standards	IEC 61557-12 IEC 61010-1 IEC 61010-2-030 IEC 61326-1 ETSI EN 300 328
Height	16.5 mm
Width	72 mm
Depth	43 mm
Net weight	35 g
Colour	White (RAL 9003)

Environment

Quality labels	CE
Directives	2014/53/EU - radio equipment directive
Operating altitude	0...2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C
Overvoltage category	III conforming to IEC 61010-1
Measurement category	Category III conforming to IEC 61010-2-030
IP degree of protection	IP20 conforming to IEC 60529
IK degree of protection	IK05
Pollution degree	3
Relative humidity	0...95 % at 45 °C conforming to IEC 60721-3-3
Vibration resistance	3M4 conforming to IEC 60721-3-3
Environmental characteristics	Dustproof class 3S3 conforming to IEC 60721-3-3 Salt mist class 3C2 conforming to IEC 60721-3-3

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	66 g
Package 1 Height	5 cm
Package 1 width	6 cm
Package 1 Length	8.5 cm
Unit Type of Package 2	S02
Number of Units in Package 2	48
Package 2 Weight	3.526 kg
Package 2 Height	15 cm
Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins