



### Main

Range of product	Square D Pumptrol
Product or component type	Float switch
Device application	Closed tank
Device short name	9037H
Product specific application	Liquid level control
Electrical circuit type	Power circuit
Quantity per set	Set of 1
Type of packing	Individual

### Complementary

Product destination	For closed tank
Device mounting	Screw-in bushing
Cable entry number	3 knock-outs for 1/2" conduit conforming to UL 508
Contacts type and composition	2 NO, snap action, DPST-DB, Form XX
Controlled fluid	Fresh water at specific gravity of 0.85 in or higher 0...220 °F Sea water at specific gravity of 0.85 in or higher 0...220 °F Hydraulic oil at specific gravity of 0.85 in or higher 0...220 °F Corrosive fluid at specific gravity of 0.85 in or higher 0...220 °F
Motor power kW	1.5 kW (2 hp) at 115 V AC, 1 phase 2.2 kW (3 hp) at 115 V AC, 3 phases 2.2 kW (3 hp) at 230 V AC, 1 phase 3.7 kW (5 hp) at 230 V AC, 3 phases 0.75 kW (1 hp) at 460 V AC, 3 phases 0.75 kW (1 hp) at 475 V AC, 3 phases 0.18 kW (0.25 hp) at 32 V DC 0.37 kW (0.5 hp) at 115 V DC 0.37 kW (0.5 hp) at 230 V DC
Electrical connection	Screw-clamp terminals, clamping capacity: 10 AWG
Contact operation	Contacts open on liquid rise
Float movement	2...5 in adjustable
Float position	Right

Float rod angle	45°
Short-circuit protection	20 A cartridge fuse, type gG
Local signalling	With external pointer
Materials in contact with fluid	Yellow brass Nitrile (Buna-N) or equivalent rubber Cast iron 316 stainless steel 304 stainless steel
Enclosure material	Polypropylene or equivalent
Operating position	Vertical position only
Electrical durability	100 cycles, operating rate <60 cyc/mn
Mechanical durability	300 cycles
Terminal block type	4 terminals
Maximum operating rate	60 cyc/mn
[UI] rated insulation voltage	575 V conforming to UL 508
Net weight	4.41 lb(US)
Terminals description ISO n°1	Line-load-load-line
Factory modification	Without
Kit composition	Float switch Float Rod

## Environment

Standards	UL 508 CE
Ambient air temperature for operation	-30...104 °C
Ambient air temperature for storage	-30...104 °C
NEMA degree of protection	NEMA 1 conforming to UL 50
Product certifications	CSA file LR25490 UL listed file E12158

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------