Safety Data Sheet (SDS)

CHIPQUIK®

www.chipquik.com

Tacky Flux

To comply with European CLP Regulation 1272/2008, US 29CFR 1910.1200 OSHA's Hazard Communication Standard, and Australian NOHSC: 1008 [2004] and ADG Code 7.4

1. PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: SYNONYMS: PART NUMBERS:	Chip Quik Tacky Flux Series: SMD291, SMD291NL, SMD4300, SMDLT, RMA591, RMA591NL, SMD491 Tack Flux, Gel Flux, Paste Flux SMD191, SMD191_3CC, SMD291, SMD291_3CC, SMD29130CC, SMD2915CC, SMD291NL, SMD4300TF10, SMD4300TF30, SMD291ST2CC6, SMD291ST8CC, SMD29175G, SMD291150G, SMD291NL75G, SMD291NL150G, SMD430075G, SMD4300150G, SMDLT75G, SMDLT150G, SMD1(flux), SMD1NL(flux), SMD2000(flux), SMD6000(flux), SMDST2CC4, RMA591, RMA591NL, SMD491, NC191, NC191-30CC, NC191-2CC6, SMDLT10
MANUFACTURER:	Chip Quik Inc.
ADDRESS:	931-3909 Witmer Rd., Niagara Falls, NY 14305 (USA) 3rd Floor, 207 Regent Street, London W1B 3HH (UK and EU)
	5-1480 Sandhill Dr., Ancaster, ON L9G 4V5 (Canada)
DUONE	42A Crimea Street, C/O A03886, Parramatta, NSW, 2150 (Australia)
PHONE: EMERGENCY PHONE:	(508) 477-2264 (800) 424-9300 (USA and Canada 24/7 CHEMTREC)
	+44 20 3868 7152 (UK and EU 24/7)
	+61 2 8607 7057 (Australia 24/7)
REVISION DATE:	2019/12/3
REVISION NUMBER:	3.8
REVISED BY:	Chip Quik Product Safety
PRODUCT USE:	Bonding solder joints in production and repair of circuit boards. This product is for industrial use only.

2. HAZARD IDENTIFICATION

Classified in accordance with European CLP Regulation 1272/2008

Acute Tox.	4
Skins Sens.	1
CHEMICAL NAME:	NA
CHEMICAL FAMILY:	Mixture
CHEMICAL FORMULA:	Proprietary
ROUTES OF ENTRY:	Inhalation, Ingestion, Skin/Eye Contact
TARGET ORGANS:	NA



GHS/CLP LABEL ELEMENTS:

Hazard statement(s)	
H302	Harmful if swallowed.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H332	Harmful if inhaled.
H334	May cause allergy or asthma symptoms or breathing difficulties if inhaled.
H335	May cause respiratory irritation.

Precautionary statement(s)P102Keep out of reach of children.P201Obtain special instructions before use.P202Do not handle until all safety precautions have been read and understood.P233Keep container tightly closed.P260Do not breathe dust/fume/gas/mist/vapor/spray.P262Do not get in eyes, on skin, or on clothing.

P264	Wash hands thoroughly after handling.
P270	Do not eat, drink, or smoke when using this product.
P271	Use in a well-ventilated area.
P272	Contaminated work clothing should not be allowed out of the workplace.
P273	Avoid release to the environment.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P284	In case of inadequate ventilation wear respiratory protection.
P301/P330/P331/P310	IF SWALLOWED: Rinse mouth. DO NOT induce vomiting. Immediately call a POISON CENTER/Doctor.
P303/P361/P352/P333/P313	IF ON SKIN (or hair): Take off immediately all contaminated clothing. Wash with soap & water. Get medical advice/attention if skin irritation or rash occurs or if you feel unwell.
P304/P340/312	IF INHALED: Remove victim to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if
1 304/1 340/312	you feel unwell.
P305/P351/338/P310	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue
	rinsing. Immediately call POISON CENTER/Doctor.
P308/P313	IF EXPOSED OR CONCERNED: Get medical advice/attention.
P342/P311	IF EXPERIENCING RESPIRATORY SYMPTOMS: Call POISON CENTER/Doctor.
P362	Take off contaminated clothing and wash it before reuse.
P391	Collect spillage.
P402/P404	Store in a dry place. Store in a closed container.
P405	Store locked up.
P501	Dispose of contents/container in accordance with local/regional/national/international regulations.
POTENTIAL HEALTH EFFE	CTS:
EYE CONTACT:	May cause moderate irritation. Do not allow material to come in contact with eyes.
SKIN CONTACT:	May cause moderate skin irritation

SKIN CONTACT: May cause moderate skin irritation. INHALATION: May cause irritation to the respiratory tract. INGESTION: Harmful if swallowed. May cause irritation to the mouth, throat, and stomach. May cause abdominal discomfort, nausea, vomiting, and/or diarrhea. CHRONIC: Not established.

MEDICAL CONDITIONS POSSIBLY AGGRAVATED BY EXPOSURE: Diseases of the blood-forming organs, kidneys, nervous and possibly reproductive systems. Occupational Asthma.

SECTION 2 NOTES:

Chip Quik Inc. does not recommend, manufacture, market, or endorse any of its products for human consumption.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Classified in accordance with European CLP Regulation 1272/2008

Hazardous Ingredients (1)	C.A.S. Number	Weight Percent	OSHA PEL	ACGIH TLV TWA	LD 50 Ingested	LD 50 Inhaled
			mg/m ³	mg/m ³	g/Kg	g/m ³
Modified Rosins (Rosin) (2)	8050-09-7	<45	NE	NE	NE	NE
Pine Oil Derivatives	8000-41-7	<5	NE	NE	NE	NE
(Terpineol)						
Mixed Carboxylic Acids	110-16-7	<4	NE	NE	NE	NE
(Maleic Acid) ⁽²⁾						

Non-Hazardous Ingredients	C.A.S. Number	Weight Percent	OSHA PEL mg/m ³	ACGIH TLV TWA mg/m ³	LD 50 Ingested g/Kg	LD 50 Inhaled g/m ³
Surfactants	NA	<4	NE	NE	NE	NE
Rheological Modifier	NA	<5	NE	NE	NE	NE
Solubilizer	NA	<37	NE	NE	NE	NE

SECTION 3 NOTES:

(1) Per 29 CFR 1910 the mixture has not been tested as a whole. All hazardous components, which comprise 1% of the mixture (0.1% carcinogenic), are listed. Percentages of individual components are not listed as this information is considered a trade secret.

(2) The identity of the specific chemical(s) is being withheld as a trade secret per 29 CFR 1910.1200. The hazardous properties of these ingredients are disclosed in this SDS.

4. FIRST-AID MEASURES

EYES: Flush with plenty of water, contact a physician. If contact lenses can be removed easily, flush eyes without contact lenses.

SKIN: Wash affected area with plenty of warm, soapy water. If irritation persists, seek medical attention.

INGESTION: Call a physician or Poison Control Center immediately. Do not induce vomiting.

INHALATION: Remove to fresh air. If not breathing, seek immediate medical attention.

5. FIREFIGHTING MEASURES

EXTINGUISHING MEDIA:

Dry chemical, foam

SPECIAL FIRE FIGHTING PROCEDURES:

Do not use water. Use NIOSH-approved self-contained Breathing Apparatus and full protective clothing if involved in a fire.

UNUSUAL FIRE AND EXPLOSION HAZARDS: This product does not present any unusual fire and explosion hazards.

6. ACCIDENTAL RELEASE MEASURES

ACCIDENTAL RELEASE MEASURES: If material spills or leaks use a spatula to collect and place it in a plastic or glass jar. Remove traces of residue using cloth rags or paper towels moistened with Isopropyl Alcohol. Exposure to spilled material may be irritating. Follow on-site personal protective equipment recommendations.

ENVIRONMENTAL PRECAUTIONS: Avoid release to the environment. Collect spillage.

SECTION 6 NOTES:

See Sections 2, 4, and 7 for additional information.

7. HANDLING AND STORAGE

HANDLING/STORAGE: Keep containers tightly closed when not in use. Use care to avoid spills. Avoid inhalation of fumes or dust. Avoid contact with eyes, skin, and clothing. Store in a closed corrosive resistant container, with corrosive resistant liner, in cool dry place. Wear appropriate personal protective equipment when working with or handling. Always wash hands thoroughly after handling this product. Dispose of following Federal, State/Provincial, and Local regulations.

OTHER PRECAUTIONS: Empty containers may retain product residues in vapor, liquid, and/or solid form. All labeled hazard precautions should be observed.

WORK HYGIENIC PRACTICES: Cosmetics/Food/Drink/Tobacco should not be consumed or used in work areas. Always wash hands after handling material and before applying or using cosmetics/food/drink/tobacco.

SECTION 7 NOTES:

For industrial use only. Keep out of reach of children. Not for internal consumption.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Occupational Exposure Limit Values:

Rosin flux fumes (as total resin acids) MEL: 0.05 mg/m³ 8h TWA. MEL: 0.15 mg/m³ 15 min.

Extraction is necessary to remove fumes evolved during reflow.

Also see section 3.

ENGINEERING CONTROLS: Use only with production equipment designed for use with tacky flux.

VENTILATION: Provide sufficient mechanical (general and/or local exhaust) ventilation to maintain exposure below TLVs.

RESPIRATORY PROTECTION: A (US: NIOSH; EU: EN 140:1998, EN 14387:2004 A)-approved air-purifying respirator with fume/organic chemical cartridge should be worn when airborne concentrations may be exceeded. General and local exhaust ventilation is the preferred means of protection.

EYE PROTECTION: Use with appropriate eye protection: Goggles or face shield (EU: EN 166-S 3 9).

SKIN PROTECTION: Protective gloves should be worn when the possibility of skin contact exists (EU: EN 374-1:2003).

PROTECTIVE CLOTHING OR EQUIPMENT: Work clothes should be worn and laundered in accordance with current Lead (Pb) standards (US: OSHA).

WORK HYGIENIC PRACTICES: Cosmetics/Food/Drink/Tobacco should not be consumed or used in areas where solder products may be used. Always wash hands after handling soldering products and before applying or using cosmetics/food/drink/tobacco.

OTHER: Maintain eye wash stations in work areas. Avoid the use of contact lenses in high fume areas. Clean protective equipment regularly. Clean up spills immediately.

9. PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE: ODOR: ODOR THRESHOLD: pH as SUPPLIED: MELTING POINT: FREEZING POINT: INITIAL BOILING POINT: BOILING RANGE: FLASH POINT: EVAPORATION RATE: FLAMMABILITY (solid): UPPER/LOWER FLAMMABILITY: UPPER/LOWER EXPLOSIVE LIMITS:	Clear, White, or Yellow to Dark Amber gel Mild odor NE N/A NE NE NE NE NE NE NE NE NE NE
VAPOR PRESSURE (mmHg): VAPOR DENSITY (AIR = 1):	N/A N/A

RELATIVE DENSITY: SOLUBILITY IN WATER: PARTITION COEFFICIENT (n-octanol/water): AUTOIGNITION TEMPERATURE: DECOMPOSITION TEMPERATURE: VISCOSITY:

10. STABILITY AND REACTIVITY

STABILITY: CONDITIONS TO AVOID (STABILITY): INCOMPATIBILITY (MATERIAL TO AVOID): HAZARDOUS DECOMPOSITION/BY-PRODUCTS: POSSIBILITY OF HAZARDOUS REACTIONS:

Stable NE Oxidizing materials, acids, hydrogen peroxide, bases Harmful organic fumes and toxic oxide fumes may form at elevated temperatures. NE

11. TOXICOLOGICAL INFORMATION

INHALATION:

This product does not present a risk at ambient temperatures. The flux fumes evolved during soldering will irritate the nose, throat and lungs. Repeated or prolonged exposure to flux fumes may cause an allergic affect which may lead to occupational asthma.

NE

NE

NE

NF

N/A

Partially

SKIN:

Contact with flux fumes and flux residues may cause irritation and sensitization.

EYES:

Flux fumes may cause irritation.

ACUTE TOXICITY:

Product/Ingredient Name	Result	Species	Dose	Exposure
Rosin	LD50 Oral	Rat	7600 mg/kg	-
Terpineol	LD50 Oral	Rat	2000 mg/kg	-
	LD50 Inhalation	Rat	4.76 mg/l	4 hours
	LD50 Dermal	Rat	2000 mg/kg	-
Maleic acid	LD50 Oral	Rat	708 mg/kg	Remarks: Behavioral: Convulsions or effect on seizure threshold. Behavioral: Muscle weakness. Gastrointestinal: Ulceration or bleeding from stomach.
	LD50 Inhalation LD 50 Dermal	Rat Rabbit	720 mg/m ³ 1560 mg//kg	1 hour Remarks: Behavioral: Tremor

SKIN CORRISION/IRRITATION:

Not available

SERIOUS ETE DAMAGE/IRRITATION:						
Product/Ingredient	Result	Species	Score	Exposure	Observation	
Name						
Maleic acid	Eyes – Severe Irritant	Rabbit	-	2 minutes 1 percent	-	

RESPIRATORY OR SKIN SENSITIZATION: NE GERM CELL MUTAGENICITY: Not available CARCINOGENICITY: OSHA: N/A ACGIH: N/A NTP: N/A IARC: N/A **REPRODUCTIVE TOXICITY:** Not available STOT-SINGLE EXPOSURE: Product/Ingredient Name Route of exposure Category Target organs Maleic acid Category 3 Not applicable Respiratory tract irritation

STOT-REPEATED EXPOSURE: ASPIRATION HAZARD:

NE NF

12. ECOLOGICAL INFORMATION

TOXICITY:

Product/Ingredient Name	Result	Species	Exposure
Rosin	Acute LC50 60.3 mg/I Fresh water	Acute LC50 60.3 mg/l Fresh water Brachydanio rerio (zebra fish) 96 hours	
Terpineol	Acute LC50 62.80 mg/l Fresh water	Danio rerio (zebra fish)	96 hours
	Acute LC50 68 mg/l Marine water	Algae – Pseudokirchneriella subcapitata (green algae)	72 hours
Maleic acid	Acute EC50 316200 µg/l Fresh water	Daphnia - Daphnia magna - Larvae	48 hours
	Acute LC50 5000 µg/l Fresh water	Fish - Pimephales promelas	96 hours

PERSISTENCE AND DEGRADIBILITY: NE BIOACCUMULATIVE POTENTIAL:

Product/Ingredient Name	LogPow	BCF	Potential
-------------------------	--------	-----	-----------

Rosin	1.9 to 7.7	-	High
Terpineol			NE
Maleic acid	-1.3	-	Low

MOBILITY IN SOIL:	NE
RESULT OF PBT and vPvB ASSESSMENT:	Not applicable
OTHER ADVERSE EFFECTS:	NE

13. DISPOSAL CONSIDERATIONS

WASTE DISPOSAL METHOD: Scrap and waste should be recycled or stored in a dry, sealed container for later disposal. Disposal must be in accordance with Federal, State/Provincial, and Local Regulations.

14. TRANSPORT INFORMATION

Transport in accordance with applicable regulations and requirements.

UN Number:	Not available
UN Proper Shipping Name:	Not available
Packaging Group:	Not applicable
Environmental Hazards:	None
TRANSPORT HAZARD CLASSES:	
US DOT Hazardous Material Classification:	Non-Hazardous
Water Transportation:	Non-Hazardous
IATA Hazardous Material Classification:	Non-Hazardous

15. REGULATORY INFORMATION

ADR Road Regulations

IMDG Sea Regulations

ADG Land Transportation

All ingredients used to manufacture this product are listed on the EPA TSCA Inventory. Finished product is not listed on the EPA TSCA Inventory.

Not regulated

Not regulated

Not regulated

U.S. FEDERAL REGULATIONS:	Not regulated
STATE REGULATIONS:	Not regulated
INTERNATIONAL REGULATIONS:	Not regulated
AUSTRALIAN REGULATIONS:	Not regulated

16. OTHER INFORMATION

LEGEND:

ACGIH	American Conference of Governmental Industrial Hygienists
ADG	Australian Dangerous Goods Code
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
AICS	Australian Inventory of Chemical Substances
BCF	Bioconcentration factor
C.A.S.	Chemical Abstract Service
CLP	Classification, Labeling and Packaging
DOT	Department of Transportation
EC	Effective Concentration
EPA	Environmental Protection Agency
GHS	Global Harmonized System
HMIS	Hazardous Material Identification System
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods Code
LC	Lethal Concentration
LD	Lethal Dose
NA	Not available
NE	Not established
NIOSH	National Institute for Occupational Safety & Health
NOEC	No observed effective concentration
NOHSC	National Occupational Health and Safety Commission (Australia)
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
PEL	Permissible Exposure Limit
Pow	Octanol water partition coefficient
SDS	Safety Data Sheet
STEL	Short-Term Exposure Limit
STOT	Specific target organ toxicity
TLV	Threshold Limit Value
TSCA	Toxic Substance Control Act
TWA:	Time Weighted Average
US DOT:	United States Department of Transportation

PREPARATION INFORMATION:

This update supersedes all previously released documents.

DISCLAIMER:

The information and recommendations contained within this publication have been compiled from sources believed to be reliable and to represent the best information available to Chip Quik at the time of issue. No warranty, guarantee, or representation is made by Chip Quik nor does Chip Quik assume any responsibility in connection there within; nor can it be assumed that all acceptable safety measures or other safety measures may not be required under particular or exceptional conditions or circumstances. The data on this Safety Data Sheet relates only to this product and does not relate to use with any other material or in any process. All chemical products should be used only by, or under the direction of, technically qualified personnel who are aware of the hazards involved and necessity for reasonable care in handling. Hazard communication regulations require that employees must be trained on how to use a Safety Data Sheet as a source for hazard information.

Copyright © 1994-2019 Chip Quik® Inc.