

May, 2017

## 3M™ Scotch® Industrial Box Sealing Tape 371

### Product Description

Scotch® Box Sealing Tape 371 is an industrial packaging tape used for box sealing, splicing, recoupage and other packaging applications. This product has a conformable backing and a consistent pressure sensitive hot melt synthetic rubber adhesive system.

### Product Features

- Adheres instantly to a variety of surfaces.
- Edge tear and split resistance.
- Good adhesion to fiberboard.
- Roll to roll consistency increases productivity for improved unit costs.
- Meets FDA requirements for indirect food contact.



# 3M™ Scotch® Industrial Box Sealing Tape 371

## Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

## Typical Physical Properties

Property	Values		Method	Substrate
Color	Blue, clear, green, orange, red, tan, yellow, and white			
Total Tape Thickness	0.046 mm	1.8 mil	ASTM D3652	
Backing Thickness	0.03 mm	1.2 mil	ASTM D3652	
Backing	Biaxially oriented polypropylene			
Adhesive	Pressure sensitive hot melt rubber-resin			
Holding Power	3,500+ min		ASTM D3654	Fiberboard

## Typical Performance Characteristics

Property	Values		Method	Dwell/Cure Time	Dwell Time Units	Substrate	Backing	Notes
180° Peel Adhesion	40 oz/in	43.8 N/100mm	ASTM D3330	72	hr	Stainless Steel	2 mil Aluminum Foil	12 in/min (305 mm/min)
Elongation at Break	160 %		ASTM D3759					

Tensile Strength	Test Condition
385 N/100mm	22 lb/in Machine Direction
771 N/100mm	44 lb/in Cross Direction

Property: Tensile Strength  
Method: ASTM D3759

# 3M™ Scotch® Industrial Box Sealing Tape 371

## Available Sizes

Property	Values		Attribute Modifier
Standard Roll Length	50, 100, 914, 1500 m	55, 109, 1000, 1641 yd	
Standard Width	36, 42, 48, 72 mm	1.4, 1.7, 1.9, 2.8 in	
Core Size	76.2 mm	3 in	ID

## Handling/Application Information

### Application Techniques

An extensive line of application equipment including hand held manual dispensers and semi-automatic and fully automatic equipment is available. Application of Scotch® Box Sealing Tape 371 is most easily accomplished at room temperature. At colder temperatures, approaching 32°F (0°C), the adhesive becomes more firm. Once applied, Scotch® Tape 371 performs well throughout the normal temperature ranges typically encountered by packaged products in shipping and storage environments.

### Storage and Shelf Life

Store in a clean, dry place. Temperature of 40-80°F (4-26°C) and 40 to 50% relative humidity are recommended. To obtain best performance, use this product within 18 months from date of manufacture.

## Industry Specifications

Meets FDA requirements for indirect food contact.

## Trademarks

Scotch is a registered trademark of 3M.

## References

Property	Values
3m.com Product Page	<a href="https://www.3m.com/3M/en_US/company-us/all-3m-products/-/Scotch-Box-Sealing-Tape-371?N=5002385+3293242350&amp;rt=rud">https://www.3m.com/3M/en_US/company-us/all-3m-products/-/Scotch-Box-Sealing-Tape-371?N=5002385+3293242350&amp;rt=rud</a>
Safety Data Sheet (SDS)	<a href="https://www.3m.com/3M/en_US/company-us/SDS-search/results/?gsaAction=msdsSRA&amp;msdsLocale=en_US&amp;co=ptn&amp;q=371">https://www.3m.com/3M/en_US/company-us/SDS-search/results/?gsaAction=msdsSRA&amp;msdsLocale=en_US&amp;co=ptn&amp;q=371</a>

## Family Group

	371	371+
Color	Blue, clear, green, orange, red, tan, yellow, and white	Clear
Total Tape Thickness (mm)	0.046	0.048
Backing Thickness (mm)	0.03	0.03

Table continued on next page

**Family Group (continued)**

	371	371+
Backing	Biaxially oriented polypropylene	Biaxially oriented polypropylene
Adhesive	Pressure sensitive hot melt rubber-resin	Pressure sensitive hot melt rubber-resin

**ISO Statement**

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

**Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M’s control and uniquely within user’s knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer’s application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M’s option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

