

Specifications:

Mechanical:

Maximum Operating Force	: 40gf
Maximum Stroke	: 3.9mm (stem height 5.3mm) 2.6mm (stem height 3.8mm)
Operating Temperature	: -10°C to +60°C
Storage Temperature	: -20°C to +70°C
External Height	: 2.3mm
External Width	: 4.7mm
External Depth	: 3.8mm

Electrical:

Electrical Life	: 100,000 Cycles
Rating	: 1mA, 5V DC
Maximum Contact Resistance	: 1Ω
Minimum insulation resistance	: 100MΩ at 100V DC
Dielectric Strength	: 100V AC/1minute
Rate Of Operating	: 20 to 25 operation per minute
Contact Arrangement	: 1 pole
Contact Configuration	: SPST-NO

Material:


Cover(1)	: LCP High-temperature thermoplastic Colour : Black
Cover(2)	: LCP High-temperature thermoplastic Colour : Black
Stem	: LCP High-temperature thermoplastic Colour : Black
Contact	: Stainless with silver cladding
Base	: PA9T High-temperature thermoplastic Colour : Black
Contact disc	: Stainless with silver cladding
Terminal	: Brass with silver plated

Soldering Process:

For best results, please follow these recommendations:


Hand Soldering	: Use a soldering iron of 30W, controlled at 608°F (350°C) approximately maximum 5 seconds while applying
Reflow Soldering	: When applying reflow soldering, the peak temperature or the reflow oven should be set to 260°C maximum

MCATE-1




Dimensions : Millimetres (Inches)

Reflow Temperature Profile:



MCATE-2



Part Number Table

Description	Part Number
Switch, Card Detect, Top Actuated	MCATE-1-V
Switch, Card Detect, Top Actuated	MCATE-2-V

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.