


**RoHS  
Compliant**



## Specifications

Current Rating	: 20Amp 600V
Wire Range	: 12 AWG to 22 AWG
Stripped Length	: 4.5mm to 5.5mm
Continuous Working Temp.	: 105°C Max.
Operation Temperature	: -30°C to +85°C
Insulation Withstands Volt	: AC2000V min
Insulation Resistance	: >2,000MΩ DC500V

## Diagram



Dimensions : Millimetres

Part Number	A	B
MC001819	14mm	8.2mm
MC001820	22.2mm	16.4mm
MC001821	30.4mm	24.6mm
MC001822	79.6mm	73.8mm

No.	Material		Plating/Finish
1	Insulating Body	PA66(UL94-V2)	-
2	Wire Protector	SUS301	-
3	Screw	Steel	Zinc Plate
4	Cage Clamp	Brass	Ni Plate

## Part Number Table

Description	Part Number
H Type Dual-Pole Terminal Block, 20A, 600V, 8.2mm, 2×2 Poles, White	MC001819
H Type Dual-Pole Terminal Block, 20A, 600V, 8.2mm, 3×2 Poles, White	MC001820
H Type Dual-Pole Terminal Block, 20A, 600V, 8.2mm, 4×2 Poles, White	MC001821
H Type Dual-Pole Terminal Block, 20A, 600V, 8.2mm, 10×2 Poles, White	MC001822

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.