

November 1996

Quad, 3.5MHz, Operational Amplifier
Features

- Slew Rate 1.6V/ μ s
- Bandwidth 3.5MHz
- Input Voltage Noise 9nV/ $\sqrt{\text{Hz}}$
- Input Offset Voltage 0.5mV
- Input Bias Current 60nA
- Supply Range $\pm 2\text{V}$ to $\pm 20\text{V}$
- No Crossover Distortion
- Standard Quad Pinout



Applications

- Universal Active Filters
- D3 Communications Filters
- Audio Amplifiers
- Battery-Powered Equipment

Ordering Information

PART NUMBER	TEMP. RANGE ($^{\circ}\text{C}$)	PACKAGE	PKG. NO.
HA1-4741-2	-55 to 125	14 Ld CERDIP	F14.3
HA1-4741-5	0 to 75	14 Ld CERDIP	F14.3
HA3-4741-5	0 to 75	14 Ld PDIP	E14.3
HA9P4741-9	-40 to 85	16 Ld SOIC	M16.3

Pinouts

 HA-4741
 (PDIP, CERDIP)
 TOP VIEW

 HA-4741
 (SOIC)
 TOP VIEW


Absolute Maximum Ratings

$T_A = 25^\circ\text{C}$ Unless Otherwise Stated	
Supply Voltage Between V+ and V- Terminals	40V
Differential Input Voltage	30V
Input Voltage	V_{SUPPLY}
Output Short Circuit Duration (Note 3)	Indefinite

Operating Conditions

Temperature Range:	
HA-4741-2.	-55°C to 125°C
HA-4741-5.	0°C to 75°C
HA-4741-9.	-40°C to 85°C

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.

NOTES:

1. Maximum power dissipation, including output load, must be designed to maintain junction temperature below 175°C for the ceramic package, and below 150°C for the plastic packages.
2. θ_{JA} is measured with the component mounted on an evaluation PC board in free air.
3. One amplifier may be shorted to ground indefinitely.

Electrical Specifications $V_{\text{SUPPLY}} = \pm 15\text{V}$, Unless Otherwise Specified

PARAMETER	TEST CONDITIONS	TEMP. (°C)	HA-4741-2			HA-4741-5			(NOTE 4) HA-4741-9	MAX	UNITS
			MIN	TYP	MAX	MIN	TYP	MAX			
INPUT CHARACTERISTICS											
Offset Voltage		25	-	0.5	3	-	1	5	5	mV	
		Full	-	4	5	-	4	6.5	8.5	mV	
Average Offset Voltage Drift		Full	-	5	-	-	5	-		$\mu\text{V}/^\circ\text{C}$	
Bias Current		25	-	60	200	-	60	300	300	nA	
		Full	-	-	325	-	-	400	400	nA	
Offset Current		25	-	15	30	-	30	50	50	nA	
		Full	-	-	75	-	-	100	100	nA	
Common Mode Range		Full	± 12	-	-	± 12	-	-	-	V	
Differential Input Resistance		25	-	0.5	-	-	0.5	-	-	$\text{M}\Omega$	
Input Voltage Noise	$f = 1\text{kHz}$	25	-	9	-	-	9	-	-	$\text{nV}/\sqrt{\text{Hz}}$	
TRANSFER CHARACTERISTICS											
Large Signal Voltage Gain	$V_{\text{OUT}} = \pm 10\text{V}$, $R_L = 2\text{k}\Omega$	25	50	100	-	25	50	-	-	kV/V	
		Full	25	-	-	15	-	-	-	kV/V	
Common Mode Rejection Ratio		25	80	95	-	80	95	-	-	dB	
		Full	74	-	-	74	-	-	-	dB	
Channel Separation (Note 5)		25	66	69	-	66	69	-	-	dB	
Small Signal Bandwidth		25	2.5	3.5	-	2.5	3.5	-		MHz	
OUTPUT CHARACTERISTICS											
Output Voltage Swing	$R_L = 10\text{k}\Omega$	Full	± 12	± 13.7	-	± 12	± 13.7	-	-	V	
Output Voltage Swing	$R_L = 2\text{k}\Omega$	Full	± 10	± 12.5	-	± 10	± 12.5	-	-	V	
Full Power Bandwidth (Notes 6, 7)		25	-	25	-	-	25	-	-	kHz	
Output Current	$V_{\text{OUT}} = \pm 10\text{V}$	Full	± 5	± 15	-	± 5	± 15	-	-	mA	
Output Resistance		25	-	300	-	-	300	-	-	Ω	
TRANSIENT RESPONSE $R_L = 2\text{k}\Omega$, $C_L = 50\text{pF}$											
Rise Time	$V_{\text{OUT}} = \pm 200\text{mV}$	25	-	75	140	-	75	140	140	ns	
		25	-	25	40	-	25	40	40	%	

Electrical Specifications $V_{SUPPLY} = \pm 15V$, Unless Otherwise Specified **(Continued)**

PARAMETER	TEST CONDITIONS	TEMP. (°C)	HA-4741-2			HA-4741-5			(NOTE 4) HA-4741-9	UNITS
			MIN	TYP	MAX	MIN	TYP	MAX		
Slew Rate	$V_{OUT} = \pm 5V$	25	-	± 1.6	-	-	± 1.6	-	-	$V/\mu s$
POWER SUPPLY CHARACTERISTICS										
Supply Current		25	-	4.5	5	-	5	7	7	mA
Power Supply Rejection Ratio	$\Delta V_S = \pm 5V$	Full	80	95	-	80	95	-	-	dB

NOTES:

4. Typical and Minimum specifications for the -9 version are the same as those for the -5 version.
5. Referred to input; $f = 10\text{kHz}$, $R_S = 1\text{k}\Omega$, $V_{IN} = 100\text{mV}_{PEAK}$.
6. $V_{OUT} = \pm 10V$, $R_L = 2\text{k}\Omega$.
7. Full power bandwidth guaranteed based upon slew rate measurement: $FPBW = S.R./2\pi V_{PEAK}$.


Test Circuit and Waveforms

FIGURE 1. SMALL AND LARGE SIGNAL TEST CIRCUIT




FIGURE 2. LARGE SIGNAL RESPONSE









FIGURE 3. SMALL SIGNAL RESPONSE

Schematic Diagram**Typical Performance Curves** $V_{SUPPLY} = \pm 15V$, $T_A = 25^{\circ}\text{C}$, Unless Otherwise Specified


Typical Performance Curves $V_{SUPPLY} = \pm 15V$, $T_A = 25^\circ C$, Unless Otherwise Specified (Continued)

FIGURE 8. INPUT NOISE vs FREQUENCY




FIGURE 9. SMALL SIGNAL BANDWIDTH AND PHASE MARGIN vs LOAD CAPACITANCE




FIGURE 10. MAXIMUM OUTPUT VOLTAGE SWING vs LOAD RESISTANCE




FIGURE 11. INPUT BIAS AND OFFSET CURRENT vs TEMPERATURE




FIGURE 12. POWER CONSUMPTION vs TEMPERATURE

Die Characteristics**DIE DIMENSIONS:**

87 mils x 75 mils x 19 mils
 $2210\mu\text{m} \times 1910\mu\text{m} \times 483\mu\text{m}$

METALLIZATION:

Type: Al, 1% Cu
Thickness: $16\text{k}\text{\AA} \pm 2\text{k}\text{\AA}$

PASSIVATION:

Type: Nitride
Thickness: $7\text{k}\text{\AA} \pm 0.7\text{k}\text{\AA}$

SUBSTRATE POTENTIAL (Powered Up):

V-

TRANSISTOR COUNT:

72

PROCESS:

Junction Isolated Bipolar/JFET

Metallization Mask Layout

HA-4741

