

ESD Spray Bottle

8oz



RoHS
Compliant



Description

All of our Cleanroom static dissipative pump action spray bottles have an average surface resistivity of 10^9 to 10^{10} Ohms.

The spray bottle will dissipate a charge of plus or minus 5000 volts in less than 2 seconds at 40% relative humidity. By their chemical nature, they will not have any chemical reactivity with solvents such as TCE or alcohol. Meets ANSI/ESDA S20.20.

The bottles are manufactured from polyethylene utilizing a concentrate that does not contain any Exthoxylated Tertiary Amine.

Features

- 8oz ESD mister bottle
- Leak resistant
- Easy to fill

Part Number Table

Description	Part Number
ESD Spray Bottle, 8oz	146-0023

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

