

LED PIPE High OUTPUT

LED PIPE G2 L1500 HIGH OUTPUT NW

0051050



Product features

- LED T5 replacement batten, high output range: more lumens per meter with efficiency up to 125 lum/watt, seamless linking (up to 10M), Ideal for direct lighting such as under cabinet or in kitchens, 150 degree beam angle, includes switch, includes 0.30m stripped cable, white polycarbonate body, includes standard and tilting brackets



PRODUCT OVERVIEW

IPC Code	0051050
Product name	LED PIPE G2 L1500 HIGH OUTPUT NW
Technology	LED
Housing	PC Polycarbonate
General application	Residential & Consumer,
Certifications	EUNEW009
ETIM Class	EC000109
E-number SE	7505157
Fixture luminous flux (lm)	2500
Luminaire efficacy (lm/W)	120
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Variation Initial (SDCM)	6
Photobiological Risk Group	RG0
Total power consumption (W)	21
Electrical protection	Class II
Dimmable	N
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	5410288510507
Lamps	Yes

DATA TABLE

General data

IPC Code	0051050
Product name	LED PIPE G2 L1500 HIGH OUTPUT NW
Technology	LED
Housing	PC Polycarbonate
General application	Residential & Consumer,
Operating temperature range (°C)	-20°C - 40°C

LED PIPE High OUTPUT

LED PIPE G2 L1500 HIGH OUTPUT NW
0051050

Certifications	EUNEW009
ETIM Class	EC000109
E-number SE	7505157

Optical data

Fixture luminous flux (lm)	2500
Luminaire efficacy (lm/W)	120
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Variation Initial (SDCM)	6
Beam angle (Rated) (°)	150
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	21
Mains voltage (V)	220-240V~
Lamp power factor	0.9
Electrical protection	Class II
Dimmable	N
Drive current (mA)	180
Inrush Current (A)	2
Inrush Duration (µs)	50
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	10
Max. Luminaires per 13A C Breaker	10
Max. Luminaires per 16A C Breaker	10
Max. Luminaires per 20A C Breaker	10
Max. Luminaires per 10A B Breaker	10
Max. Luminaires per 13A B Breaker	10
Max. Luminaires per 16A B Breaker	10
Max. Luminaires per 20A B Breaker	10

Lifetime data

Lumen maintenance - L70 B50	30000
-----------------------------	-------

Physical data

Housing colour	White
IP rating	IP20
IK rating	IK02
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	1500
Nominal Product Width (mm)	24
Nominal Product Height (mm)	35
Weight (kg)	0.326

Packaging


Single packaging type	Carton
Product EAN number	5410288510507

LED PIPE High OUTPUT


LED PIPE G2 L1500 HIGH OUTPUT NW
0051050

Packaging single length / height (cm)	4.1
Packaging single width (cm)	3.2
Packaging single depth (cm)	162.0
DUN14 (outer)	15410288510504
Units per outer package	20
Packaging outer length / height (cm)	164.0
Packaging outer width (cm)	18.5
Packaging outer depth (cm)	19.0

PHOTOMETRY





TECHNICAL DRAWINGS




LED PIPE High OUTPUT LED PIPE G2 L1500 HIGH OUTPUT NW 0051050


SYLVANIA 0051050


 This luminaire contains built-in LED lamps

 } LED


The lamps cannot be changed in the luminaire.

874/2012 

 This luminaire contains built-in LED lamps

 } LED

The lamps cannot be changed in the luminaire.

SYLVANIA 0051050 

874/2012