

# RV45

## DC Centrifugal fan

**ebmpapst**

the engineer's choice



### Highlights:

- Quiet-running: Exemplary noise level of just 49 dB(A)
- Very dynamic and top performance: Up to 100 rev/ms
- Static pressure increase of over 5,000 Pa.
- Intelligent design: Highly compact outer dimensions and weighs only 135 grams (4.8 oz)

### Nominal data


Type	Item number	Air flow l/min	Air flow cfm	Nominal voltage VDC <sup>-1</sup>	Voltage range *	Sound pressure ** dB(A)	with Hall sensors without Hall sensors	Power consumption W	Nominal speed rpm	Temperature range °C	Service life L <sub>10</sub> (20°C) ebm-papst standard Service life L <sub>10</sub> (T <sub>max</sub> ) ebm-papst standard	Life expectancy L <sub>10</sub> IPC (25°C)	Characteristic curve
RV45-3/14	9593505001	410	14.5	24	7...30	49	■	43	40,000	-20...+70	22,500/7,500	50,000	①
RV45-3/14S	9593505002	410	14.5	24	7...30	49	□	43	40,000	-20...+70	22,500/7,500	50,000	①

\* Depending on the customer's actuation electronics.

\*\* Measured at 1,000 Pa and a distance of 1 m above the intake side.

Blower with hose and standard resistor with 4 mm inside diameter, a length of 40 mm and a 45° outlet angle.

All dimensions in mm.



Breathing device applications demand fans with highly dynamic characteristics. A high pressure is required at the start of the breathing sequence and a low pressure at the end. In practice, that means pressure fluctuations between 400 Pa and 2000 Pa. With a centrifugal impeller, the flow quantity and delivery pressure increase with increasing speed. The high nominal speed of 40,000 rpm thus produces dynamic power output – with a compact design.

for plastic screw Ø 2,5  
maximum screw depth 6 mm

