Note: This datasheet may be out of date.

Please download the latest datasheet of GCM1885C1J222JA16# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=GCM1885C1J222JA16%23

"#" indicates a package specification code.

# GCM1885C1J222JA16#


















< List of part numbers with package codes > GCM1885C1J222JA16J GCM1885C1J222JA16D



### Appearance & Shape







### References

Packaging	Specifications	Minimum Order Quantity
J	330mm Paper Tape	10000
D	180mm Paper Tape	4000

Mass (typ.)		
1 piece	6.3mg	
φ180mm Reel	144g	

1 of 4

#### Attentior

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



GCM1885C1J222JA16#

Note: This datasheet may be out of date.

Please download the latest datasheet of GCM1885C1J222JA16# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=GCM1885C1J222JA16%23

"#" indicates a package specification code.



# **Specifications**

Length	1.6±0.1mm
Width	0.8±0.1mm
Thickness	0.8±0.1mm
Capacitance	2200pF ±5%
Distance between external terminals g	0.5mm min.
External terminal size e	0.2 to 0.5mm
Operating Temperature Range	-55°C to 125°C
Rated Voltage	63Vdc
Size code in inch(mm)	0603 (1608M)
тс	0±30ppm/°C
Temperature characteristics (complied standard)	C0G(EIA)
Temperature range of temperature characteristics	25°C to 125°C

2 of 4

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



#### Note: This datasheet may be out of date. Please download the latest datasheet of GCM1885C1J222JA16# from the official website of Murata Manufacturing Co., Ltd.


"#" indicates a package specification code.

# GCM1885C1J222JA16#




### Characteristic Data


The charts below may show another part number which shares its characteristics.








GCM1885C1J222JA16 R DCOV, 25degC



GCM1885C1J222JA16 C-DC bias capchange, 25.0degC, AC1V



GCM1885C1J222JA16 C-AC Voltage capchange, DCOV, 25.0d

3 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering




Note: This datasheet may be out of date.


Please download the latest datasheet of GCM1885C1J222JA16# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=GCM1885C1J222JA16%23

"#" indicates a package specification code.

# GCM1885C1J222JA16#





GCM1885C1J222JA16 S21 DCOV, 25degC

4 of 4

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

