

4200UV

# Safety Data Sheet

## Section 1: Identification

### Product Identifier and Other Means of Identification

**Product Identifier:** 4200UV**Other Means of Identification:** UV Curable Conformal Coating**Related Part #** 4200UV-945ML, 4200UV-3.78L

### Recommended Use and Restriction on Use

**Use:** UV Curable Conformal Coating**Uses Advised Against:** Industrial use only.

### Details of Manufacturer or Importer

**Manufacturer**MG Chemicals  
1210 Corporate Drive  
Burlington, Ontario L7L 5R6  
CANADAMG Chemicals (Head Office)  
9347-193 Street  
Surrey, British Columbia V4N 4E7  
CANADA**☎** +1-800-340-0772**FAX** +1-800-340-0773**E-MAIL** [support@mgchemicals.com](mailto:support@mgchemicals.com)**WEB** [www.mgchemicals.com](http://www.mgchemicals.com)**☎** +1-905-331-1396**FAX** +1-905-331-2682**E-MAIL** [info@mgchemicals.com](mailto:info@mgchemicals.com)**E-MAIL** (Competent Person): [sds@mgchemicals.com](mailto:sds@mgchemicals.com)

### Emergency Phone Number

**For hazardous material incidents ONLY** (leaks, spills, fires, exposures or accidents)USA or CANADA—Call Verisk 3E at **+1-866-519-4752** or **+1-760-476-3962**

(Service access code: 335388)

**For emergencies involving the transport of dangerous goods;** 24/7 serviceCANADA—Call CANUTEC collect at **+1-613-996-6666** or **\*666** on cellular phones

## 4200UV

### Section 2: Hazard(s) Identification




#### Classification of Hazardous Chemical

##### GHS Categories

Criteria	Category	Signal Word	Pictograms
Eye Damage	1	Danger	Corrosion
Sensitization	1	Warning	Exclamation
Hazardous to the Aquatic Environment	1	Warning	Environment
Flammable Liquids	4	Warning	<i>none</i>

*Note:* The degree of severity is ranked within each hazard class from 1 (Highest Severity) to up to 5 (Lowest Severity), which is opposite to HMIS and NFPA conventions. Severity category rankings do not allow comparisons between classes.

#### Label Elements

<b>Signal Word</b>	<b>DANGER</b>
<b>Pictograms</b>	<b>Hazard Statements</b>
	H318: Causes serious eye damage
	H317: May cause an allergic skin reaction
	H410: Very toxic to aquatic life with long lasting effects
<i>No symbol</i>	H227: Combustible liquid

*Section continued on the next page*

## 4200UV

*Continued...*

<b>Prevention</b>	<b>Precautionary Statements</b>
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P261	Avoid breathing fumes, vapors and spray.
P280	Wear protective gloves and eye protection.
P272	Contaminated work clothing should not be allowed out of the workplace.
P273	Avoid release to the environment.
<b>Response</b>	<b>Precautionary Statements</b>
P370 + P378	In case of fire: Use dry chemical, carbon dioxide, chemical foam, or water spray to extinguish.
P305 + P351 + P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P310	Immediately call a POISON CENTER or doctor.
P302 + P352	IF ON SKIN: Wash with plenty of water or shower.
P362 + P364	Take off contaminated clothing and wash it before reuse.
P333 + P313	If skin irritation or rash occurs: Get medical advice or attention.
P391	Collect spillage.
<b>Storage</b>	<b>Precautionary Statements</b>
P403	Store in a well-ventilated place.
<b>Disposal</b>	<b>Precautionary Statements</b>
P501	Dispose of contents in accordance to local, regional, national, and international regulations.

### Hazards Not Otherwise Classified

<b>Other Criteria</b>	<b>Hazard Statements/Precautionary Statement</b>	<b>Signal Word</b>	<b>Pictograms</b>
Defats skin	Repeated exposure may cause skin dryness or cracking.	Not applicable	Not applicable

**4200UV**
**Section 3: Composition/Information on Ingredients**

CAS #	Chemical Name	%(weight)
5888-33-5	isobornyl acrylate	52%
Trade secret <sup>a)</sup>	isocyanatoacrylate	31%
3524-68-3	pentaerythritol triacrylate	4%
123-86-4	n-butyl acetate	3%
4986-89-4	pentaerythritol tetraacrylate	2%

a) The specific chemical identity and/or exact percentage (concentration) of composition has been withheld as a trade secret. Exemption granted under HMIRC Registry Number: 3339191, December Pending.

**Section 4: First-Aid Measures**

<i>Exposure Condition</i>	<i>GHS Code/Symptoms/Precautionary Statements</i>
<b>IF IN EYES</b>	P305 + P351 + P338, P310
<b>Immediate Symptoms</b>	<i>redness, pain, eye damage, swelling of the eye lids</i>
<b>Response</b>	Rinse cautiously with water for at least 30 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or doctor.
<b>IF ON SKIN</b>	P302 + P352, P362 + P364, P333 + P313
<b>Immediate Symptoms</b>	<i>redness, irritation, dry skin, allergic contact dermatitis</i>
<b>Response</b>	Wash with plenty of water or shower. Take off contaminated clothing and wash it before reuse. If skin irritation or rash occurs: Get medical advice or attention.
<b>IF INHALED</b>	P304 + P340, P312
<b>Immediate Symptoms</b>	<i>cough, sore throat, dizziness, headache, irritation to the respiratory tract</i>
<b>Response</b>	Remove person to fresh air and keep comfortable for breathing.

*Section continued on the next page*

**4200UV***Continued...*

<b>IF SWALLOWED</b>	P301 + P330 + P331
<b>Immediate Symptoms</b>	<i>nausea, abdominal pain, diarrhoea, vomiting</i>
<b>Response</b>	Rinse mouth. Do NOT induce vomiting.

**Section 5: Fire-Fighting Measures**

<b>Extinguishing Media</b>	In case of fire: Use dry chemical, carbon dioxide, chemical foam, or water spray to extinguish.
<b>Specific Hazards</b>	Produces irritating and toxic fumes in fires or in contact with hot surfaces. Produces irritating smoke of unknown toxicity in fires.  Prevent fire-fighting wash from entering waterway or sewer system.
<b>Combustion Products</b>	Produces carbon oxides (CO, CO <sub>2</sub> ) and toxic fumes.
<b>Fire-Fighter</b>	Wear self-contained breathing apparatus and full fire-fighting turn-out gear.

**Section 6: Accidental Release Measures**

<b>Personal Protection</b>	See personal protection recommendations in Section 8.
<b>Precautions for Response</b>	Avoid breathing fumes, vapors or spray. Remove or keep away all sources of extreme heat or open flames.
<b>Environmental Precautions</b>	Avoid releasing to the environment. Prevent spill from entering drains and waterways.
<b>Containment Methods</b>	Contain with inert and non-flammable absorbent (such as soil, sand, vermiculite).
<b>Cleaning Methods</b>	Collect liquid in a sealable, chemical-resistant container. Sprinkle inert absorbent compound onto spill, then sweep into the container. Wipe off residues with paper towels and place the used towels in the waste container. Use soap and water to remove the last traces of residue.
<b>Disposal Methods</b>	Dispose of spill waste according to Section 13.

## 4200UV

### Section 7: Handling and Storage

<b>Prevention</b>	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.  Avoid breathing fumes, vapors or spray. Keep container tightly closed.  Avoid release to the environment.
<b>Handling</b>	Wear protective gloves and eye protection.  Take off contaminated clothing and wash it before reuse. Contaminated work clothing should not be allowed out of the workplace.  Collect spillage.
<b>Storage</b>	Store in a well-ventilated place.

### Section 8: Exposure Controls/Personal Protection

#### Substances with Occupational Exposure Limit Values

Chemical Name	Country	Long Term Exposure Limits (PEL)	Short Term Exposure Limits (STEL)
n-butyl acetate	ACGIH	150 ppm	Not established
	U.S.A. OSHA PEL	150 ppm	Not established
	Canada AB	150 ppm	200 ppm
	Canada BC	20 ppm	200 ppm
	Canada ON	150 ppm	Not established
	Canada QC	150 ppm	200 ppm

*Note:* The ACGIH<sup>1</sup>, OSHA (Table Z-1), and Canadian provinces exposure limits were consulted. Limits from the RTECS database<sup>2</sup> and from suppliers' SDS were also consulted. Short term exposure limits (STEL) are for 15 min and long term permissible exposure limits (PEL) for 8 h.

#### Engineering Controls

<b>Ventilation</b>	Keep airborne concentrations below the occupational exposure limits (OEL).
--------------------	--

*Section continued on the next page*

## 4200UV

### Personal Protective Equipment

**Eye protection**

Wear appropriate protective eyeglasses or chemical safety goggles.

**RECOMMENDATION:** Ensure that glasses have side shields for lateral protection.

**Skin Protection**

For likely contacts, use of protective butyl rubber or other chemically resistant gloves.

For incidental contacts, use nitrile or other chemically resistant gloves.

**Respiratory Protection**

For over-exposures up to 10 x OEL of mist, vapors, and spray, wear respirator such as a half-mask respirator with organic vapor cartridges.

Above 10 x OEL, use a positive-pressure, air-supplied respirator or a self-contained breathing apparatus.

**RECOMMENDATION:** Consult your local safety supply store to ensure that your respirator has a NIOSH (U.S.) approved filter cartridges appropriate for the ingredients listed in Section 3. The respirator should be fitted to the employee by a professional. Ensure vapor cartridges are stored in sealed plastic bags when not being used.

### General Hygiene Considerations

Wash hands thoroughly with water and soap after handling.

**4200UV**
**Section 9: Physical and Chemical Properties**

<b>Physical State</b>	Liquid	<b>Lower Flammability Limit</b> <sup>a)</sup>	1%
<b>Appearance</b>	Amber	<b>Upper Flammability Limit</b> <sup>a)</sup>	8%
<b>Odor</b>	Slightly acrylic	<b>Vapor Pressure @20 °C</b>	Not available
<b>Odor Threshold</b>	Not available	<b>Vapor Density</b>	>1 (Air=1)
<b>pH</b>	Not available	<b>Relative Density @25 °C</b>	1.06
<b>Freezing/Melting Point</b>	Not available	<b>Solubility in Water</b>	Immiscible
<b>Initial Boiling Point</b>	≥127 °C [≥261 °F]	<b>Partition Coefficient n-octanol/water</b>	Not available
<b>Flash Point</b>	68 °C [154 °F]	<b>Auto-ignition Temperature</b>	Not available
<b>Evaporation Rate</b>	Not available	<b>Decomposition Temperature</b>	Not available
<b>Flammability</b>	Combustible	<b>Viscosity @25 °C</b>	>20.5 mm <sup>2</sup> /s

a) Based on Raoult's Law and LeChatelier principle.

**Section 10: Stability and Reactivity**

<b>Reactivity</b>	Not applicable.
<b>Chemical Stability</b>	Chemically stable at normal temperatures and pressures
<b>Conditions to Avoid</b>	Avoid flames, sparks, other ignition sources, direct sunlight and incompatible substances.
<b>Incompatibilities</b>	Strong oxidizing agents, strong acids, alkali, water
<b>Polymerization</b>	Will not occur
<b>Decomposition</b>	Will not decompose under normal conditions. For thermal decomposition, see combustion products in Section 5.



## 4200UV

### Section 11: Toxicological Information

#### Summary of Effects and Symptoms by Routes of Exposure

<b>Eyes</b>	May cause redness, pain, irritation, or swelling of the eye lids.
<b>Skin</b>	May cause skin redness, irritation, dry skin, or allergic contact dermatitis.
<b>Inhalation</b>	May cause cough, sore throat, dizziness, headache, irritation to the respiratory tract.
<b>Ingestion</b>	May cause nausea, abdominal pain, diarrhoea or vomiting.
<b>Chronic</b>	Prolonged and repeated exposure may lead to skin sensitization.

#### Acute Toxicity (Lethal Exposure Concentrations)

Chemical Name	LD50 oral	LD50 dermal	LC50 inhalation
isobornyl acrylate	4 350 mg/kg Rat	Not available	Not available
pentaerythritol triacrylate	Not available	Not available	Not available
n-butyl acetate	10 768 mg/kg Rat	17 600 mg/kg Rat	Not available
pentaerythritol tetraacrylate	>10 000 mg/kg Rat	17 600 mg/kg Rat	>1 820 mg/L Rat

*Note:* Toxicity data from the RTECS<sup>2</sup> and ECHA were consulted. The data from supplier SDSs' were also consulted.

#### Other Toxicological Effects

<b>Skin corrosion/irritation</b>	Based on available data, the classification criteria are not met.
<b>Serious eye damage/irritation</b>	Based on available data, the classification criteria are not met.
<b>Sensitization</b> (allergic reactions)	Isobornyl acrylate and isocyanatoacrylate can cause skin sensitization.

*Section continued on the next page*

## 4200UV

**Carcinogenicity**

(risk of cancer)

None of the ingredients are classified or listed as a carcinogen by IARC, ACGIH, CA Prop 65, or NTP.

**Mutagenicity**

(risk of heritable genetic effects)

Based on available data, the classification criteria are not met.

**Reproductive Toxicity**

(risk to sex functions)

Based on available data, the classification criteria are not met.

**Teratogenicity** (risk of fetus

malformation)

Based on available data, the classification criteria are not met.

**STOT-single exposure**

Based on available data, the classification criteria are not met.

**STOT-repeated exposure**

Based on available data, the classification criteria are not met.

**Aspiration hazard**

There are no category 1 components, and the kinematic viscosity is  $>20.5 \text{ mm}^2/\text{s}$  at  $40 \text{ }^\circ\text{C}$ .

### Section 12: Ecological Information

Ecological classifications are based on the IMDG/GHS criteria in conjunction with ecotoxicological data from our suppliers, the European Chemical Agency database (<http://echa.europa.eu>), and other reliable sources.

Isobornyl acrylate is an acute and chronic category 1 environmental toxicant according to GHS criteria.

Based on available data, pentaerythritol triacrylate, n-butyl acetate, and pentaerythritol tetraacrylate are not classified as environmental hazards according to GHS criteria.

**Acute Ecotoxicity**

See chronic ecotoxicity.

*Section continued on the next page*

## 4200UV

### Chronic Ecotoxicity

Category 1

Very toxic to aquatic life with long lasting effect

Avoid release to the environment. Collect spillage.

### Biodegradability

Not available

### Bioaccumulation

Not available

### Other Effects

Not available

## Section 13: Disposal Considerations

Dispose of contents in accordance with all local, regional, national, and international regulations.

## Section 14: Transport Information

### Ground

**Refer to TDG regulations** (Canadian Transportation of Dangerous Goods regulations);  
**USA DOT 49 CFR** (Parts 100 to 185) **Regulations.**

Sizes 5 L and under  
4200UV-945ML, 4200UV-3.78L  
**Limited Quantity**



*FOR REFERENCE ONLY*

**UN number:** NA1993

**Shipping Name:** COMBUSTIBLE LIQUID  
(isobornyl acrylate)

**Class:** 3

**Packaging Group:** III

**Marine Pollutant:** Yes

*Section continued on the next page*

**4200UV****Air****Refer to ICAO-IATA regulations.**

Sizes 5 L and under  
4200UV-945ML, 4200UV-3.78L  
**Limited Quantity**



*FOR REFERENCE ONLY*

**UN number:** NA1993

**Shipping Name:** COMBUSTIBLE LIQUID  
(isobornyl acrylate)


**Class:** 3

**Packaging Group:** III

**Marine Pollutant:** Yes

**Sea****Refer to IMDG Regulations.**

Sizes 5 L and under  
4200UV-945ML, 4200UV-3.78L  
**Limited Quantity**



*FOR REFERENCE ONLY*

**UN number:** NA1993

**Shipping Name:** COMBUSTIBLE LIQUID  
(isobornyl acrylate)

**Class:** 3

**Packaging Group:** III

**Marine Pollutant:** Yes

**Note: Shipper must be appropriately trained and certified before involvement with the transport of dangerous goods.**

**Section 15: Regulatory Information****Canada****Domestic Substance List (DSL) / Non-Domestic Substance Lists (NDSL)**

All hazardous ingredients are listed on the DSL.


**Hazardous Products Act (R.S.C., 1985, c. H-3)**

The safety data sheet and label comply with the Hazardous Product Act and WHMIS 2015.

*Section continued on the next page*

**4200UV****USA****Other Classifications****HMIS<sup>®</sup> RATING**

<b>HEALTH:</b>	<b>*</b>	<b>2</b>
<b>FLAMMABILITY:</b>		<b>2</b>
<b>PHYSICAL HAZARD:</b>		<b>0</b>
<b>PERSONAL PROTECTION:</b>		

**NFPA<sup>®</sup> 704 CODES**

*Approximate HMIS and NFPA Risk Ratings Legend:*

0 (Low or none); 1 (Slight); 2 (Moderate); 3 (Serious); 4 (Severe)

**CAA** (Clean Air Act, USA)

This product does not contain any class 1 ozone depleting substances.

This product does not contain any class 2 ozone depleting substances.

This product does not contain substances that are listed as hazardous air pollutants.

**EPCRA** (Emergency Planning and Right to Know Act, USA, 40 CFR 372.45)

This product does not contain substances which are subject to the reporting requirements of section 313 Title III of the SARA of 1986 and 40 CFR part 372.

**TSCA** (Toxic Substances Control Act of 1976, USA)

All substances are TSCA listed.

**California Proposition 65** (Chemicals known to cause cancer or reproductive toxicity, USA).

This product does not contain any substances on the California Proposition 65 list.

**Europe****RoHS** (Restriction of Hazardous Substances Directive)

This product does not contain any lead, cadmium, mercury, hexavalent chromium, PBB's, PBDE's, DEHP, BBP, DBP, or DIBP and complies with European RoHS regulations.

**WEEE** (Waste Electrical and Electronic Equipment Directive)

This product is not a piece of electrical or electronics equipment, and is therefore not governed by this regulation.

**4200UV****Section 16: Other Information**

<b>SDS Prepared by</b>	MG Chemical's Regulatory Department
<b>Date of Review</b>	05 March 2020
<b>Supersedes</b>	10 February 2020
<b>Reason for Changes:</b>	Update to the emergency phone number information.

**Reference**

- 1) ACGIH 2017 TLVs and BEIs: Based on the documentation of the threshold limit values for chemical substances and physical agents & biological exposure indices, American Conference of Governmental of Industrial Hygienist Cincinnati, OH (2017).
- 2) All toxicological data were checked against the RTECS (Registry of Toxic Effects of Chemical Substances®)

**Abbreviations**

ACGIH	American Conference of Governmental Industrial Hygienists (USA)
EC50	Half maximal effective concentration
EL50	Half maximal effective loading
NOELR	No observable effect loading ratio
NTP	National Toxicology Program
GHS	Globally Harmonized System of Classification of Labeling of Chemicals
HMIRC	Hazardous Materials Information Review Commission
IARC	International Agency for Research on Cancer
LC50	Lethal Concentration 50%
LCLo	Lowest published lethal concentration
LD50	Lethal Dose 50%
OEL	Occupational Exposure Limit
PEL	Permissible Exposure Limit
SDS	Safety Data Sheet
STEL	Short-Term Exposure Limit
TCLo	Lowest published toxic concentration
TWA	Time Weighted Average
VOC	Volatile Organic Content

*Section continued on the next page*

---

**4200UV**

**Technical Queries** Contact us regarding any questions, improvement suggestions, or problems with this product. Application notes, instructions, and FAQs are located at [www.mgchemicals.com](http://www.mgchemicals.com).

Email: [support@mgchemicals.com](mailto:support@mgchemicals.com)

Phone: +1-905-331-1396

**Mailing Addresses** *Manufacturing & Support*  
1210 Corporate Drive  
Burlington, Ontario, Canada  
L7L 5R6

*Head Office*  
9347-193rd Street  
Surrey, British Columbia, Canada  
V4N 4E7

**Disclaimer** This safety data sheet is provided as an information resource only. *M.G. Chemicals, Ltd.* believes the information contained herein is accurate and compiled from reliable sources. It is the responsibility of the user to query and verify any information seeming suspect where doubt on the validity may exist. The buyer assumes all responsibility of using and handling the product in accordance with local, regional, national, and international regulations.