

Rhino™ 4200



Compact, Time-Saving Label Maker for On-The-Go Pros

- Familiar computer-style keyboard with country-specific layout for fast and easy text entry
- One-Touch “Hot Keys” provide shortcuts for creating and formatting wire/cable wraps, flags, Code 39 and Code 128 bar codes, fixed-length, general and breaker labels
- “Favorites” key provides single-key access to your most commonly used labels, symbols and terms
- Avoid repeated steps with the “Custom” key – customize and save settings for individual label formats
- Pre-programmed library with 150 symbols and terms for security, electrical, pro A/V, and facilities management
- Integrated rubber bumpers help prevent damage from accidental drops and falls
- Large back-lit display is easy to read, even in dimly-lit work areas



Single Unit Includes:

- Rhino 4200 Label Maker
- 12 mm White Vinyl Label Cartridge
- Quick Reference Guide



Kit Includes everything in single unit, plus:

- AC Adapter
- Carry Case
- Rechargeable Battery



Quick Specs

Unit Dimensions (H x W x L)	215 x 103 x 57 mm
Weight (excluding battery)	540 g
Mac®/PC Compatible	No
Accepts Label Sizes	6mm, 9mm, 12mm, 19mm
Tape Platform	IND Rhino™
Resolution	180 dpi
Printing System	Thermal Transfer
Print Speed	15mm/sec
Barcodes	Yes, Code 39 & Code 128
Cutter Type	Manual
Batteries	6 AA or Rechargeable (not included)
AC Adapter	Yes (not included)
Networking	No
Country of Origin	China

Item Number	Description		Length (cm)	Width (cm)	Height (cm)	Weight (kg)	QTY	EAN	Customer Price
1801611	RHINO 4200 QWERTY UK	Unit	8.8	15.6	23.0	0.7	1	0071701059598	
1852992	RHINO 4200 KIT QWERTY UK	Unit	9.2	27.5	26.5	1.1	1	3501178529920	

www.DYMO.com

Rhino™ 4200 | Authentic Labels



IND Vinyl

Ideal for both indoor and outdoor applications. Available in a wide range of colors.

- UL recognized component to UL 969
- RoHS compliant
- Temperature rating: -40°C to 80°C

IND Permanent Polyester

Professional, polished finish ideal for panels, blocks, faceplates, shelves, bins, beams and more.

- UL recognized component to UL 969
- RoHS compliant
- For flat surfaces only
- Temperature rating: -40°C to 150°C

IND Flexible Nylon

Specifically designed for curved surfaces and wire and cable marking.

- UL recognized component to UL 969
- RoHS compliant
- Temperature rating: -10°C to 80°C

IND Heat-Shrink Tube

For high-end cable identification. A 3:1 shrink ratio helps ensure a secure fit on wires and cables.

- Meets MIL-M-81531, MIL-STD-202G, SAE-DTL-23053/5 (Class 1 & 3)
- UL recognized as a component to UL 224
- RoHS compliant
- Temperature rating: -55° C to 135°C

IND Labels										
Width	Length	A	A	A	A	A	A	A	A	A
IND VINYL										
9mm	5.5m	18443	-	-	-	-	-	1805437	-	-
12mm		-	-	-	18435	-	1805416	1805435	1805414	1805243
19mm		-	-	18433	-	-	1805422	1805436	1805420	1805417
IND PERMANENT POLYESTER										
6mm	5.5m	1805442	1805440	-	-	1805441	-	-	-	-
9mm		18482	18508DMO	-	-	18485	-	-	-	-
12mm		18483	622289	-	-	18486	-	-	-	-
19mm		18484	622290	-	-	18487	-	-	-	-
IND FLEXIBLE NYLON										
12mm	3.5m	18488	-	18490	-	-	-	-	-	-
19mm	3.5m	18489	-	18491	-	-	-	-	-	-
IND HEAT-SHRINK TUBE										
6mm	1.5m	18051	-	18052	-	-	-	-	-	-
9mm		18053	-	18054	-	-	-	-	-	-
12mm		18055	-	18056	-	-	-	-	-	-
19mm		18057	-	18058	-	-	-	-	-	-

Country of Origin: Belgium



This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.

