

Handheld True RMS Digital Multimeter

**multicomp**PRO

RoHS  
Compliant



Features

- True RMS
- USB Communication
- NCV
- Max/Min
- Relative Mode
- Analog Bar
- Display Count: 6000
- Duty Cycle: 0.1% to 99.9%

Specifications	Range	
DC Voltage	1000V	±(0.5%+3)
AC Voltage	1000V	±(1%+3)
DC Current	10A	±(1%+2)
AC Current	10A	±(1.2%+5)
Resistance	60MΩ	±(1%+2)
Capacitance	60mF	±(3%+5)
Frequency	10Hz to 10MHz	±(0.1%+4)

General Characteristics

- Power
- : 1.5V battery (R03) x 4
- Weight
- : 350g
- Size
- : 190mm × 90mm × 50mm
- Standard accessories
- : Battery, Test Leads, USB cable
- Warranty
- : 12 Months

Part Number Table

Description	Part Number
Handheld True RMS Digital Multimeter, 1000V AC/DC, 10A AC/DC, 60MΩ	MP730651

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
Element14.com/multicomp-pro

**multicomp**PRO