



TECHNICAL INFORMATION

| | |
|--------------|-------------------|
| Input Power: | AC:220-240V, 50Hz |
| Unit Color: | Black |
| Body Type: | Aluminium |
| Dimmable: | No |
| Beam Angle: | 300° |
| Rated Load: | Max 60Wx2 |
| Dimension: | 500x1990mm |

POLE LAMPS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 7062 - 938

[View more details](#)



**TRADITIONAL
GARDEN LAMPS**
ALUMINIUM &
GLASS BODY



FEATURES

- Traditional garden lamps designed to meet modern day requirements
- Strong and sturdy Aluminium body
- Offering IP44 Ingress protection
- Compatible with E27 holder type (Fitting only - light not included)
- Suitable for gardens, patio, pathways etc.
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warranty

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs): 6.3

Unit CBM: 0.0723

Dimension: 500x1990mm

MASTER BOX PACKAGING

Box Qty: 1

Qty Per Pallet: 20

LISTING DETAILS

Commodity Code: 9405109890

EanCode: 3800157612654