



TECHNICAL INFORMATION

Input Power:	AC:220-240V, 50Hz
Unit Color:	Black
Body Type:	Aluminium
Dimmable:	No
Beam Angle:	300°
Rated Load:	Max 60Wx3
Dimension:	500x1990mm

POLE LAMPS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 7063 - 938

[View more details](#)



**E27
HOLDER**

COMPATIBLE WITH
E27 BULBS

*Bulbs are not included

**TRADITIONAL
GARDEN LAMPS**

**ALUMINIUM &
GLASS BODY**



**3 YEAR
WARRANTY**



**IP44
RATING**

FEATURES

- Traditional garden lamps designed to meet modern day requirements
- Strong and sturdy Aluminium body
- Offering IP44 Ingress protection
- Compatible with E27 holder type (Fitting only - light not included)
- Suitable for gardens, patio, pathways etc.
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warranty

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs): 7.1

Unit CBM: 0.0723

Dimension: 500x1990mm

MASTER BOX PACKAGING

Box Qty: 1

Qty Per Pallet: 20

LISTING DETAILS

Commodity Code: 9405109890

EanCode: 3800157612661